



DISASTER RESPONSE SOLUTIONS

M18 FUEL™ 20" DUAL BATTERY CHAINSAW KIT


2827-22

GENERATES
70cc GAS
POWER

REDUCED STALLS
FASTER
CUTTING

BALANCED
DESIGN, MORE
CONTROL

RESPOND FASTER. WE'RE READY TO SUPPORT YOU.



POWER TOOLS | EQUIPMENT | LIGHTING | HAND TOOLS | ACCESSORIES | PERSONAL PROTECTIVE EQUIPMENT



DISASTER RESPONSE SOLUTIONS

POWER TOOLS

Crimping/Cutting

-  **M18™ FORCE LOGIC™ 6T Latched Linear Utility Crimper Kit**
2979-22
-  **M18™ FORCE LOGIC™ 6T Linear Utility Crimper Kit w/ BG-D3 Jaw**
2978-22BG
-  **M18™ FORCE LOGIC™ 6T Pistol Utility Crimper BG-D3 Kit**
2977-22BG
-  **M18™ FORCE LOGIC™ 6T Utility Crimper Kit w/ BG-D3 Jaw**
2678-22BG
-  **M18™ FORCE LOGIC™ 12T Utility Crimper Kit**
2778-22
-  **M18™ FORCE LOGIC™ 15T Crimper Kit**
2879-22
-  **M18™ FORCE LOGIC™ 10,000 PSI Hydraulic Pump Kit**
2774-21HD
-  **M18™ FORCE LOGIC™ 3" Underground Cable Cutter Kit w/ Wireless Remote**
2776R-21
-  **M18™ FORCE LOGIC™ 5" Underground Cable Cutter Kit w/ Wireless Remote**
2875R-21
-  **M18™ FORCE LOGIC™ 1590 ACSR Cable Cutter Kit**
2777-21

Drilling/Driving

-  **M18 FUEL™ 7/16" Hex Utility High Torque Impact Wrench Kit w/ ONE-KEY™**
2865-22
-  **M18 FUEL™ 1/2" Hammer Drill/Driver Kit**
2904-22
-  **M18 FUEL™ 1/4" Hex Impact Driver Kit**
2953-22
-  **M18 FUEL™ 1-1/2" Lineman Magnetic Drill Kit**
2788-22HD
-  **M18 FUEL™ SUPER HAWG™ 1/2" Right Angle Drill**
2809-20
-  **M18 FUEL™ SUPER HAWG™ Right Angle Drill w/ QUIK-LOK™**
2811-20

Outdoor Power Equipment

-  **M18 FUEL™ 14" Top Handle Chainsaw 2 Battery Kit**
2826-22T
-  **M18 FUEL™ 16" Chainsaw Kit**
2727-21HD
-  **M18 FUEL™ 20" Dual Battery Chainsaw Kit**
2827-22
-  **M18 FUEL™ 10" Pole Saw Kit w/ QUIK-LOK™**
2825-21PS
-  **M18 FUEL™ QUIK-LOK™ 10" Pole Saw Attachment**
49-16-2720
-  **M18 FUEL™ HATCHET™ 8" Pruning Saw**
3004-20
-  **M18™ Brushless Stick Transfer Pump**
2940-20

Staplers

-  **M18 FUEL™ Utility Fencing Stapler Kit**
2843-22

STAPLES

-  **1-1/2" 9 Gauge Galvanized Staples**
MPU112-960
-  **1-3/4" 9 Gauge Galvanized Staples**
MPU134-960
-  **2" 9 Gauge Galvanized Staples**
MPU2-960

BATTERIES AND CHARGERS

M18™

-  **M18™ REDLITHIUM™ FORGE™ XC6.0 Battery Pack**
48-11-1861
-  **M18™ REDLITHIUM™ HIGH OUTPUT™ XC8.0 Battery Pack**
48-11-1880
-  **M18™ REDLITHIUM™ HIGH OUTPUT™ HD12.0 Battery Pack**
48-11-1812
-  **M18™ REDLITHIUM™ XC5.0 Battery Pack**
48-11-1850
-  **M18™ Six Pack Sequential Charger**
48-59-1806
-  **M18™ and M12™ Vehicle Charger**
48-59-1810
-  **M18™ Dual Bay Simultaneous Super Charger**
48-59-1815
-  **M18™ Dual Bay Simultaneous Rapid Charger**
48-59-1802

MX FUEL™

-  **MX FUEL™ REDLITHIUM™ FORGE™ HD12.0 Battery Pack**
MXFHD812
-  **MX FUEL™ REDLITHIUM™ FORGE™ XC8.0 Battery Pack**
MXFXC608
-  **MX FUEL™ REDLITHIUM™ XC406 Battery Pack**
MXFXC406
-  **MX FUEL™ REDLITHIUM™ CP203 Battery Pack**
MXFCP203
-  **MX FUEL™ Super Charger**
MXFSC
-  **MX FUEL™ Rapid Charger**
MXFRC
-  **MX FUEL™ Charger**
MXFC

POWER SUPPLY

-  **ROLL-ON™ 7200W/3600W 2.5kWh Power Supply**
3300R
-  **MX FUEL™ CARRY-ON™ 3600W/1800W Power Supply Kit**
MXF002-2XC
-  **M18™ TOP-OFF™ 175W Power Supply**
2846-20
-  **M12™ TOP-OFF™ Power Supply and Charger**
48-59-1211

EQUIPMENT

-  **MX FUEL™ 1 HP 2" Submersible Pump Kit**
MXF211-1XC
-  **MX FUEL™ ROCKET™ Dual Power Compact Tower Light**
MXF040-1XC
-  **MX FUEL™ ROCKET™ Tower Light/Charger Kit**
MXF041-1XC

HAND TOOLS

Cutting

-  **Lineman's Blunt Tip Hawkbill Knife w/ STICKWORK™ 3m1 Ring**
48-22-1923
-  **Lineman's Hawkbill Knife w/ STICKWORK™ 3m1 Ring**
48-22-1924
-  **Lineman's Underground Knife**
48-22-1929
-  **FASTBACK™ Hawkbill Folding Knife**
48-22-1525
-  **FASTBACK™ Blunt Tip Hawkbill Folding Knife**
48-22-1526

Fastening

-  **9" Lineman's Dipped Grip Pliers (USA)**
MT500
-  **9" Lineman's Dipped Grip Pliers w/ Thread Cleaner (USA)**
MT500T
-  **8" Long Nose Dipped Grip Pliers (USA)**
MT505
-  **9" Lineman's Comfort Grip Pliers (USA)**
MT550
-  **9" Lineman's Comfort Grip Pliers w/ Thread Cleaner (USA)**
MT550T
-  **8" Long Nose Comfort Grip Pliers (USA)**
MT555
-  **Lineman's 2m1 Insulated Ratcheting Box Wrench**
48-22-9211
-  **Lineman's 4m1 Insulated Ratcheting Box Wrench**
48-22-9212
-  **Lineman's High-Leverage Ratcheting Wrench w/ Smooth Strike Face**
48-22-9213
-  **Lineman's High-Leverage Ratcheting Wrench w/ Milled Strike Face**
48-22-9213M
-  **Lineman's 5m1 Ratcheting Wrench w/ Smooth Strike Face**
48-22-9216
-  **Lineman's 5m1 Ratcheting Wrench w/ Milled Strike Face**
48-22-9216M

-  **2 Pc Demolition Screwdriver Set**
48-22-2702

-  **Demo Driver**
48-22-2860

-  **12" Straight Jaw Comfort Grip Pliers**
48-22-6312

-  **10" Straight Jaw Comfort Grip Pliers**
48-22-6310

-  **Lineman's High-Leverage Dipped Grip Pliers w/ Thread Cleaner**
48-22-6503

Measuring

-  **6-1/2' Composite Folding Rule**
48-22-3801
-  **100' Steel Open Reel Long Tape**
48-22-5201

LIGHTING

M18™ Lighting

-  **M18™ Utility Bucket Light**
2122-22HD, 2122-20
-  **M18™ ROCKET™ Dual Pack Tower Light w/ ONE-KEY™**
2120-22HD, 2120-20
-  **M18™ ROCKET™ Dual Power Tower Light**
2131-20
-  **M18™ ROCKET™ Tower Light/Charger**
2136-21, 2136-20
-  **M18™ Search Light**
2354-20
-  **Utility Remote Control Search Light**
2123, 2123-20
-  **M18™ Utility Remote Control Search Light Kit**
2123-21HD

Personal Lighting

-  **MILWAUKEE™ Headlamp**
2103
-  **USB Rechargeable Hard Hat Headlamp Kit**
2111-21

PPE

Milwaukee Tool offers personal protective equipment solutions for a disaster response.

-  **BOLT™ White Front Brim Hard Hat w/ 4pt Ratcheting Suspension – Type I Class E**
48-73-1100
-  **Cut Level 1 Nitrile Dipped Gloves – S**
48-22-8900
-  **Cut Level 1 Nitrile Dipped Gloves – M**
48-22-8901
-  **Cut Level 1 Nitrile Dipped Gloves – L**
48-22-8902
-  **Cut Level 1 Nitrile Dipped Gloves – XL**
48-22-8903
-  **Cut Level 1 Nitrile Dipped Gloves – XXL**
48-22-8904
-  **Anti-Vibration Work Gloves – S**
48-73-8770
-  **Anti-Vibration Work Gloves – M**
48-73-8771
-  **Anti-Vibration Work Gloves – L**
48-73-8772
-  **Anti-Vibration Work Gloves – XL**
48-73-8773
-  **Anti-Vibration Work Gloves – XXL**
48-73-8774
-  **Goatskin Leather Gloves – S**
48-73-0010
-  **Goatskin Leather Gloves – M**
48-73-0011
-  **Goatskin Leather Gloves – L**
48-73-0012
-  **Goatskin Leather Gloves – XL**
48-73-0013
-  **Goatskin Leather Gloves – XXL**
48-73-0014

**MORE SOLUTIONS
ON NEXT PAGE**

RESPOND FASTER. WE'RE READY TO SUPPORT YOU.

Please contact your local Milwaukee Tool representative to order
or for additional program details.



DISASTER RESPONSE SOLUTIONS

PPE (Continued)

- ☐ Impact Cut Level 5
Goatskin Leather Gloves – S
48-22-8780
- ☐ Impact Cut Level 5
Goatskin Leather Gloves – M
48-22-8781
- ☐ Impact Cut Level 5
Goatskin Leather Gloves – L
48-22-8782
- ☐ Impact Cut Level 5
Goatskin Leather Gloves – XL
48-22-8783
- ☐ Impact Cut Level 5
Goatskin Leather Gloves – XXL
48-22-8784

ACCESSORIES

MILWAUKEE® offers a full line of accessories for disaster response. The following are the most common.

Auger Bits

- ☐ 11/16" SHOCKWAVE™ Impact Duty Lineman's
18" Auger Bit
48-13-6705
- ☐ 13/16" SHOCKWAVE™ Impact Duty Lineman's
18" Auger Bit
48-13-6707
- ☐ 15/16" SHOCKWAVE™ Impact Duty Lineman's
18" Auger Bit
48-13-6709
- ☐ 11/16" SHOCKWAVE™ Impact Duty Lineman's
24" Auger Bit
48-13-6805
- ☐ 15/16" SHOCKWAVE™ Impact Duty Lineman's
24" Auger Bit
48-13-6809
- ☐ 11/16" SHOCKWAVE™ Impact Duty Lineman's
30" Auger Bit
48-13-6905
- ☐ 13/16" SHOCKWAVE™ Impact Duty Lineman's
30" Auger Bit
48-13-6907
- ☐ 9/16" SHOCKWAVE™ Impact Duty Lineman's
12" Fiberglass Drill Bit
48-13-7703
- ☐ 9/16" SHOCKWAVE™ Impact Duty Lineman's
18" Auger Bit
48-13-6703
- ☐ 9/16" SHOCKWAVE™ Impact Duty Lineman's
24" Auger Bit
48-13-6803

Sockets

- ☐ 7/16" SHOCKWAVE™ Impact Duty Lineman's
3-in-1 Transmission Utility Socket
49-66-5102
- ☐ 3/8" & 1/2" SHOCKWAVE™ Impact Duty
Lineman's 2-in-1 12 Point Socket
49-66-5119
- ☐ 7/16" & 5/8" SHOCKWAVE™ Impact Duty
Lineman's 2-in-1 12 Point Socket
49-66-5120
- ☐ 9/16" & 3/4" SHOCKWAVE™ Impact Duty
Lineman's 2-in-1 12 Point Socket
49-66-5121
- ☐ 15/16" & 1-1/8" SHOCKWAVE™ Impact Duty
Lineman's 2-in-1 12 Point Socket
49-66-5124
- ☐ 9/16" & 3/4" SHOCKWAVE™ Impact Duty
Lineman's 2-in-1 6 Point Socket
49-66-5111

- ☐ 10 Pc SHOCKWAVE™ Impact Duty Lineman's
2-in-1 12 Point Socket Set
49-66-5125

- ☐ 1/2" SHOCKWAVE™ Impact Duty Lineman's
3-in-1 Distribution Utility Socket
49-66-5101

- ☐ 5/16" SHOCKWAVE™ Impact Duty Lineman's
1/2" Drive Hex Bit Socket
49-66-5141

POWER UTILITY STORAGE

- ☐ Lineman's Aerial Tool Apron
48-22-8290
- ☐ Canvas Utility Bucket w/ Pockets
48-22-8270
- ☐ Underground Oval Bucket
48-22-8275
- ☐ Aerial Oval Bucket
48-22-8276
- ☐ Canvas Utility Bucket
48-22-8271
- ☐ Lineman's Compact Aerial Tool Apron
48-22-8291
- ☐ 2" Bucket Hook
48-22-8292
- ☐ 3" Bucket Hook
48-22-8293



RESPOND FASTER. WE'RE READY TO SUPPORT YOU.

Please contact your local Milwaukee Tool representative to order
or for additional program details.