



V-Gard C1™ Hard Hat

The coolest hard hat on the market, keeping the inside of your hard hat up to 20°F cooler.




WE KNOW WHAT'S AT STAKE.



ReflectIR™ Thermal Barrier

The patent-pending ReflectIR™ Thermal Barrier works to block the energy of the sun, keeping the inside of the hard hat up to 20°F (11°C) cooler¹, reducing the risk of heat stress.




Available with the Largest Vents MSA Offers on a Full-Brim Hat

- Strategically placed vents optimize airflow, increasing comfort and further reducing heat stress.
- Non-vented options available to maintain Class E Certification

¹ Compared to a hard hat without the ReflectIR Thermal Barrier in sunny conditions; testing done with black, non-vented, V-Gard C1 Hard Hats


Increased Comfort

- The market-leading Fas-Trac® III Suspension comes preinstalled, providing the highest level of customization and comfort you depend on from MSA head protection.
- The premium moisture-wicking sweat band pulls sweat away from the head allowing it to evaporate into the air, while providing a breathable foam padding, keeping you dry and comfortable. The sweat band can be easily removed to be laundered or replaced to help maintain hygiene.



Increased Sun Protection

- The full brim on the V-Gard C1 Hard Hat offers 12% more coverage², providing additional shade while protecting you from harmful UV rays.
- Unique textured brim provides added grip when donning and doffing the hard hat.



² Compared to a full-brim V-Gard® or V-Gard 500 Hard Hat



Specifications

	Non-Vented	Vented
STANDARDS COMPLIANCE	ANSI/ISEA Z89.1-2014 (R2019) CSA Z94.1-15	
OPTIONAL REQUIREMENTS (ANSI)	LT (Low Temp) HT High Temp Reverse Donning HV (Hi-Viz, as indicated)	
ANSI Z89.1 & CSA Z94.1 CLASSIFICATION	Type 1, Class E	Type 1, Class C
3RD PARTY CERTIFICATIONS	SEI	
STYLE	Non-Vented	Vented
PRODUCT SIZE	Standard head size 6½-8 (52-64 cm head circumference)	
OTHER PPE	Compatible with all current V-Gard Hard Hat accessories: Fas-Trac III Suspension, frames, visors, hearing protection, chinstraps, sun shades, sun shields, cooling pads, & winter liners	

Ordering Information

Color	Non-Vented	Vented
WHITE	10215837	10215828
RED	10215838	10215829
BLUE	10215839	10215830
GREEN	10215840	10215831
YELLOW	10215841	10215832
ORANGE	10215843	10215834
BLACK	10215844	10215835
GRAY	10215845	10215836
HI-VIZ ORANGE	10215842	10215833
HI-VIZ YELLOW GREEN	10237724	10236066
CUSTOM COLOR	Custom color options available.	



Customization

- Full-color logos available in up to three locations:
 - Front and back
 - Front, back left, and back right
- Reflective striping available in silver or yellow up to 360° coverage: front, back, and sides
- Custom hard hat colors available



Note: This Bulletin contains only a general description of the products shown. While product uses and performance capabilities are generally described, the products shall not, under any circumstances, be used by untrained or unqualified individuals. The products shall not be used until the product instructions/user manual, which contains detailed information concerning the proper use and care of the products, including any warnings or cautions, have been thoroughly read and understood. Specifications are subject to change without prior notice. MSA is a registered trademark of MSA Technology, LLC in the US, Europe, and other Countries. For all other trademarks visit <https://us.msasafety.com/Trademarks>.

MSA operates in over 40 countries worldwide. To find an MSA office near you, please visit [MSAsafety.com/offices](https://us.msasafety.com/offices).