



MOBILE CART PRODUCT FAMILY



PRODUCT IDEA



The market is moving toward a different style and aesthetic for mobile carts. Our goal was to provide a similar style and aesthetic with unparalleled features and benefits that customers require

peerless-AV[®]
Driving Technology Through Innovation

PURPOSE BUILT LEG DESIGN

SR860 & SR898 Mobile Carts

- MOVE FREELY AROUND THE CART WHILE PRESENTING
- LEGS ROLL UNDER MEETING TABLES FOR TELECONFERENCING SOLUTIONS
- MODERN STYLE FOR CORPORATE ENVIRONMENTS
- REDUCES DAMAGE TO WALLS WHEN MOVING CART FROM ROOM TO ROOM
- ALLOWS NESTING OF MULTIPLE CARTS FOR STORAGE

COMPACT LEG DESIGN ALLOWS ENTRY THROUGH
DOORWAYS AS NARROW AS 30" (762MM) WIDE

- ADA COMPLIANT DESIGN
- LEG DESIGN ALLOW WHEELCHAIR ACCESS FOR TOUCH APPLICATIONS
- DISPLAY IS HEIGHT ADJUSTABLE FROM 49.8" TO 65.8"



LATEST TECHNOLOGY

SR860 & SR898 Mobile Carts

- **ALLOWS EASY INTEGRATION OF VIDEO CONFERENCING SOLUTIONS**
- **WIDE RANGE OF ACCESSORIES TO SUPPORT SOUND BARS, POWER AND VARIOUS AV COMPONENTS**

PRODUCT OVERVIEW

Mobile Cart Product Family

Flat Panel Cart Comparison



	SR898	SR860	SR598	SR560M	PR565
In warehouse date:	12/7/23	12/7/23	2/5/24	2/5/24	4/1/24
Max VESA Pattern	900 x 600mm	800 x 400mm	900 x 600mm	600 x 400mm	1000 x 600mm
Display Range	55" to 110"	32" to 75"	55" to 98"	32" to 75"	55" to 75"
Max Display Height	65.8"	65.8"	60"	60"	61.5"
TAA Compliant	✓	✓	✓	✓	✓
UL Listed	✓	✓	✓	✓	
Tested to 2X+ 100lb Load	✓	✓	✓	✓	
Tested to 10 Degree Tip Test	✓	✓	✓	✓	
Caster Braking Test	✓	✓	✓	✓	
ADA Compliant	✓	✓			
Height Adjustment	✓	✓	✓	✓	✓



	SR898	SR860	SR598	SR560M	PR565
4" Casters	✓	✓	✓	✓	✓
Internal Cable Management	✓	✓	✓	✓	
Fit through 30" Door Frame	✓	✓	✓	✓	
Fixed Shelf with Hidden Storage	✓	✓			
3-outlet Power Cord Included	✓	✓			
Stacking for Easy Storage	✓	✓			✓
Removable Rear Cover	✓	✓			
HETMA Approved					
Integrated Cord Wrap	✓	✓			
Adjustable Equipment Shelf			Optional	Optional	
Plumb Display Adjustment	✓	✓	✓	✓	
Dual Column Design for Touch	✓	✓	✓		✓
VC Camera Shelf			Optional	Optional	
Leveling Foot Accessory (ACC310)	Optional	Optional	Optional	Optional	

8 KEY DIMENSIONS OF PRODUCT - WHAT DID WE IMPROVE UPON?



SR860 & SR898

Mobile Cart Product Family

PRODUCT OVERVIEW

SR860 & SR898 Mobile Carts

SR carts have not had a major update since 2015

Goal - Improve cart design based off customer feedback:

- Improve base design to better facilitate presenting in front of a display
- Integrated cord wrap simplifies moving the cart and storing the power cable when not in use
- Provide better cord management and aesthetics for the area behind the display
- Increase height for better visibility in multiple row seating
- Improve integration with video conferencing solutions
- Provide hand grip areas to better maneuver the cart when transporting
- Improve installation / commonize hardware and reduce tools required
- Reduce the footprint of carts/displays when being stored



PRODUCT OVERVIEW

SR860 & SR898 Mobile Carts

SR860

- 43-75"+ Displays
- 125 lb (56.7 kg) load rating
- Up to 830 x 400mm max VESA pattern
- Manual Height Adjustment – 49.8 – 65.8" (1266-1672mm)
- Up to 5° of plumb adjustment for leveling display
- Shelf Included
- Rear ABS Cover Included (security screws and thumb screws)
- Cord Wrap Included
- 20ft 3 outlet extension cord included (US only)



PRODUCT OVERVIEW

SR860 & SR898 Mobile Carts

SR898

- 55-110"+ Displays
- 300 lb (136.1 kg) load rating
- Up to 900 x 600mm max VESA pattern
- Manual Height Adjustment – 49.8 – 65.8" (1266-1672mm)
- Up to 5° of plumb adjustment for leveling display
- Shelf Included
- Rear ABS Cover Included (security screws and thumb screws)
- Cord Wrap Included
- 20ft 3 outlet extension cord included (US only)




NEW LEG CONFIGURATIONS

SR860 & SR898 Mobile Carts

- Users should not feel awkward or create a tripping hazard when presenting or transporting the cart
- Reduced damage to walls and doorways
- Competitors product has to be “walked around” a door opening which can lead to display damage
- It is recommended by the ADA that you have a minimum of 32” for door openings. However, for most people, a door with a 30-inch opening is more than enough for standard wheelchair access.
- Legs easily fit under standard height tables for video conferencing use



Cart Easily Fits Through
Standard 30" (762mm) Doorway



ADA Compliant

STANDARD SHELF

SR860 & SR898 Mobile Carts


- 32" x 11" Fixed Shelf
- Dual Purpose- provides cross beam cart structure and a place for laptops, notebooks, pens and pencils
- 3 lips around the shelf prevent object from sliding off the shelf
- 21" Height from floor provides a functional height



CABLE MANAGEMENT

SR860 & SR898 Mobile Carts


- Allow end user to quickly and easily deploy cart and pack it back up
- Cable solution that hides cabling yet easily allows moves and changes without tools
- Hinged cover hides the cord wrap area
- Integrated cord wrap is preinstalled on the cart
- Integrated power cable allows easy routing of power to the display



CABLE MANAGEMENT

SR860 & SR898 Mobile Carts

- Integrated 3 outlet power cable provides a simple solution for plugging in the display, media players, mini PCs and other AV equipment
- Works with ACC-UCM to secure AV equipment
- Managing devices and cabling at the top of the cart creates the cleanest solution possible



REAR COVER

SR860 & SR898 Mobile Carts

- Rear cover accessory creates an ultra clean look and covers all cabling and AV equipment
- Cover is ABS molded so Wi-Fi signals are not degraded
- Great solution for glass walled meeting rooms



CART NESTING

SR860 & SR898 Mobile Carts

- Frame design allows carts to be easily nested for storage
- 21 ft² for (3) SR560M vs 13 ft² for (3) SR860



ACCESSORIES

SR860 & SR898 Mobile Carts

- ACC-SB2 – Soundbar / VC Bar Mount
- ACC-UCM – Universal AV Component Mount
- ACC-V900X – 600, 800 and 900mm VESA Adaptor
- ACC-V1500X – 1200 and 1500mm VESA Adaptor (Jupiter 21:9)
- MIS995 – 800mm VESA Adaptor
- ACC148 – 6 Outlet Surge Protector, 15ft Cord with Mounting Bracket
- ACC149 – (2) 600mm Tall Adaptor Brackets
- ACC151 – Replacement Caster Kit (SR860)
- ACC152 – Replacement Caster Kit (SR898)



PRODUCT OVERVIEW

Product Name: SmartMount Universal Mobile Cart

Model Number: SR860

Available Colors: Black

On Shelf: Available Now!

List Price: \$899



PRODUCT OVERVIEW

Product Name: SmartMount Universal Mobile Cart

Model Number: SR898

Available Colors: Black

On Shelf: Available Now!

List Price: \$1099



SR560M & SR598

Mobile Cart Product Family

PRODUCT OVERVIEW

SR560M & SR598 Knock-Down

SR560M

- Cart base will change from 1 pc welded design to 3 pc bolt together (customer assembled)
- Cart will no longer include metal shelf (ACC-MS) (Less than 25% used shelves)
- Adaptor brackets will now be preassembled
- Disty. pricing will be reduced from \$472.37 to \$429.00
- **Reduced packing size adds 5 units per skid (12 → 17)**
- March 1st Transition
- Assembly time remain unchanged

SR598

- Cart base will change from 1 pc welded design to 3 pc bolt together (customer assembled)
- Disty. pricing will be reduced from \$639.73 to \$579.00
- **Reduced packing size adds 2 units per skid (7 → 9)**
- March 1st Transition



PRODUCT OVERVIEW

SR560M & SR598 Knock-Down

Reduction of 10 containers per year!
A reduction of 43,541kgCO₂e!



9.7 gasoline-powered passenger
vehicles driven for one year ?



8.5 homes' electricity use for one
year ?



5,296,442 number of smartphones charged
?



48,773 pounds of coal burned ?



4,899 gallons of gasoline consumed ?



2,000 propane cylinders used for home
barbeques ?



[EPA Emission Equivalencies](#)

[Pledge freight emission calculator](#)

PRODUCT OVERVIEW

SR560M & SR598 Knock-Down



Every kg of cardboard in packaging produces about .94kg CO₂e

A 3lb packaging reduction = 9500 kg CO₂e reduction

2.1

gasoline-powered passenger vehicles driven for one year ?



1,069

gallons of gasoline consumed ?



[EPA Emission Equivalencies](#)

[Pledge freight emission calculator](#)

PR565

Mobile Cart Product Family

PRODUCT OVERVIEW

PR565 Mobile Cart


PR565

- 55-75"+ Displays
- 150 lb (56.7 kg) load rating
- Up to 1000 x 600mm max VESA pattern
- Fixed Height Adjustment – 45.1, 50.6, 56.0, 61.5"
- Up to 3° of plumb adjustment for leveling display
- Includes video conferencing shelf that can be mounted above or below the display, 10 lbs max, up to 98" display
- 39.7 x 8.5" shelf holds up to 20 lbs (9.1kg)
- Cabling is secured with velcro around cart legs
- No additional accessories
- No UL listing
- In stock




SELLING MESSAGE

SR860 / SR898




SELLING MESSAGE

SR560M / SR598



SELLING MESSAGE

PR565



QUESTIONS?

Thank You