




PIP

PERFORMANCE WORKWEAR

INDUSTRIAL LAUNDERABLE,
PREMIUM COMFORT


wesco

Bisley
WORKWEAR





HIGH PERFORMANCE MEETS COMFORT

Designed for today's industrial athletes, Bisley® redefines protective workwear by combining advanced design features, superior comfort, and exceptional freedom of movement. Built for demanding environments, these new high-performance garments not only excel on the jobsite but maintain their professional fit and comfort levels, even after repeated industrial washes. Available in styles tailored for both men and women, this collection ensures all workers can feel confident and capable.



BENEFITS OF INDUSTRIAL LAUNDERING

Safety Compliance: Ensuring flame-resistant and hi-visibility garments maintain their protective properties.

Enhanced Durability: Professional laundering is designed to handle industrial-strength fabrics, extending their lifespan.

Cost-Effectiveness: Effective cleaning of heavy contaminants reduces the need for replacement, improving sustainability.



DUAL-CERTIFIED INHERENT RANGE

When your job exposes you to extreme heat, fire, or the risk of explosions, you need flame-resistant workwear you can trust. Bisley® AR/FR workwear is dual-certified to NFPA 70E (ASTM F1506) and NFPA 2112-2023 standards and is manufactured from an AR/FR inherent fabric, meaning that its protective properties won't wash out or fade over time, for protection that's built to last.



LIGHTWEIGHT VENTED RANGE

Wearing PPE that lacks breathability can reduce productivity and lead to injury in high temperature environments. Our lightweight vented workwear meets ANSI 107 standards and doesn't compromise on comfort. Featuring strategically placed ventilation under the arms and across the back, these garments promote airflow in critical heat-stress areas. Now, workers can stay cool, comfortable and protected all day long.

APPLICATIONS



MINING



OIL AND GAS



PETROCHEMICAL



UTILITIES



CONSTRUCTION



DUAL-CERTIFIED AR/FR INHERENT WORK SHIRT H-TAPED WITH NAVY BOTTOM



385MFRHS
Men's



385WFRHS
Women's



385MFRHS Men's

385WFRHS Women's

- Ideal for mining, petrochemical, oil & gas, utilities and welding professionals
- ARC rating PPE 2 and dual NFPA certifications 70E and 2112 ensure reliable defense against arc flash, flash fire and heat-related hazards
- Durable but lightweight, 5.9oz AR/FR inherent ripstop fabric resists wear and tear, reinforced with high-tenacity Aramid thread to endure high-stress, high-temperature conditions
- FR melamine buttons and closures provide added flame resistance
- 1% Antistatic fabric reduces electrostatic discharge (ESD) risks
- 2-inch silver FR reflective H-tape ensures maximum visibility in low-light or high-risk environments
- Navy bottom conceals dirt maintaining a professional appearance
- Secure chest pockets with snap closures and mic tabs on shoulders for easy access to tools or essentials
- A two-piece structured collar adds style while maintaining form
- DEKO-TEX® Standard 100 ensures the fabric is free from harmful substances, prioritizing safety and environmental responsibility

STYLE NUMBER	COLOR	FIT	FEATURE	ANSI 107 TYPE/CLASS	FABRIC	ARC RATING	PPERATING	REFLECTIVE	CLOSURE	INDUSTRIAL LAUNDERABLE	SIZES
385MFRHS-YN	Hi-Vis Yellow	Men's	Dual-Certified: NFPA 70E (ASTM F1506), NFPA 2112-2023	Type R, Class 2	Inherent FR, 1% Antistatic	ATPV 8.9 cal/cm ²	2	2" Silver FR Tape	Button-Down	Yes	S-6XL
385WFRHS-YN	Hi-Vis Yellow	Women's	Dual-Certified: NFPA 70E (ASTM F1506), NFPA 2112-2023	Type R, Class 2	Inherent FR, 1% Antistatic	ATPV 8.9 cal/cm ²	2	2" Silver FR Tape	Button-Down	Yes	S-4XL
385MFRHS-ON	Orange	Men's	Dual-Certified: NFPA 70E (ASTM F1506), NFPA 2112-2023	n/a	Inherent FR, 1% Antistatic	ATPV 9.0 cal/cm ²	2	2" Silver FR Tape	Button-Down	Yes	S-6XL
385WFRHS-ON	Orange	Women's	Dual-Certified: NFPA 70E (ASTM F1506), NFPA 2112-2023	n/a	Inherent FR, 1% Antistatic	ATPV 9.0 cal/cm ²	2	2" Silver FR Tape	Button-Down	Yes	S-4XL



*ANSI R2 in Hi-Vis Yellow Only



DUAL-CERTIFIED AR/FR INHERENT CARGO PANTS TAPED BELOW KNEES



385MFRCS
Men's



385WFRCS
Women's



385MFRCS Men's **385WFRCS** Women's

- Ideal for mining, petrochemical, oil & gas, utilities and welding professionals
- ARC rating PPE 2 and dual NFPA certifications 70E and 2112 ensure reliable defense against arc flash, flash fire and heat-related hazards
- Durable but lightweight, 6oz AR/FR inherent ripstop fabric resists wear and tear, reinforced with high-tenacity Aramid thread to endure high-stress, high-temperature conditions
- FR melamine buttons and closures provide added flame resistance
- 2% Antistatic fabric reduces electrostatic discharge (ESD) risks
- 2-inch silver FR reflective tape below knees ensures maximum visibility in low-light or high-risk environments
- Front waistband button with curved design prevents gaping at the back for a secure, comfortable fit
- Wide beltloops accommodate heavy-duty belts for added utility
- Multiple pockets including 2 cargo pockets on sides, 2 rear hip pockets and 2 front pockets provide ample storage for tools and essentials
- OEKO-TEX® Standard 100 ensures the fabric is free from harmful substances, prioritizing safety and environmental responsibility

STYLE NUMBER	COLOR	FIT	FEATURE	ANSI 107	FABRIC	ARC RATING	PPE RATING	REFLECTIVE	CLOSURE	INDUSTRIAL LAUNDERABLE	SIZES
385MFRCS	Navy	Men's	Dual-Certified: NFPA 70E (ASTM F1506), NFPA 2112-2023	n/a	Inherent FR, 2% Antistatic	ATPV 9.0 cal/cm ²	2	2" Silver FR Tape	Zipper	Yes	30-50W x 30-32L
385WFRCS	Navy	Women's	Dual-Certified: NFPA 70E (ASTM F1506), NFPA 2112-2023	n/a	Inherent FR, 2% Antistatic	ATPV 9.0 cal/cm ²	2	2" Silver FR Tape	Zipper	Yes	4 - 20 (R)





DUAL-CERTIFIED AR/FR INHERENT COVERALL H-TAPED WITH NAVY BOTTOM



385MFRHC
Men's



385WFRHC
Women's



385MFRHC Men's 385WFRHC Women's

- Ideal for mining, petrochemical, oil & gas, utilities and welding professionals
- ARC rating PPE 2 and dual NFPA certifications 70E and 2112 ensure reliable defense against arc flash, flash fire and heat-related hazards
- Durable but lightweight, 6.0oz AR/FR inherent ripstop fabric resists wear and tear, reinforced with high-tenacity Aramid thread to endure high-stress, high-temperature conditions
- FR melamine buttons and closures provide added flame resistance
- 1% Antistatic fabric reduces electrostatic discharge (ESD) risks
- 2-inch silver FR reflective tape below knees ensures maximum visibility in low-light or high-risk environments
- Two-tone with navy bottom conceals dirt maintaining a professional appearance
- 8 multi-functional pockets including side access and mic tabs on shoulders for easy access to tools or essentials
- Two-button adjustable sleeve cuffs deliver a secure and tailored fit
- A two-piece structured collar adds style while maintaining form
- OEKO-TEX® Standard 100 ensures the fabric is free from harmful substances, prioritizing safety and environmental responsibility

STYLE NUMBER	COLOR	FIT	FEATURE	ANSI 107 TYPE/CLASS	FABRIC	ARC RATING	PPE RATING	REFLECTIVE	CLOSURE	INDUSTRIAL LAUNDERABLE	SIZES
385MFRHC-YN	Hi-Vis Yellow	Men's	Dual-Certified: NFPA 70E (ASTM F1506), NFPA 2112-2023	Type R, Class 2	Inherent FR, 1% Antistatic	ATPV 8.9 cal/cm ²	2	2" Silver FR Tape	Zipper	Yes	S - 6XL
385WFRHC-YN	Hi-Vis Yellow	Women's	Dual-Certified: NFPA 70E (ASTM F1506), NFPA 2112-2023	Type R, Class 2	Inherent FR, 1% Antistatic	ATPV 8.9 cal/cm ²	2	2" Silver FR Tape	Zipper	Yes	S - 4XL
385MFRHC-ON	Orange	Men's	Dual-Certified: NFPA 70E (ASTM F1506), NFPA 2112-2023	n/a	Inherent FR, 1% Antistatic	ATPV 9.0 cal/cm ²	2	2" Silver FR Tape	Zipper	Yes	S - 6XL
385WFRHC-ON	Orange	Women's	Dual-Certified: NFPA 70E (ASTM F1506), NFPA 2112-2023	n/a	Inherent FR, 1% Antistatic	ATPV 9.0 cal/cm ²	2	2" Silver FR Tape	Zipper	Yes	S - 4XL



*ANSI R2 in Hi-Vis Yellow Only




DUAL-CERTIFIED AR/FR INHERENT INSULATED PARKA H-TAPED WITH NAVY BOTTOM



385M8387H
Men's



DETACHABLE INSULATED HOOD



ONE INTERNAL POCKET



PEN POCKETS

385M8387H Men's

- Ideal for mining, petrochemical, oil & gas, utilities and welding professionals
- ARC rating PPE 4 and dual NFPA certifications 70E and 2112 ensure reliable defense against arc flash, flash fire and heat-related hazards
- Durable but lightweight, 7oz AR/FR inherent ripstop outer fabric resists wear and tear, while 14oz FR modacrylic/cotton insulation adds a layer of extra warmth in extreme conditions
- Reinforced with high-tenacity Aramid thread to endure high-stress, high-temperature conditions
- FR melamine buttons and closures provide added flame resistance
- 1% Antistatic fabric reduces electrostatic discharge (ESD) risks
- Detachable insulated hood allows for easy customization and provides added warmth
- Hidden rib cuffs inside the sleeves block out cold air and provide a snug, secure fit
- 2-inch silver FR reflective H-tape ensures maximum visibility in low-light or high-risk environments
- Navy bottom conceals dirt maintaining a professional appearance
- Multiple pockets including twin waist patch pockets with flap closures and 1 internal pocket offer secure and convenient storage for tools and personal items
- A two-piece structured collar adds style while maintaining form
- OEKO-TEX® Standard 100 ensures the fabric is free from harmful substances, prioritizing safety and environmental responsibility

STYLE NUMBER	COLOR	FIT	FEATURE	ANSI 107	FABRIC	ARC RATING	PPE RATING	REFLECTIVE	CLOSURE	INDUSTRIAL LAUNDERABLE	SIZES
385M8387H-YN	Hi-Vis Yellow	Men's	Dual-Certified: NFPA 70E (ASTM F1506), NFPA 2112-2023	Type R, Class 3	Outer - 7oz Inherent FR, 1% Antistatic // Insulation - 14oz FR Modacrylic, Quilted to Cotton	ATPV 40.0 cal/cm ²	4	2" Silver FR Tape	Two-Way Brass Zipper	Yes	S - 5XL





Lightweight Vented Industrial Workwear



LIGHTWEIGHT VENTED INDUSTRIAL WORK SHIRT

H-TAPED WITH NAVY BOTTOM



312M6367H
Men's



312W6367H
Women's



VENTED



312M6367H Men's

312W6367H Women's

- Ideal for mining crews, oil & gas workers and construction
- Industrial wash durable fabric with a 65% polyester and 35% cotton blend for reliable performance
- Lightweight 4.5oz fabric actively wicks away moisture from the skin, helping you stay cool in hot conditions
- Ventilation under the arms and on the back promotes air circulation in high heat stress areas
- 2-inch silver reflective tape ensures maximum visibility in low-light conditions
- Navy bottom conceals dirt maintaining a professional appearance
- Secure chest pockets with touch tape closures and reinforced stitching, and mic tabs on shoulders for easy access to tools or essentials
- Two-button adjustable sleeve cuffs deliver a secure and tailored fit
- A two-piece structured collar adds style while maintaining form

STYLE NUMBER	COLOR	FIT	FEATURE	ANSI 107 TYPE/CLASS	FABRIC	SLEEVE	REFLECTIVE	CLOSURE	INDUSTRIAL LAUNDERABLE	SIZES
312M6367H-YN	Hi-Vis Yellow	Men's	Vented, with Permanent Moisture Wicking	Type R, Class 2	65% Polyester, 35% Cotton	Long	2" Silver	Button-Down	Yes	S-6XL
312W6367H-YN	Hi-Vis Yellow	Women's	Vented, with Permanent Moisture Wicking	Type R, Class 2	65% Polyester, 35% Cotton	Long	2" Silver	Button-Down	Yes	S-5XL
312M6367H-ON	Hi-Vis Orange	Men's	Vented, with Permanent Moisture Wicking	Type R, Class 2	65% Polyester, 35% Cotton	Long	2" Silver	Button-Down	Yes	S-6XL
312W6367H-ON	Hi-Vis Orange	Women's	Vented, with Permanent Moisture Wicking	Type R, Class 2	65% Polyester, 35% Cotton	Long	2" Silver	Button-Down	Yes	S-5XL





LIGHTWEIGHT INDUSTRIAL CARGO PANTS

TAPED BELOW KNEES



318M6368T
Men's



318W6368T
Women's



318M6368T Men's

318W6368T Women's

- Ideal for mining crews, oil & gas workers and construction
- Industrial wash durable fabric with a 65% polyester and 35% cotton blend for reliable performance
- Lightweight 7.2oz fabric actively wicks away moisture from the skin, helping you stay cool in hot conditions
- 2-inch silver reflective tape below knees ensures maximum visibility in low-light conditions
- Front waistband button with curved design prevents gaping at the back for a secure, comfortable fit
- Multiple pockets including 2 cargo pockets on sides, 2 rear hip pockets and 2 front pockets provide ample storage for tools and essentials
- Wide beltloops accommodate heavy-duty belts for added utility
- Durable, high-quality YKK zipper ensures long-lasting performance

STYLE NUMBER	COLOR	FIT	FEATURE	ANSI 107	FABRIC	WAIST	REFLECTIVE	CLOSURE	INDUSTRIAL LAUNDERABLE	SIZES
318M6368T	Navy	Men's	Permanent Moisture Wicking	n/a	65% Polyester, 35% Cotton	Contoured	2" Silver	Zipper	Yes	30-50W x 30-36L
318W6368T	Navy	Women's	Permanent Moisture Wicking	n/a	65% Polyester, 35% Cotton	Contoured	2" Silver	Zipper	Yes	4-20 (S/R/T)



LIGHTWEIGHT VENTED INDUSTRIAL COVERALL H-TAPED WITH NAVY BOTTOM



314M6369H
Men's



314W6369H
Women's



VENTED

ZIPPERED
WAIST



314M6369H Men's

314W6369H Women's

- Ideal for mining crews, oil & gas workers and construction
- Industrial wash durable fabric with a 65% polyester and 35% cotton blend for reliable performance
- Lightweight, 5.6oz upper and 7.2oz lower fabric actively wicks away moisture from the skin, helping you stay cool in hot conditions
- Ventilation under the arms and on the back promotes air circulation in high heat stress areas
- 2-inch silver reflective tape below knees ensures maximum visibility in low-light conditions
- Double layered reinforced knee for added durability
- Two-tone with navy bottom conceals dirt maintaining a professional appearance
- 8 multi-functional pockets including side access and mic tabs on shoulders for easy access to tools or essentials
- Two-button adjustable sleeve cuffs deliver a secure and tailored fit
- A two-piece structured collar adds style while maintaining form
- Centered YKK front zipper with hidden snap and a hidden 2-way YKK waist zipper, allowing for easy removal of the bottom back for versatile, adaptable wear

STYLE NUMBER	COLOR	FIT	FEATURE	ANSI 107 TYPE/CLASS	FABRIC	SLEEVE	REFLECTIVE	CLOSURE	INDUSTRIAL LAUNDEABLE	SIZES
314M6369H-YN	Hi-Vis Yellow	Men's	Vented, with Permanent Moisture Wicking	Type R, Class 2	65% Polyester, 35% Cotton	Long	2" Silver	Zipper	Yes	S - 6XL
314W6369H-YN	Hi-Vis Yellow	Women's	Vented, with Permanent Moisture Wicking	Type R, Class 2	65% Polyester, 35% Cotton	Long	2" Silver	Zipper	Yes	S - 5XL
314M6369H-ON	Hi-Vis Orange	Men's	Vented, with Permanent Moisture Wicking	Type R, Class 2	65% Polyester, 35% Cotton	Long	2" Silver	Zipper	Yes	S - 6XL
314W6369H-ON	Hi-Vis Orange	Women's	Vented, with Permanent Moisture Wicking	Type R, Class 2	65% Polyester, 35% Cotton	Long	2" Silver	Zipper	Yes	S - 5XL





PROTECTIVE INDUSTRIAL PRODUCTS, INC.

518-861-0133 | 800-262-5755

sales@pipusa.com | www.pipusa.com

