

G-Tek[®]
BY **PIP**

G-Tek[®]
BY **PIP**

16-361
PARADOX[®]
www.pipglobalsafety.com
XL/10
AC

ULTRA LIGHTWEIGHT HAND PROTECTION


wesco

PARADOX[®]
ENGINEERED YARN




CUT RESISTANCE WITHOUT THE BULK

Experience the perfect balance of protection and tactility with G-Tek® Paradox™ 21-gauge seamless knit gloves. Designed to feel like a second skin, these ultra-lightweight, breathable gloves deliver exceptional dexterity and superior flexibility without compromising on cut protection.


With ANSI/ISEA 105-2024 A4 to A7 cut resistant options and proven industry coatings, including polyurethane, foam nitrile and NEW PosiGrip Max™, workers can confidently choose the best glove to tackle any task with ease.

HIGHEST DEXTERITY!



**21
GAUGE**
PER 1 INCH

**TIGHT WEAVE
FOR DEXTEROUS
PROTECTIVE
COVERAGE**



**13
GAUGE**
PER 1 INCH

**LOOSER, THICKER
WEAVE WITH GAPS
IN PROTECTIVE
COVERAGE**





POLYURETHANE COATING

- 
Enhanced Tactility
 Conforms closely to the glove liner, providing superior touch sensitivity for precise handling of parts
- 
Durable Protection
 Ultra-thin coating maintains excellent abrasion resistance without sacrificing flexibility
- 
Cost Effective
 Delivers high performance at a great value

DRY GRIP



RESIDENTIAL ELECTRICAL



PICKING & PACKING



HVAC



ASSEMBLY



PAPER & PULP MANUFACTURING



16-541
XXS-3XL

- Lightweight 21G PolyKor® shell offers dexterity, tactile sensitivity, and cut resistance
- Touchscreen compatible for convenience and to avoid glove removal
- Reinforced thumb crotch enhances durability and protection in high wear areas
- Washable/reusable

ANSI/ISEA 105



TOUCHSCREEN



16-541HV
XXS-3XL

- Lightweight 21G PolyKor® shell offers dexterity, tactile sensitivity, and cut resistance
- Touchscreen compatible for convenience and to avoid glove removal
- Reinforced thumb crotch enhances durability and protection in high wear areas
- Hi-vis shell color enhances visibility and hand/eye acuity on the job
- Washable/reusable

ANSI/ISEA 105



TOUCHSCREEN



HI-VIS

STYLE NUMBER	ANSI/ISEA 105 CUT	ANSI/ISEA 105 ABRASION	ANSI/ISEA 105 PUNCTURE	COATING	SILICONE FREE	LATEX FREE	REINFORCED	OEKO-TEX® STANDARD 100	OEKO-TEX® MADE IN GREEN	PROP 65
16-541	A4	3	2	Polyurethane	No	No	Yes	No	No	⚠️ C
16-541HV	A4	3	2	Polyurethane	No	No	Yes	No	No	⚠️ C

⚠️ = ⚠️ WARNING: Cancer - www.P65Warnings.ca.gov

FOAM NITRILE COATING



Superior Protection

Offers excellent flexibility while resisting punctures, tears and abrasions



Breathable Comfort

Porous construction enhances airflow, keeping hands cooler during extended wear



Enhanced Grip

Open cell structure disperses fluids and light oils on contact, maintaining a secure grip in challenging conditions

DRY OR SLIGHTLY OILY GRIP



OPEN CELL STRUCTURE
DISPERSES FLUIDS
AND LIGHT OILS



MRO



AEROSPACE &
DEFENSE



METAL
STAMPING



GLASS
MANUFACTURING



AUTOMOTIVE
MANUFACTURING



16-351
XXS-3XL

- Lightweight 21G PolyKor® shell offers dexterity, sensitivity, and cut resistance
- Touchscreen compatible for convenience and to avoid glove removal
- Reinforced thumb crotch boosts durability and protection in high wear areas
- Latex-free to avoid allergic skin reactions

ANSI/ISEA 105



TOUCHSCREEN



16-351HV
XXS-3XL

- Lightweight 21G PolyKor® shell offers dexterity, sensitivity, and cut resistance
- Touchscreen compatible for convenience and to avoid glove removal
- Reinforced thumb crotch boosts durability and protection in high wear areas
- Latex-free to avoid allergic skin reactions

ANSI/ISEA 105



TOUCHSCREEN



HI-VIS



16-361
XXS-3XL

- Lightweight 21G PolyKor® shell offers dexterity, sensitivity, and cut resistance
- Touchscreen compatible for convenience and to avoid glove removal
- Reinforced thumb crotch boosts durability and protection in high wear areas
- Latex-free to avoid allergic skin reactions
- Silicone free for smudge free handling
- Made with recycled yarns, meeting Oeko-Tex® Made in Green standards
- Oeko-Tex® 100 certified, free from heavy metals, formaldehyde, pesticides, and banned dyes

ANSI/ISEA 105



TOUCHSCREEN



MADE IN GREEN



STANDARD 100



16-371
XXS-3XL

- Lightweight 21G PolyKor® shell offers dexterity, sensitivity, and cut resistance
- Touchscreen compatible for convenience and to avoid glove removal
- Reinforced thumb crotch boosts durability and protection in high wear areas
- Latex-free to avoid allergic skin reactions
- Silicone free for smudge free handling
- Made with recycled yarns, meeting Oeko-Tex® Made in Green standards
- Oeko-Tex® 100 certified, free from heavy metals, formaldehyde, pesticides, and banned dye

ANSI/ISEA 105



TOUCHSCREEN



MADE IN GREEN



STANDARD 100

STYLE NUMBER	ANSI/ISEA 105 CUT	ANSI/ISEA 105 ABRASION	ANSI/ISEA 105 PUNCTURE	COATING	SILICONE FREE	LATEX FREE	REINFORCED	Oeko-TEX® STANDARD 100	Oeko-TEX® MADE IN GREEN
16-351	A5	4	3	Foam Nitrile	No	Yes	Yes	No	No
16-351HV	A5	4	3	Foam Nitrile	Yes	Yes	Yes	No	No
16-361	A6	4	2	Foam Nitrile	Yes	Yes	Yes	Yes	Yes
16-371	A7	3	2	Foam Nitrile	Yes	Yes	Yes	Yes	Yes

POSIGRIP MAX™ COATING



Effortless Grip

Requires 35% less gripping force on dry and oily surfaces compared to foam nitrile, reducing hand fatigue



Superior Oil Protection

Near zero oil penetration to keep hands dry and protected, even during prolonged exposure



Precise Handling

Delivers the same high level of tactility as polyurethane for confident control of small parts

DRY OR VERY OILY GRIP



CNC
OPERATION



STONE
CUTTING



AUTOMOTIVE
MAINTENANCE



MACHINERY
MANUFACTURING



OIL REFINERY



16-861

XXS-3XL

- Lightweight 21G PolyKor® shell offers dexterity, sensitivity, and cut resistance
- Touchscreen compatible for convenience and to avoid glove removal
- Reinforced thumb crotch boosts durability and protection in high wear areas
- Latex-free to avoid allergic skin reactions
- Oeko-Tex® 100 certified, free from heavy metals, formaldehyde, pesticides, and banned dyes

ANSI/ISEA 105



TOUCHSCREEN



STANDARD 100



16-871

XXS-3XL

- Lightweight 21G PolyKor® shell offers dexterity, sensitivity, and cut resistance
- Touchscreen compatible for convenience and to avoid glove removal
- Reinforced thumb crotch boosts durability and protection in high wear areas
- Knit wrist keeps out dirt and debris
- Latex-free to avoid allergic skin reactions
- Oeko-Tex® 100 certified, free from heavy metals, formaldehyde, pesticides, and banned dyes

ANSI/ISEA 105




TOUCHSCREEN




STANDARD 100

STYLE NUMBER	ANSI/ISEA 105 CUT	ANSI/ISEA 105 ABRASION	ANSI/ISEA 105 PUNCTURE	COATING	SILICONE FREE	LATEX FREE	REINFORCED	Oeko-TEX® STANDARD 100	Oeko-TEX® MADE IN GREEN	PROP 65
16-861	A6	4	2	PosiGrip MAX™	No	Yes	Yes	Yes	No	⚠️ C
16-871	A7	3	3	PosiGrip MAX™	No	Yes	Yes	Yes	No	⚠️ C

⚠️ = ⚠️ WARNING: Cancer - www.P65Warnings.ca.gov



For our complete line of safety products
visit www.pipusa.com



SCAN HERE
to learn more
about this collection



PROTECTIVE INDUSTRIAL PRODUCTS, INC.
518-861-0133 | 800-262-5755
sales@pipusa.com | www.pipusa.com

