

JACKSON®
SAFETY

MAXVIEW



EXTENDED COVERAGE

BOLD PROTECTION. BOLD STYLE.

Jackson Maxview+ Safety Glasses deliver top protection and style, with maximum eye coverage and a sleek design for work and beyond. Featuring high-impact polycarbonate lenses with 99.9% UV protection, they meet strict safety standards like ANSI Z87.1-2020. Comfortable and durable, they're built for tough jobs yet stylish for everyday use.

ANSI Z87+

IMPACT RATING

CLEAR AF

ANTI-FOG

99% UV

UVA, UVB, UVC

DIAMOND CUT

ANTI-SCRATCH

BALLISTIC RATED

US MIL-PRF-31013



GREEN MIRROR | SMOKE | AMBER | GOLD

EXTENDED COVER EDGE



COMFORTABLY SECURE

• High-Grip TPU Temples •

FULL WRAP DESIGN

• Maximum coverage area •

BUILT TO WEAR ALL-DAY

• Contoured Nosepiece •

PICK YOUR STYLE

• Frame and lens variety •

PRODUCT NO.	FRAME	LENS
60000	BLACK	CLEAR, ANTI-FOG
60001	BLACK	SHADE 5 IR
60002	BLACK	AMBER, ANTI-FOG
60003	BLACK	SMOKE, ANTI-FOG
60004	WHITE	SMOKE, ANTI-FOG
60005	RED	SMOKE, ANTI-FOG
60006	BLACK	GREEN MIRROR
60007	WHITE	GREEN MIRROR
60008	RED	GREEN MIRROR
60009	BLACK	GOLD MIRROR
60010	WHITE	GOLD MIRROR
60011	RED	GOLD MIRROR