



JACKSON[®]
SAFETY

EXCLUSIVE! **F4XP PREMIUM**
MODULAR FACE SHIELD SYSTEM



F4XP Incorporates THE WORLD'S GREATEST Ratcheting Headgear System—Period!



Our patented Jackson Safety® **370 Speed Dial™** offers the fastest, easiest, and most efficient ratcheting headgear system in the industry today!


The 370 Speed Dial™ incorporates two unique designs—an oversized ratcheting adjuster knob, and a patented “quick-fit” rear swivel headband.

Together, these two features combine to achieve a perfect fit every time, increasing safety, productivity and satisfaction.

Try any of our industry-leading Jackson Safety® products that incorporate our famous 370 Speed Dial™ and experience the difference yourself!




UNPARALLELED COMFORT • FIT • SATISFACTION



F4XP IN FOOD PRODUCTION

Face shields are a critical component for maintaining cleanliness in food production facilities especially where there is high contact with consumable products. The F4XP crown and headgear combined with our industry leading selection of windows provide valuable protection against droplets or particles that could harm food as it moves through various phases of packaging.



F4XP IN MEDICAL & LABORATORY

When working in a medical or laboratory environment, hazards such as chemical, biological and physical threats can be prevalent. The F4XP modular face shield system is designed to be used with protective eyewear, goggles and respirators so workers can do their job safely and effectively.

A Face Shield Crown and Headgear Like No Other!

Oversized crown built with premium high impact rated material for maximum protection

Designed to offer maximum protection, ease-of-use, and extreme comfort and fit



For use with all universal pin pattern windows including over 40 Jackson models

Exclusive quick-change install and removal system ensures fast and efficient window changes



Speed Dial 370™ headgear offers the fastest, easiest, and most efficient ratcheting headgear system in the industry



Shown with model **28766** propionate window shape H



Shown with model **29062** polycarbonate window shape T



Shown with model **29096** polycarbonate window shape E





Shown with model **29104** PETG window shape E



Shown with model **29106** polycarbonate window shape D

WHAT IS THE UNIVERSAL PIN PATTERN WINDOW MOUNTING SYSTEM?

The Jackson Safety® F4XP adopts a window mounting system that incorporates what is known as a universal pin pattern, the most popular hole pattern in the world. This allows use with all 45 of Jackson's long established windows to ensure that you always have the best solution for your application.



F4XP IN INDUSTRIAL MRO

When working in an industrial environment, the correct face protection can be an all-day necessity. Flying debris, airborne particles and other hazards can be a constant threat. The F4XP Modular Face Shield system has what you need to keep you comfortable while working safe.



Choose the Protection You Need.


- Used in conjunction with protective eyewear, Jackson Safety® face shields provide a high degree of on-the-job protection for heat applications as well as grinding, flying debris, splash protection, and more
- All Jackson Safety® face shields meet **ANSI Z87.1** Standards when used with any Jackson Safety® headgear (except for #28765)
- Universal bracket pin pattern is designed to accommodate most universal window brands including Kedman, Crews, Wilson, North, Jackson, and Sellstrom

F60	Wire Face Shields
F50	Polycarbonate Special Face Shields
F40	Propionate Face Shields
F30	Acetate Face Shields
F20	Polycarbonate Face Shields
F10	PETG Face Shields

MATERIAL TYPES		LENS TINTS
PETG	• A low-cost, recyclable option, ideal for general debris and splash protection	Clear Allows for maximum visible-light transmission.
Polycarbonate	• Premium impact protection • Good performance against heat • Excellent cold flexibility • Excellent clarity	IRUV Worn for applications and in environments where others are performing welding tasks such as torch brazing, torch soldering, gas welding, and oxygen cutting. Available in Shades 3.0 and 5.0.
Acetate	• Robust combination of weight and strength • Excellent cold flexibility • Scratch and chemical resistant • Optimum clarity	SPECIAL TINTS Enhances vision and reduces glare by blocking light transmission. Available in light, medium, and dark green tints, as well as aluminum, copper, and gold coated to deflect heat in high-heat applications.
Propionate	• Lightweight and chemical resistant	WARNING: APPLICATIONS & SAFETY <i>Face shields do not provide unlimited eye and face protection—primary eye protection (safety eyewear or goggles) must be worn.</i>
Wire Mesh	• Wear with face shield to dissipate heat • Ideal for flying-debris applications • Air flow for comfort	

Recommended Applications	F10 PETG	F30 Acetate & F40 Propionate	F20 Polycarbonate & F50 Polycarbonate Special	F60 Wire Mesh
	GOOD	BETTER	BEST	
Light industrial manufacturing	●	●	●	
Cutting or grinding metal			● (IRUV only)	
Cutting wood			●	●
Splash (general)	●	●	●	
Impact		●	●	
High-heat applications			●	●
Landscaping	●	●	●	●
Food processing	●	●	●	
Scratch resistance		●		
High impact			●	

F4XP Can be Used with Over 45 Jackson Windows





14260 (front)



14260 (back)

F4XP Premium Crown and 370 Speed Dial™ Ratcheting Headgear

- Specially designed to offer maximum protection, ease of use and unsurpassed comfort and fit
- Oversized crown is manufactured using premium high rated materials for optimum safety
- Built with an exclusive quick removal mounting system, ensuring fast and easy window changes
- Designed to mount all universal pattern face shield windows including the full range of Jackson Safety® windows (F10, F20, F30, F40 and F50) making it one of the most advanced and versatile face shield programs in the world!
- Comes standard with a soft and extra-absorbent replaceable sweatband for added comfort
- All models meet or exceed **ANSI Z81.1+** high impact standards
- Model 14260 is **CSA certified to CAN/CSA Z94.3** standards when used in conjunction with windows 29087, 29080, 29106, and 30706



PRODUCT NO.	Crown	Suspension	Window	Mounting Pattern	Case Qty.
14260	Black	370 Speed Dial Ratcheting Headgear	None	Universal Bracket Pin Pattern	12

F4XP Replacement Parts and Accessories

PRODUCT NO.	Description	Fits Models	Case Qty.
20695	370 Speed Dial™ Ratcheting Headgear	14260	12
32187	Replacement Washable Sweatband-2/pack	14260, 14262	24 packs
38424	HHIS Face Shield Hard Hat Adaptor (option)	14260, 14262	6

Oversized crown built with premium high impact rated material for maximum protection

For use with all universal pin pattern windows including over 30 Jackson models

Designed to offer maximum protection, ease-of-use, and extreme comfort and fit

Choose from over 45 Jackson Universal Pin Patterned windows



Exclusive quick-change install and removal system ensures fast and efficient window changes

Speed Dial 370™ headgear offers the fastest, easiest, and most efficient ratcheting headgear system in the industry



F10 PETG Face Shields

Meets ANSI Z87.1 Standards								
PRODUCT NO.	Old Code	Shade	Dimensions (L" x W" x T")	Case Count	Shape	Bound	Compatible with Hard Hat Interchange System	MADE IN USA
28765*	3005392	Clear	6" x 15.5" x .040"	36	N	Unbound		
28764**	NEW!	Clear AF	8" x 15.5" x .035"	96	N	Unbound		
29107	NEW!	Clear AF	8" x 15.5" x .035"	96	E	Unbound		
29104	3005399	Clear	8" x 15.5" x .040"	100	E	Unbound		
29101	3005382	Medium Green	8" x 15.5" x .040"	36	E	Unbound		
28962	3029190	Clear	9" x 15.5" x .040"	50	D	Bound		
28963	3029191	Clear	9" x 15.5" x .040"	50	D	Unbound		

*Model 28765 does not meet ANSI Z87.1 standards due to limited coverage

**Please note: 28764 and 28765 windows are designed specifically to fit on Jackson bump caps with face shield attachment.


For more information about the Hard Hat Interchange System, refer to page 105.

F20 Polycarbonate Face Shields

All models meet or exceed ANSI Z87.1+ high impact standards. Models 29087, 29106, and 30706 are CSA certified to CAN/CSA Z94.3 standards when combined with Jackson models 14260 F4XP headgear, or when combined with an SC-6 hard hat and 38425 HHIS hard hat adaptor.

PRODUCT NO.	Old Code	Shade	Dimensions (L" x W" x T")	Case Count	Shape	Bound	Compatible with Hard Hat Interchange System	MADE IN USA
30706*	3005372	Clear	8" x 15.5" x .040"	36	E	Unbound		
29097*	3005373	Medium Green	8" x 15.5" x .040"	36	E	Unbound		
29100*	3005379	Dark Green	8" x 15.5" x .040"	36	E	Unbound		
29096*	3005371	Clear	8" x 15.5" x .040"	25	E	Bound		
29099*	3005378	Clear	8" x 15.5" x .040"	36	F	Unbound		
▲ 29062*	3000449	Clear	8" x 15.5" x .040"	12	T	Unbound		
29087*	3002832	Clear	8" x 15.5" x .060" (Molded)	12	B	Unbound		
29109*	3009492	Clear	8" x 15.5" x .060"	12	E	Unbound		
14132*	3005375	Clear	8" x 15.5" x .060"	36 (bulk)	E	Unbound		
29106*	NEW!	Clear	9" x 15.5" x .040"	96	D	Bound		
29057*	NEW!	Clear	9" x 15.5" x .060" (Molded)	12	R	Unbound		
29103*	3005385	Clear	9" x 19.25" x .060"	36	L	Unbound		
29098	3005377	Clear	10" x 20" x .040"	36	K	Unbound		

F4XP Can be Used with Over 45 Jackson Windows



F30 Acetate Face Shields

Meets ANSI Z87.1 Standards

CODE	Old Code	Shade	Dimensions (L" x W" x T")	Case Count	Shape	Bound	Compatible with Hard Hat Interchange System	MADE IN USA
29078 ¹	3002806	Clear	8" x 12" x .040"	24	C	Bound	●	●
29052	3000122	Clear	8" x 15.5" x .040"	24	E	Bound	●	●
29053	3000123	Medium Green	8" x 15.5" x .040"	24	D	Bound	●	●
29054	3000125	Clear	8" x 15.5" x .060"	24	E	Bound	●	●
▲ 29060	3000411	Clear	9" x 15" x .040"	24	P	Unbound	●	●
29092	NEW!	Clear	9" x 15.5" x .040"	35	D	Unbound	●	●
29079	3002808	Clear	9" x 15.5" x .040"	24	D	Bound	●	●
29091	3002848	Clear	9" x 15.5" x .040"	50 (Bulk)	D	Bound	●	●
29082	3002817	Light Green	9" x 15.5" x .040"	12	D	Bound	●	●
29090	3002845	Dark Green	9" x 15.5" x .040"	50	D	Bound	●	●
29083	3002826	Clear	9" x 19.5" x .040"	12	I	Unbound	●	●
29056	3000136	Clear	9" x 19.5" x .040"	24	O	Unbound	●	●
▲ 14445	3000146	Clear	9" x 20" x .040"	12	Q	Unbound	●	●

▲ Chin Cup

¹Face Shield 29078 does not meet ANSI Z87.1 splash protection requirements when used with headgear 29076

F40 Propionate Face Shields—Molded

Meets ANSI Z87.1 Standards


CODE	Old Code	Shade	Dimensions (L" x W" x T")	Case Count	Shape	Bound	Compatible with Hard Hat Interchange System	MADE IN USA
29084	3002830	Clear	9" x 15.5" x .060"	12	G	Unbound	●	●
29089	3002843	Clear	9" x 15.5" x .060"	50 (Bulk)	G	Unbound	●	●
29086	3002831	Dark Green	9" x 15.5" x .060"	12	G	Unbound	●	●
28766	3000175	Clear	10" x 20" x .060"	1	H	Unbound	●	●

F50 Polycarbonate Special Face Shields—Molded—Premium Clarity and Impact Protection

All models meet or exceed ANSI Z87.1+ high impact standards. Model 29080 is CSA certified to CAN/CSA Z94.3 standards when combined with Jackson models 14260 F4XP headgear, or when combined with an SC-6 hard hat and 38425 HHIS hard hat adaptor.

CODE	Old Code	Shade	Dimensions (L" x W" x T")	Case Count	Shape	Bound	Compatible with Hard Hat Interchange System
26262*	3002813	IRUV 3.0	8" x 15.5" x .060"	12	B	Unbound	●
29080*	3002810	IRUV 5.0	8" x 15.5" x .060"	12	B	Unbound	●
28633*	3002838	IRUV 5.0	8" x 15.5" x .060"	50 (Bulk)	B	Unbound	●
29058	NEW!	IRUV 3.0	9" x 15.5" x .060"	12	R	Unbound	●
29059	NEW!	IRUV 5.0	9" x 15.5" x .060"	12	R	Unbound	●
28634*	3000162	Gold	10" x 20" x .060"	1	H	Unbound	●
29075	NEW!	Alum	10" x 20" x .060"	12	R	Unbound	●
29085	NEW!	Copper	10" x 20" x .060"	12	R	Unbound	●
29088	NEW!	Gold	10" x 20" x .060"	12	R	Unbound	●

Aluminum—Basic heat deflection/protection, Copper—Medium-to-high heat deflection/protection, Gold—High heat deflection/protection







Our Family of U.S. Brands

JACKSON
SAFETY

sellstrom



K1TM
S E R I E S

 **duenorth**[®]



800.323.7402
orders.usa@surewerx.com
surewerx.com/usa

F4XP21

Be Smart. Be Safe. Be Sure.TM