tradeSELECT®

Contractor Focused

Readily Available

Reliable

Current

wesco

Always On.

At Current, inspiration flows both ways. In providing the lighting and controls solutions that help create beautiful, functional and safe environments, we're inspired by the people who live, work and play in those spaces.

Only Current can provide reliable performance, responsive service, and the uncompromising quality you expect from an industry leader every time, always.

Our Solutions

Indoor **Outdoor** **Controls** **Life Safety**

Express Shipping

In-Stock **Same Day Shipping** **Will Call**

Contractor Preferred Brands

Columbia LIGHTING · EXO · NX LIGHTING CONTROLS · COMPASS · DUAL LITE · prescolite

Current

tradeSELECT® by Current HLI Brands

We value our customers' confidence in our products. With tradeSELECT, we have selected our most popular, quality-driven lighting solutions to provide you with your everyday lighting needs.

tradeSELECT features products from our trusted brands - Columbia, Compass, Dual-Lite, EXO, Prescolite and NX Lighting Controls.

Contractor Focused

tradeSELECT offers contractors the right set of products—so all you have to do is select! Designed for the contractor in mind, we make it easy for you to purchase and install our products, making each job worry-free.

Readily Available

Our products are always in stock, ready to ship from our strategically located Distribution Centers. Meet tight deadlines with tradeSELECT products available through your preferred authorized distributor.

Reliable

The long history of innovation, performance, quality, and reliability at Current is something contractors can count on. tradeSELECT provides a selection of our most popular products with superior design, durable construction, and maintenance-free operation, giving you peace of mind.

Freight Allowance

Into-stock* orders equal or greater than $100 qualify for freight allowance.

*Same Sold-To/Ship-To address, not a project/job order

tradeSELECT® Markets Served

DATA CENTERS

In today's digital world, data centers rely on high-performance lighting to keep operations running smoothly. Bright, reliable illumination ensures safe movement and easy equipment maintenance. Our solutions are designed to fit the unique ceiling structures and hot- or cold-aisle containment systems found in modern data centers..

INDUSTRIAL

From factory floors to warehouse aisles, the right lighting makes all the difference. Our solutions help you work safer, smarter, and more efficiently—no matter the environment. Whether you're lighting up a general workspace or a tough industrial zone, reliable lighting keeps operations running smoothly and sustainably.

EDUCATION

Our full range of LED lighting helps create brighter, safer, and more energy-efficient schools and campuses. With the right mix of indoor and outdoor lighting, you can cut costs while enhancing the learning environment for students and staff alike.

STOCK Service Program

Current's strategically-placed Distribution Centers are stocked with inventory customized to meet each market's unique needs. We understand tight deadlines and immediate needs; we're ready to ship on-time and on-demand wherever and whenever you need us.

Express Shipping Available

We offer same-day shipping on orders placed by 11:00 am local time.

Need it now?

Check our Will Call Pick Up Program or expedite shipping options.

Trusted Certifications

BUY AMERICAN SOLUTIONS

Current has qualified our most popular product families with self-serve options for Buy American FAR §52.225-9 or Trade Agreements FAR §52.225-11 solutions.

Visit our Buy America(n) Solutions page for qualifying families and look for the logo on specification sheets of participating product families: currentlighting.com/resources/america-solutions

THE DESIGNLIGHTS CONSORTIUM® (DLC)

Our partnership with The DesignLights Consortium® (DLC) assure our products are designated to meet and exceed industry specifications.

Look in this guide to see which products comply!

offering with smooth even illumination. Shallow height is ideal fo
ng. Available with Switchable Lumen and CCT technology.

	UPC Code	Lbs. Each	Pallet QTY	DLC
)0/5000K),	840141432670	5.7	48	S-0BBXCH
)0/5000K),	840141412184	4.9	40	S-V0XH25

Visit designlights.org for more information.

Switchable Solutions

SWITCHABLE LUMINARIES

Look for these icons throughout the brochure.

FIELD ADJUSTMENTS FOR EVERY APPLICATION

Switchable luminaires offer field adjustability of lumen output, color temperature or both–lumen and CCT. This feature simplifies having multiple SKUs into 1! Reduce inventory on the shelf, reduce inventory costs and reduce stock outs with Switchable luminaires.



ORDER ONE SKU AND GET THE FEATURES OF MULTIPLE LUMEN AND CCT OPTIONS

Accounting for higher mounting heights or warmer color temperatures is as easy as moving the switch! Switches are easily accessible and clearly labeled for simple selection of settings.

Exits - 2 SKUs In 1

Compass CARG Exit shown

Compass CCRG Combination shown

These units are designed with both red and green LEDs to meet luminance requirements and supplied with both color faceplates. To toggle between colors simply move the jumper inside the fixture and snap on the correct color faceplate.

Floodlights - 10 SKUs In 1

This switchable floodlight with Red, Blue and White LEDs, provides ten different custom color illumination choices allowing a wide variety of landscape accent or medium area illumination. Simply toggle the color selection at the bottom of the fixture.

In-Person & Online Training

THE Institute

Customized curriculum delivered LIVE
in an interactive virtual classroom.

Current and our education team at The Institute offer an unprecedented opportunity to gain a cutting-edge lighting education in an environment that brings today's most relevant lighting solutions to life.



In-person classroom instruction available at our facilities:
Greenville, SC • Hendersonville, NC • Austin, TX • Plympton, MA

Online content available **24/7** at Current University.
Learn more at LED.com/education/the-institute

Tools for Growth

connect

Designed to maximize productivity, Connect is an online portal that integrates your business with Current across one easy-to-use platform. It packs a powerful set of tools and intuitive features to help you sell more effectively.

- View quotations, orders, invoices and packing lists
- Search inventory and compare product specifications
- Access configurations and pricing
- Create service requests and view updates

All with a sleek user interface designed to work with your needs. Log in to myconnect.currentlighting.com to register and get started today!

QUICK DESIGN LAYOUT TOOL

Look for the QD logo next to select fixtures' IES files, simply click on the logo and the application will launch in a separate window.



Current's LitePro QD (Quick Design) Layout Tool allows you to compute iso-contours and point by point illuminance for selected fixtures.

DesignSuite

Current Controls Design

DesignSuite is our comprehensive software solution designed to streamline the design and documentation process for NX lighting control systems. Whether you're working on a small or medium-sized project, our software can assist with complete documentation, system layout, design and quoting. Our expert design team is available to provide support and guidance throughout the entire process.



Retrofit Opportunities

The Compare in the Air program allows you to see the results of a lighting retrofit or renovation real–time in your facility with no risk! Grounded in serving customers' needs, Current understands there's no one size fits all solution, especially for unique applications, offering lighting and control solutions that span the full spectrum for new construction and retrofit projects.

4 EASY STEPS

STEP 1 – SELECT UP TO FOUR QUALIFYING PRODUCTS
STEP 2 – MARK THE ORDER "COMPARE IN THE AIR"
STEP 3 – RECEIVE A 90–DAY DATING TERMS ON YOUR ORDER
STEP 4 – INSTALL THE PRODUCTS AND SEE THE RESULTS

Whether you are completing a retrofit and upgrading inefficient systems, or starting from the beginning, we are here to help. Contact your Current representative today to get started!

$REBATE SEARCH



Get access to the latest data from over 3,000 utility programs across North America for tradeSELECT® products on the DesignLights Consortium® Qualified Product Listing with our Rebate Search Tool.

Where To Buy

Ready to Get Started?

Find our products from our authorized distributors

Visit tradeSELECT® online for more new products and other resources

Contents

Columbia

Indoor Commerical and Industrial

CBT – Back-Lit Troffer 16
CLT - Center Lens Troffer 17
CLH-LSCS – Switchable Linear High Bay 17
CRN2-LSCS – Wet Location High Bay 18
PELA – Linear High Bay 18
LCAT – Contemporary Architectural Troffer 19
LCAT-S – Contemporary Architectural Troffer – Shallow 19
CSL – Lensed Striplight 19
CVT – Linear Vaportite Luminaire 20
LXEM – Enclosed and Gasketed Luminaire 20
LXEN Narrow Enclosed and Gasketed Luminaire . 20
MPS – MultiPurpose Linear 21
CNW – Narrow Wrap 21
CWP – Wrap Luminaire 21

Compass

Emergency and Exit

CC Series 30
CEL Universal 30
CE Series 31
COR Series 31
CSWEU2LED 32
CU2 Series 32
CU2HL Series 32

Dual-Lite

Emergency and Exit

EV Series 37
EVC Series 37
EVE Series 38
EVO Series 38
EZ-2 Series 38
PG Series 39
PowerLED PLD+ Series 39

EXO

Outdoor

Poles and Accessories 50
SGC-F Sling Canopy 50
SGD Sling Dusk-to-Dawn 51
Sling Bollard 51
VBGL2 & VWGL2 Vaportites 52
LBUL Colt 52
Lightscaper® 53
Lightscaper® RGBW 53
Marshal LED Twin Head Motion Sensor Kit 53
Options and Accessories 54
Photocontrol 54
SGF Sling Flood Family Floodlights 55
LNC2 Wallpack 55
Prelude Wallpack 55
PRS Perimashield Wallpack 56
WGH Switchable Glass Refractor Wallpack 56
SG Sling Wallpack 57

NX Lighting Controls

Controls

Cables 65
CX Lighting Control Panels 65
Emergency Lighting Units 65
LightHAWK® Wall Switch Sensors 66
Wallbox Devices 67
NX Lighting Controls 68
NX Lighting Controls (continued) 69
OMNI® Ceiling Sensors 70
Power Packs and Controlled Relays 70
WASP Fixture Sensors 70

Prescolite

Downlights

LiteBox® Edge-Lit 74
LiteBox® Standard 75
LiteBox® Pro 76
Accessories 77
LiteFrame 2.0 78
LITEISTRY™ 79



Columbia LIGHTING

A recognized leader in providing innovation at value for commercial and industrial markets, leading with exceptional efficacy, optical performance and quality.

Panels & Troffers

CBT – Back-Lit Troffer

SWITCHABLE LUMEN & CCT

CBT back-lit LED lens troffer is an affordable tradeSELECT offering with smooth even illumination. Shallow height is ideal for tight plenum applications with recessed or surface mounting. Available with Switchable Lumen and CCT technology.

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
CBT14-A-LSCS-EDD 1'x4' Back-Lit Troffer, Switchable Lumen (2800/3400/4600 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 1 per carton	840141432670	5.7	48	S-0BBXCH
CBT22-A-LSCS-EDD 2'x2' Back-Lit Troffer, Switchable Lumen (2800/3400/4600 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 1 per carton	840141432687	5.6	48	S-6LZF85
CBT24-A-LSCS-EDD 2'x4' Back-Lit Troffer, Switchable Lumen (3400/4600/5800 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 1 per carton	840141432700	10.5	24	S-J8QJ2F
CBT14-B-LSCS-EDD 1'x4' Back-Lit Troffer, Switchable Lumen (2800/3400/4400 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-347V	840141435312	4.9	48	-
CBT22-B-LSCS-EDD34 2'x2' Back-Lit Troffer, Switchable Lumen (2800/3400/4400 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-347V	840141430324	4.9	48	S-DMXVQI
CBT24-B-LSCS-EDD34 2'x4' Back-Lit Troffer, Switchable Lumen (3300/4400/5500 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-347V	840141430331	9.4	24	S-EJO95G
CBT14-A-LSCS-EDD 1'x4' Back-Lit Troffer, Switchable Lumen (2800/3400/4600 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 1 per carton	840141432670	5.7	48	S-0BBXCH
CBT14-B-LSCS-EDD 1'x4' Back-Lit Troffer, Switchable Lumen (2800/3400/4400 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-347V	840141435312	4.9	48	-
CBT22-A-LSCS-EDD 2'x2' Back-Lit Troffer, Switchable Lumen (2800/3400/4600 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 1 per carton	840141432687	5.6	48	S-6LZF85
CBT22-B-LSCS-EDD34 2'x2' Back-Lit Troffer, Switchable Lumen (2800/3400/4400 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-347V	840141430324	4.9	48	S-DMXVQI
CBT24-A-LSCS-EDD 2'x4' Back-Lit Troffer, Switchable Lumen (3400/4600/5800 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 1 per carton	840141432700	10.5	24	S-J8QJ2F
CBT24-B-LSCS-EDD34 2'x4' Back-Lit Troffer, Switchable Lumen (3300/4400/5500 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-347V	840141430331	9.4	24	S-EJO95G

CLT - Center Lens Troffer

The CLT is a low profile center lens troffer with switchable lumens and CCT, designed to blend seamlessly into its environment

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
CLT22-LSCS-EDD 2X2 Center Lens Troffer, Switchable Lumen (3250/3750/5000 lumens), Switchable CCT (3500/4000/5000K), 0-10V dim-to-off driver, 120-347V	840141417356	6.4	40	S-MV0H76
CLT24-LSCS-EDD 2X4 Center Lens Troffer,Switchable Lumen (3750/5000/6000 lumens), Switchable CCT (3500/4000/5000K), 0-10V dim-to-off driver, 120-347V	840141417363	11.7	20	S-4JGZHF
CLT22-LSCS-EDD 2X2 Center Lens Troffer, Switchable Lumen (3250/3750/5000 lumens), Switchable CCT (3500/4000/5000K), 0-10V dim-to-off driver, 120-347V	840141417356	6.4	40	S-MV0H76
CLT24-LSCS-EDD 2X4 Center Lens Troffer,Switchable Lumen (3750/5000/6000 lumens), Switchable CCT (3500/4000/5000K), 0-10V dim-to-off driver, 120-347V	840141417363	11.7	20	S-4JGZHF

High Bay

CLH-LSCS – Switchable Linear High Bay

CLH is a linear highbay offering selectable lumens and CCT. Field installable sensors and accessories provide maximum flexibility to meet budget and project schedules.

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
CLH1-LSCS-EDU-MD Size 1 fixture, Lumen Switchable (15,000/18,000/24,000 lumens), CCT Switchable (4000/5000K), 94W/115W/158W, 120-277V, 0-10V dimming	840141415611	6	120	S-NHLODI
CLH2-LSCS-EDU-MD Size 2 fixture, Lumen Switchable (24,000/30,000/36,000 lumens), CCT Switchable (4000/5000K), 152W/197W/242W, 120-277V, 0-10V dimming	840141415642	10	100	S-GZ6L7N

CRN2-LSCS – Wet Location High Bay

CRN2-LSCS is an efficient wet location high bay tradeSELECT offering suitable for a variety of areas including warehouses, gyms covered outdoor areas, garden centers and mezzanines. Available with Switchable Lumen and CCT technology.

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
CRN2-1-LSCS-EDMV-SO-W Size 1 fixture, Wet Location Highbay, Lumen Switchable (16,000/19,000/22,000 lumens), CCT Switchable (4000/5000K), 100W/120W/150W, selectable optics, white finish, 120-347V, 0-10V dimming	840141436098	7.5		-
CRN2-1-LSCS-EDMV-SO-B Size 1 fixture, Wet Location Highbay, Lumen Switchable (16,000/19,000/22,000 lumens), CCT Switchable (4000/5000K), 100W/120W/150W, selectable optics, black finish, 120-347V, 0-10V dimming	840141436104	7.5		-
CRN2-2-LSCS-EDMV-SO-W Size 2 fixture, Wet Location Highbay, Lumen Switchable (25,000/30,000/36,000 lumens), CCT Switchable (4000/5000K), 150W/200W/240W, selectable optics, white finish, 120-347V, 0-10V dimming	840141436111	10.1		-
CRN2-2-LSCS-EDMV-SO-B Size 2 fixture, Wet Location Highbay, Lumen Switchable (25,000/30,000/36,000 lumens), CCT Switchable (4000/5000K), 150W/200W/240W, selectable optics, black finish, 120-347V, 0-10V dimming	840141436128	10.1		-

PELA – Linear High Bay

PELA is a highly configurable linear highbay with exceptional value.

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
PELA-840-L24-B-ED-U-ST-PI-NXWHM 80 CRI, 4000K, 24,000 lumens, NX Wireless Sensor, diffuse wide distribution polycarbonate lens, 0-10V dimming driver, 120-277V, white	840141433462	10	30	S-F7Q6C3
PELA-840-L30-B-ED-U-ST-PI-NXWHM 80 CRI, 4000K, 24,000 lumens, NX Wireless Sensor, diffuse wide distribution polycarbonate lens, 0-10V dimming driver, 120-277V, white	840141433530	10	30	S-R52KE7
PELA-840-L36-B-ED-U-ST-PI-NXWHM 80 CRI, 4000K, 36,000 lumens, NX Wireless Sensor, diffuse wide distribution polycarbonate lens, 0-10V dimming driver, 120-277V, white	840141432632	20	20	S-I9B738

LCAT – Contemporary Architectural Troffer

LCAT LED contemporary architectural troffer provides both design and value with an architectural appearance for classrooms, offices, retail and healthcare applications. Available with Switchable Lumen and CCT technology.

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
LCAT22-LSCS 2'x2', 80 CRI, Switchable Lumen (2750/3300/4400 lumens), Switchable CCT (3500/4000/5000K), curved frosted acrylic lens, 1-10V dimming 10%	840141423340	11.5	40	S-0TDGS1
LCAT24-LSCS 2'x4', 80 CRI, Switchable Lumen (4200/5200/6000 lumens), Switchable CCT (3500/4000/5000K), curved frosted acrylic lens, 1-10V dimming 10%	840141423364	18.3	20	S-AROF8M

LCAT-S – Contemporary Architectural Troffer – Shallow

LCAT-S is an aesthetically appealing, value driven center lens troffer with a shallow depth perfect for ceilings with tight plenum spaces. Available with Switchable Lumen and CCT technology.

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
LCAT14-S-LSCS 1'x4' Shallow Center Lens Troffer, Switchable Lumen (4200/5200/6000 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-277V	840141415574	9	56	S-SQUPL0
LCAT22-S-LSCS 2'x2' Shallow Center Lens Troffer, Switchable Lumen (4200/5200/6000 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-277V	840141415581	8.6	56	S-W63TOR
LCAT24-S-LSCS 2'x4' Shallow Center Lens Troffer, Switchable Lumen (2750/3300/4400 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-277V	840141415598	13.3	28	S-HU52AG

Vaportites & Strips

CSL – Lensed Striplight

CSL LED lens striplight tradeSELECT offering brings together an economical price and high performance. Available with Switchable Lumen and CCT technology.

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
CSL4-A-LSCS 4' LED Striplight, Switchable Lumen (4400/4850/5300 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-347V	840141413471	5	192	S-IY4L65
CSL8-A-LSCS 8' LED Striplight, Switchable Lumen (8000/8800/9600 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-347V	840141413488	9.8	168	S-4CEB93

CVT – Linear Vaportite Luminaire

CVT is a narrow body linear vapor tight offering Switchable lumen output and CCT technology

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
CVT4-LSCS-MV 4' Linear Vaportight, Switchable Lumen (5000/6000/7000) and Switchable CCT (3500/4000/5000 CCT) 120-347V	840141431420	5.5	90	S-DGRP21
CVT8-LSCS-MV 8' Linear Vaportight, Switchable Lumen (9000/10,000/12,000) and Switchable CCT (3500/4000/5000 CCT) 120-374V	840141431437	11	128	S-SAJ91X

LXEM – Enclosed and Gasketed Luminaire

LXEM is a multi-functional enclosed LED product which serves rugged to severe conditions as well as food service areas.

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
LXEM4-40HL-RFA-EDU 4', 80 CRI, 4000K, 6200 lumens, surface mount, ribbed frosted acrylic Lens, 0-10V dimming driver, 120-277V, 47W, 139 LPW, white	78531124700	10	45	S-FJMGDL
LXEM4-40ML-RFA-EDU 4', 80 CRI, 4000K, 5200 lumens, surface mount, ribbed frosted acrylic lens, 0-10V dimming driver, 120-277V, 42W, 123 LPW, white	78531123932	10	41	P00000VY9

LXEN Narrow Enclosed and Gasketed Luminaire

LXEN is a narrow body vapor tight, ideal for applications where space is limited.

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
LXEN4-40LW-RFA-EDU 4', 80 CRI, 4000K, 4250 lumens, surface mount, ribbed frosted acrylic lens, 0-10V dimming, 120-277V, 33W, 128 LPW, white	78531130800	7.3	99	PBQB8QWH

MPS – MultiPurpose Linear

MPS multipurpose linear is a versatile linear solution that will fit seamlessly into countless applications. With continuous illumination, integrated controls, multiple lens options and single or row mounting, MPS is adaptable to your environment.

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
MPS4-35ML-CW-EDU 4', 3500K, 4500 lumens, surface mount, wall mount or suspended, curved frosted acrylic wide distribution lens, 0-10V dimming, 120-277V, 32W, 140 LPW, white	78531138714	6.1	56	PKQ78077
MPS4-40ML-CW-EDU 4', 4000K, 4600 lumens, surface mount, wall mount or suspended, curved frosted acrylic wide distribution lens, 0-10V dimming, 120-277V, 32W, 141 LPW, white	78531138721	6.1	56	P04CB2S2

Wraps

CNW – Narrow Wrap

CNW attractive narrow wrap with decorative end caps and a polished look, suitable for many applications. A tradeSELECT offering is available, featuring a frosted acrylic lens and efficacy up to 112 lumens per watt. Available with Switchable Lumen and CCT technology.

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
CNW4-LSCS 4' Narrow Wrap, Switchable Lumen (3000/3500/4000 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-277V	840141402864	4.9	84	PLWHDY39EG48

CWP – Wrap Luminaire

CWP efficient 4' LED wrap style fixture that provides an economical tradeSELECT solution for exceptional light distribution in general areas.

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY	DLC
CWP4-A-LSCS 4' Linear Wrap, Switchable Lumen (4500/4950/5400 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-347V	840141413495	7.7	40	S-XOI4PS

Pallet quantity defaulted on Harrisburg RDC. Contact customer service for more information.

CRW – Round Wrap

SWITCHABLE LUMEN & CCT

The CRW is a versatile round wrap with decorative end caps. A tradeSELECT offering featuring Switchable Lumen and CCT technology, a frosted acrylic lens and efficacy up to 153 lumens per watt.

Catalog # Description	UPC Code	Lbs. Each	Pallet QTY*	DLC
CRW4-LSCS 4' Round Wrap, Switchable Lumen (3900/4800/5500 lumens), Switchable CCT (3500/4000/5000K), 0-10V dimming, 120-277V	840141400228	5	24	PB0QBKBD

WRAPS
PRODUCT SELECTION GUIDE

VALUE

		CNW			CWP			CRW		
FEATURES	**Length**	**2'**	4'	8'	2'	4'	8'	2'	4'	8'
		–	Yes	–	–	Yes	–	–	Yes	–
	Width	5.3"			9"			9.7"		
	Continuous Row	–			–			–		
	Lumens (maximum)	4095			5400			5880		
	Efficacy (maximum LPW)	123			138			153		
	Life Rating	54,000 hours @ L70			54,000 hours @ L70			54,000 hours @ L70		
	CRI	80+			80+			80+		
	CCT	3500K, 4000K, 5000K			3500K, 4000K, 5000K			3500K, 4000K, 5000K		
	SpectraSync™ Color Tuning Technology	–			–			–		
	Switchable Technology	Lumen & CCT			Lumen & CCT			Lumen & CCT		
	SpectraSAFE™ Integrated Surveillance	–			–			–		
	Lens	Frosted Acrylic			Frosted Acrylic			Frosted Acrylic		
	Dimming	0–10V Dimming to 10%			0–10V Dimming to 10%			0–10V Dimming to 10%		
	Emergency Battery Pack	–			–			–		
	DLC® DesignLights Consortium	Standard			Standard			Premium		
	Buy America(n) Solutions	–			–			–		
INTEGRATED CONTROLS	**Standalone Occupancy & Daylighting**	–			–			–		
	NX Standalone Occupancy & Daylighting	–			–			–		
	NX Networked Occupancy & Daylighting	–			–			–		
USES	**Applications**	Education, Office, Retail, Warehouse			Education, Healthcare, Office, Warehouse			Education, Healthcare, Office, Retail, Warehouse		

DLC® (DesignLights Consortium) Qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org

VAPOR TIGHT
PRODUCT SELECTION GUIDE

		VALUE	COMMERCIAL			
		CVT	LXEN	 LXEP	LXEM	LXEW
FEATURE#S	Features	+	++	++	++	++
	Sizes	4',8'	4'	2', 4', 8'	2', 4', 8'	4'
	Mounting Height	Up to 15'	Up to 10'	Up to 25'	Up to 25'	Up to 40'
	Width	–	4.5"	6.75"	6.75"	15"
	Lumens	5,000- 12,000	2,000- 4,200	2,900- 19,700	2,100- 22,400	11,000- 38,000
	Wattage	38- 90W	15W, 30W	33-204W	20-183W	90-329W
	Efficacy (Max)	Up to 148	130-150	87-116	99-147	105-136
	Voltage	120-347V	120-277V	120-277V, 347V, 480V	120-277V, 347V, 480V	120-277V, 347V, 480V
	CRI	80	80	80	80	80
	CCT	3500K, 4000K, 5000K	3000K, 3500K, 4000K, 5000K	3000K, 3500K, 4000K, 5000K	3000K, 3500K, 4000K, 5000K	3000K, 3500K, 4000K, 5000K
	Switchable Technology	Switchable Lumen & CCT	-	-	-	-
	Color/Finish	–	White	White	White	White
	Lens	Frosted Polycarbonate	Acrylic	Acrylic	Acrylic, Polycarbonate	Acrylic, Polycarbonate
	Distribution	–	Lambertian	Parking Garage	Lambertian	Wide, Narrow
	Uplight	–	No	No	No	No
	Temperature Range	-40° to 45° C	-20° to 50° C	-20° to 50° C	-20° to 50° C	-40° to 50° C
	Emergency Battery Pack	–	-	10W	10W	10W
	Ratings	IP65, Wet, NSF2 Non-Food Zone, NEMA 4X	IP65,66,67; Wet, UL Sanitation	IP65,66,67; Wet, UL Sanitation	IP65,66,67; Wet, UL Sanitation	IP65,66,67; Wet, UL Sanitation
	DLC® DesignLights Consortium	Standard	Yes	Yes	Yes	Yes
	Buy America(n) Solutions	-	Yes (Option)	Yes (Option)	Yes (Option)	Yes (Option)
INTEGRATED CONTROLS	Standalone	-	-	Yes	Yes	Yes
	NX Networked - Wireless	-	-	-	-	-
	NX Networked - Wired	-	-	-	-	-
	NX Connect	-	-	-	-	-
APPLICATIONS	Uses	Wash Down, Cold Storage, Parking Garage, Wet Locations	Wash Down, Cold Storage, Parking Garage, Wet Locations	Parking Garage	Wash Down, Cold Storage, Parking Garage, Wet Locations	Wash Down, Cold Storage, Parking Garage, Wet Location Highbay

DLC® (DesignLights Consortium) Qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org

ROUND HIGH BAY
PRODUCT SELECTION GUIDE

		VALUE	COMMERCIAL	
		tradeSELECT		
		CRN2	**UTB2**	**SAV**
FEATURES	**Features**	+	++	++
	Sizes	11.8"/14.2" Dia	16" Dia	16"/ 22" Dia
	Mounting Height	Up to 40'	Up to 40'	Up to 30'
	Width	-	-	-
	Lumens	15,200-38,000	12,000- 30,000	8,000- 28,000
	Wattage	100-240W	84- 190W	72- 213W
	Efficacy (Max)	145-178	106-162	103-123
	Voltage	120-347V	120-277V, 347V, 480V	120-277V, 347V, 480V
	CRI	80	70, 80, 90	80, 90
	CCT	3500K, 4000K, 5000K	3000K, 3500K, 4000K, 5000K	2700K, 3000K, 3500K, 4000K, 5000K
	Switchable Technology	Switchable Lumen, CCT & Distribution	-	-
	Color/Finish	White, Black	Black, Gray, White	White, Gray, Black, Red, Blue, Champagne, Green, Currant, Wine
	Lens	Polycarbonate	Acrylic, Aluminum	Acrylic
	Distribution	Wide, Medium, Narrow	Wide	Wide
	Uplight	-	No	No
	Temperature Range	-40° to 50° C	-40° to 65° C	-40° to 50° C
	Emergency Battery Pack	40W Field Installable	10W	-
	Ratings	IP65, Wet, NSF2 Non-Food Zone, NEMA 4X,IK07	Damp Location	Damp Location
	DLC® DesignLights Consortium	Yes	-	-
	Buy America(n) Solutions	-	-	-
INTEGRATED CONTROLS	**Standalone**	Yes	Yes	Yes
	NX Networked - Wireless	-	Yes	-
	NX Networked - Wired	-	Yes	-
	NX Connect	-		-
APPLICATIONS	**Application**	Industrial, Gymnasium, Warehouse, Big Box Retail, Garden Center	Industrial, Gymnasium, Warehouse, Big Box Retail	Retail, School and Light Industrial

LINEAR HIGH BAY
PRODUCT SELECTION GUIDE

		VALUE	COMMERCIAL	SPECIFICATION
		tradeSELECT SWITCHABLE WATTAGE & CCT **CLH**	tradeSELECT  **PELA**	**ECH**
FEATURES	**Features**	+	++	+++
	Sizes	23", 31"	Scalable	Scalabe
	Mounting Height	Up to 40'	Up to 60'	Up to 60'
	Width	-	-	-
	Lumens	15,000-36,000	9,000- 60,000	9,000- 60,000
	Wattage	94-242W	57-380W	49-380W
	Efficacy (Max)	149-159	140-179	Up to 200
	Voltage	120-277V	120-277V, 347V, 480V	120-277V, 347V, 480V
	CRI	80	70, 80	70, 80, 90
	CCT	4000K, 5000K	4000K, 5000K	3000K, 3500K, 4000K, 5000K
	Switchable Technology	Switchable Lumen & CCT	-	-
	Color/Finish	White	White	White
	Lens	Polycarbonate	No Lens, Polycarbonate, Acrylic	No Lens, Polycarbonate, Acrylic
	Distribution	Medium, Narrow, Wide	Wide, Medium, Narrow	Wide, Medium, Narrow
	Uplight	–	-	Yes
	Temperature Range	-40° to 50° C	-30° to 50° C	-30° to 55° C
	Emergency Battery Pack	25W	20W, 30W	20W, 30W
	Ratings	IK08; Damp	IK10; Damp	IK10; Damp
	DLC® DesignLights Consortium	Yes	Yes	Yes
	Buy America(n) Solutions	-	Yes (Option)	Yes (Option)
INTEGRATED CONTROLS	**Standalone**	Yes	Yes	Yes
	NX Networked - Wireless	-	Yes	Yes
	NX Networked - Wired	-	Yes	Yes
	NX Connect	-	Yes	Yes
APPLICATIONS	**Application**	Industrial, Gymnasium, Warehouse, Big Box Retail	Industrial, Gymnasium, Warehouse, Big Box Retail	Industrial, Gymnasium, Warehouse, Big Box Retail

DLC® (DesignLights Consortium) Qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org

Products feature economical energy–saving commercial and light industrial life safety products. Value engineered to reduce cost without sacrificing quality, the Compass Series provides a compact product offering that can be purchased and installed without compromise.

CC Series

The CC Series LED combination exit/emergency light utilizes energy efficient LEDs and features fully adjustable LED lamp-heads and bright exit panel illumination, long-life Nickel Cadmium battery and optional remote capacity. UL 924, NFPA 101, NFPA 70, OSHA, CEC Title 20 Compliant and Damp Location.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
CCG High impact, UL flame rated thermoplastic combination exit/emergency light, single/double (universal) face, green letters, white finish	856143001417	2.5	6	-
CCR High impact, UL flame rated thermoplastic combination exit/emergency light, single/double (universal) face, red letters, white finish	856143001400	2.5	6	-
CCRG High impact, UL flame rated thermoplastic combination exit/emergency light, single/double (universal) face, selectable red or green letters, white finish	782520871635	2.5	6	-
CCRGRC High impact, UL flame rated thermoplastic combination exit/emergency light, single/double (universal) face, selectable red or green letters, white finish, remote capacity	782520871659	2.5	6	-
CCRRC High impact, UL flame rated thermoplastic combination exit/emergency light, single/double (universal) face, red letters, white finish, remote capacity	856143001424	2.5	6	-

CEL Universal

SWITCHABLE RED & GREEN

CEL Universal Edge-Lit Series offers economical upscale appearance with more configurations and less SKUs.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
CELSNA Edge-Lit Exit, surface mount, universal face, red/green switchable letters, satin aluminum, AC only	840141435510	3.1	6	-
CELSNE Edge-Lit Exit, surface mount, universal face, red/green switchable, satin aluminum, EM	840141435527	3.1	6	-
CELUNA Edge-Lit Exit, universal mount, universal face, red/green switchable letters, satin aluminum, AC only	840141435534	3.1	6	-
CELUNE Edge-Lit Exit, universal mount, universal face, red/green switchable, satin aluminum, EM	840141435541	3.1	6	-

CE Series

The CE Series Emergency Exit offers energy efficient LED's to illuminate the single or dual face exit panels. Featuring bright exit panel illumination. Available with long-life Nickel Cadmium battery and optional remote capacity or self-test/self-diagnostics.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
CAG High impact, UL flame rated thermoplastic exit, single/double (universal) face, green letters, white finish, AC only	856143002216	2	6	-
CAR High impact, UL flame rated thermoplastic exit, single/double (universal) face, red letters, white finish, AC only	856143002209	2	6	-
CARG High impact, UL flame rated thermoplastic exit, single/double (universal) face, selectable red or green letters, white finish, AC only	782520871598	2	6	-
CER High impact, UL flame rated thermoplastic exit, single/double (universal) face, red letters, white finish with battery	856143001448	2	6	-
CERG High impact, UL flame rated thermoplastic exit, single/double (universal) face, selectable red or green letters, white finish with battery	782520871611	2	6	-
CERRC High impact, UL flame rated thermoplastic exit, single/double (universal) face, red letters, white finish, remote capacity	856143001462	2	6	-
CERSD High impact, UL flame rated thermoplastic exit, single/double (universal) face, red letters, white finish, self-test/self-diagnostics	856143002414	2	6	-

COR Series

The COR Series LED Outdoor Remote offers energy efficient LEDs in an attractive single or double-head remote. Lamp-heads are fully adjustable and gasketed for outdoor operation.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
CORD Remote head, outdoor, double lamp heads, white finish, wet location	856143001530	1.2	12	-
CORS Remote head, outdoor, single lamp head, white finish, wet location	856143001523	1	20	-

CSWEU2LED

Outdoor LED emergency light with fully gasketed polycarbonate shield. Nickel Cadmium Battery, UL 924, UL Wet Location and CEC T20 Compliant.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
CSWEU2LED Wet location, impact resistant emergency light, white finish	856143002247	2.5	6	-

CU2 Series

LED emergency light with fully adjustable lamp-heads, long-life Nickel Cadmium or Nickel-Metal Hydride battery, energy efficient LED's and optional remote capacity.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
CU2 High impact, UL flame rated thermoplastic emergency light, white finish	856143001486	1	12	-
CU2RC High impact, UL flame rated thermoplastic emergency light, white finish, remote capacity	856143001493	1	12	-
CU2SD High impact, UL flame rated thermoplastic emergency light, white, finish, self-test/self-diagnostics	856143002353	1	12	-

CU2HL Series

The CU2HL Series is a high lumen output emergency light using a long-life Lithium Iron Phosphate battery, and adjustable high-power LED lamp-heads for incredible fixture spacing. 120-277VAC, UL924 and Damp Location Listed.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
CU2HL High lumen emergency light, 550 total lumens, white finish	840141417806	2.6	6	-
CU2HLHO High lumen emergency light, 1300 total lumens, white finish	840141417820	2.6	6	-
CU2HLHOSD High lumen emergency light, 1300 total lumens, white finish, self-test/self-diagnostics	840141417837	2.6	6	-

CU2SQ Series

The CU2SQ Series offers quality and value with a compact and attractive LED based emergency light. The white or black housing and lamp-heads are made of high impact UL flame rated thermoplastic. The square LED lamp-heads are fully adjustable and glare-free. Nickel Cadmium Battery, UL 924, NFPA 101, NFPA 70 and OSHA.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY
CU2SQ High impact, UL flame rated thermoplastic emergency light, square lamp heads, white finish	856143002155	1	12

CU2W Series

Emergency lighting fixture combining LED performance and value with a compact and attractive wet location LED based emergency light. Nickel Cadmium Battery, UL 924, NFPA 101, NFPA 70 and OSHA.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY
CU2WG Wet location, corrosion resistant emergency light, gray finish	856143001622	7.5	4

EXITS & COMBOS

PRODUCT SELECTION GUIDE

NOTE: See website and specification sheets for complete product family offerings.

		VALUE		
		CE Series	CC Series	CEL Series
FEATURES	Category	Exits	Combination Exit and Emergency	Exits
	Housing Material	High Imapct, UL Flame Rated Thermoplasctic	High Imapct, UL Flame Rated Thermoplasctic	Aluminum
	Function	AC only or With Battery	UL 924 Emergency Light	AC Only or with Battery
	Finish	White	White	Satin Aluminum
OPTIONS	Face(s) Universal (Single/Double Face)	Universal (Single/Double Face)	Universal (Single/Double Face)	Universal (Single/Double Face)
	Letter Color	Red; Green; Selectable Red/Green	Red; Green; Selectable Red/Green	Selectable Red/Green
	Remote Capacitiy	Models with "RC"	Models with "RC"	-
	Self-Test/Self-Diagnostics	Models with "SD"	Models with "SD"	-

Setting the standard for excellence with the broadest selection of commercial and industrial life safety products anywhere, Dual-Lite is a premiere manufacturer of life safety lighting.

EXITS & COMBOS

PRODUCT SELECTION GUIDE

		COMMERCIAL/SPECIFICATION	
		EVE Series	EVC Series
FEATURES	Category	Architectural Exits	Architectural Combination Exit and Emergency
FEATURES	Housing Material	High Imapct, UL Flame Rated Thermoplasctic	High Imapct, UL Flame Rated Thermoplasctic
FEATURES	Function	AC only or with Battery	UL 924 Emergency Light
FEATURES	Finish	White	White
OPTIONS	Face(s) Universal (Single/Double Face)	Universal (Single/Double Face)	Universal (Single/Double Face)
OPTIONS	Letter Color	Red; Green	Red; Green
OPTIONS	Remote Capacitiy	N/A	Select Models
OPTIONS	Self-Test/Self-Diagnostics	Select Models	Select Models

NOTE: See website and specification sheets for complete product family offerings.

EV Series

The EV Series is a compact architectural emergency lighting unit designed for fast wall mount installation and reliable service. The EV unit is available with or without remote capacity. The EV Series includes the EVR – 2 head LED indoor remote, and the EVO – single or double-head outdoor remote as an accessory. UL 924, RoHS and CEC Title 20 Compliant.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
EV2 High impact, UL flame rated thermoplastic emergency light, 1W LED heads, white finish	782520865405	1	12	-
EV2DI High impact, UL flame rated thermoplastic emergency light, 1W LED heads, white finish, Spectron self-test/self-diagnostics	782520865429	1	12	-
EV4D-02L High impact, UL flame rated thermoplastic emergency light, 2W LED heads, white finish	782520866785	1	12	-
EV4DI-02L High impact, UL flame rated thermoplastic emergency light, 2W LED heads, white finish, Spectron self-test/self-diagnostics	782520866792	1	12	-

EVC Series

The EVC Series is a compact architectural LED combination exit and emergency lighting unit designed for fast installation and reliable service. Remote capability, Lithium Iron Phosphate Battery, UL 924, NFPA 101, NFPA 70, CEC Title 20 Compliant and Damp Location

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
EVCUGW High impact, UL flame rated thermoplastic combination exit/emergency light, single/double (universal) face, green letters, white finish	782520866389	4	6	-
EVCURW High impact, UL flame rated thermoplastic combination exit/emergency light, single/double (universal) face, red letters, white finish	782520866372	4	6	-
EVCURWD4 High impact, UL flame rated thermoplastic combination exit/emergency light, single/double (universal) face, red letters, white finish, remote capacity	782520866402	4	6	-

EVE Series

The EVE Series is a compact architectural LED exit sign designed for fast installation and reliable service. Nickel Metal Hydride Battery, UL 924, NFPA 101, NFPA 70, CEC Title 20 Compliant and Damp Location

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
EVEUGW Architectural thermoplastic exit, universal single/double face, green letters, white finish, AC only	782520866730	3	12	-
EVEUGWE Architectural thermoplastic exit, universal single/double face, green letters, white finish with battery	782520866747	3	12	-
EVEURW Architectural thermoplastic exit, universal single/double face, red letters, white finish, AC only	782520866662	3	12	-
EVEURWE Architectural thermoplastic exit, universal single/double face, red letters, white finish with battery	782520866679	3	12	-
EVEURWEI Architectural thermoplastic exit, universal single/double face, red letters, white finish, Spectron self-test/self-diagnostics	782520866686	3	12	-

EVO Series

The EVO Series offers architecturally styled high performance LED remotes for outdoor applications which accept DC input from the EV4 emergency light with remote capacity.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
EVODW Die-cast outdoor remote, double head, white finish	782520866235	1	12	-

EZ-2 Series

The EZ-2 Series is a ceiling or wall mounted emergency light with superior performance, adjustable lamp-heads, easy access battery compartment. UL924, NFPA 101, NFPA 70, Damp Location, CEC Title 20 Compliant.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
EZ-2L High impact, UL flame rated thermoplastic emergency light, 1W LED heads, white finish	840141404592	1.6	6	-

PG Series

The PG Series is a wet location listed emergency lighting unit for indoor/outdoor installation featuring long-life, high-output LEDs. Nickel Cadmium Battery, UL 924, UL Wet Location, NFPA 101, NFPA 70 and OSHA.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
PGW-HTR LED Emergency Light, with heater, 4 lamp-heads, wall mount, 120/277V 2.8W, white housing	782520862091	6.5	6	-

PowerLED PLD+ Series

The Dual-Lite PowerLED Plus family offers intelligent 2-wire (120/277V) emergency LED battery packs that work with an AC LED driver to allow an LED lighting load to be used in both normal and emergency operation.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
PLD10+ Emergency LED battery pack, 120V/277V, 20-56 VDC, 10W, lithium iron phosphate battery	840141431451	1.9	6	-
PLD10M+ Emergency LED battery pack, 120V/277V, 20-56 VDC, 10W, metal construction, lithium iron phosphate battery	840141431468	1.9	6	-

EXO
OUTDOOR LIGHTING

Combines innovative technology with practical lighting solutions and service-oriented performance based on in-depth knowledge of the electrical distributor and contractor markets.

FLOODLIGHT
BEAM SPREAD GUIDE



MODEL	Marshal	Colt LBUL	Lightscaper®	Sling Flood
DISTRIBUTION	NEMA 5x5	NEMA 5x5	NEMA 7x6	NEMA 7x7
EQUIVALENCY	100W	100W	70W 100W	100-1000W
LUMENS	6466lm	3234lm	1000lm 2000lm	40000lm
WATTS	Switchable 26W, 40W, 50W	Switchable 13W, 20W, 25W	8W 20W	20-320W

Not all configurations and outputs shown, please visit website for the most up–to–date information. Due to our continued efforts to improve our products, product specifications are subject to change without notice.



Center Beam Axis @ 0°
(typically max beam intensity measured as Center Beam Candle Power / CBCP)

Beam Angle
(angle within the beam of light equal to 50% of the max beam intensity)

Field Angle
(angle within the beam of light equal to 10% of the max beam intensity)

NEMA BEAM SPREAD CLASSIFICATION		
Beam Spread Degrees (Field Angle)	NEMA Type	Beam Description
10° up to 18°	1	Very Narrow
18°–29°	2	Narrow
29°–46°	3	Medium Narrow
46°–70°	4	Medium
70°–100°	5	Medium Wide
100°–130°	6	Wide
130° and up	7	Very Wide

FLOODLIGHTS

PRODUCT SELECTION GUIDE

		VALUE	COMMERCIAL	COMMERCIAL
		tradeSELECT	tradeSELECT	tradeSELECT
		Marshal	Colt LBUL	Lightscaper
FEATURES	Easy to Install	Yes	Yes	Yes
	Mounting Options	Junction box	½" 14 NPS	½" 14 NPS
	Features	+	++	++
	Maintenance	Low, Aiming	Low, Aiming	Med, Aiming, Adjustment
PERFORMANCE	Lumens (lm)	3612-7258	1806-3634	984, 2009
	Watts	Switchable 26W, 40W, 50W	Switchable 13W, 20W, 25W	8W, 16W
	Efficacy (maximum LPW)	129-144	133-153	116-128
	Distribution	Each Head NEMA 5X5 Wide	NEMA 5x5 Wide	NEMA 7X6 Wide
	CCT	Switchable 3000K, 4000K, 5000K	Switchable 3000K, 4000K, 5000K	3000K, 4000K, 5000K
	CRI	80	80	70-100
	Certifications	Listed for Wet Locations: Yes; UL1598: Yes; IP65: Yes	Listed for Wet Locations: Yes; UL1598: Yes; IP65: Yes	Listed for Wet Locations: Yes; UL1598: Yes; IP65: Yes
	Product Life	>60,000hrs.	>60,000 hrs.	60,000hrs.
	HID Equivalence	100W	100W	100W
	Energy Savings (Based on HID Equivalence)	85%	83%	86%
	Voltage	120-277V	120-277V	120-277V
CONTROLS	Basic occupancy	Yes	–	–
	Occupancy and Daylight Harvesting	Yes	–	–

COMMERCIAL			SPECIFICATION		
tradeSELECT Sling FLood			 Ratio Flood		
Yes			Yes		
Threaded Knuckle, Slipfitter & Trunnion			Threaded Knuckle, Slipfitter & Trunnion		
++			+++		
Low, Aiming			Low, Aiming		
2500-40,000			3500-30,000		
20-320W			25-265W		
123-150			140		
NEMA 7x7 Wide			Narrow, Medium, Wide		
4000K			3000K, 4000K, 5000K		
70			70		
Wet Location	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
Yes	Yes	Yes	Yes	Yes	Yes
> 60,000 hours			>60,000hrs.		
100-1000W			100-1000W		
86%			76%		
120V(20 & 40W), 120-277V(80-320W)			120-277V & 347-480V		
–			Yes		
–			Yes		

WALL PACK

MOUNTING HEIGHT GUIDE



MODEL	PRS	PRL-C	SG1	SG2	WGH1	WGH2	WGH3
EQUIVALENCY	70-100W	up to 250W	70–150W	175–250W	up to 200W	up to 250W	up to 400W
LUMENS	2841-2899lm	2537–8460lm	1300–4000lm	5500–8000lm	3200-7520lm	4800-10,700lm	11,400-17,000lm
WATTS	20W	18-60W	11–38W	51–80W	20-50W	30–70W	80–120W

Not all configurations and outputs shown, please visit website for the most up–to–date information. Due to our continued efforts to improve our products, product specifications are subject to change without notice.

WALL PACK
PRODUCT SELECTION GUIDE

		VALUE			COMMERCIAL		
		tradeSELECT PRS PERIMASHIELD			tradeSELECT WGH1		
FEATURES	Easy to Install	Yes			Yes		
	Mounting Options	Junction Box, conduit			Junction Box, conduit		
	Features	+			++		
	Maintenance	Low			Low		
PERFORMANCE	Lumens (lm)	2841–2899			3000-7520		
	Watts	20W			20-50W		
	Efficacy (maximum LPW)	106			143-159		
	Distribution	Type IV			Type IV		
	Switchable Technology	–			Lumen and CCT		
	CCT	4000K, 5000K			3000K,4000K, 5000K		
	CRI	70			80		
	Certifications	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
		Yes	Yes	–	Yes	Yes	Yes
	Product Life	>60,000hrs.			>60,000hrs.		
	HID Equivalence	100W			Up to 200W		
	Energy Savings (Based on HID Equivalence)	77%			75–80%		
	Voltage	120–277V			120-347V		
CONTROLS	Basic occupancy	Yes			Yes		
	Occupancy & Daylight Harvesting	Photocontrol			Photocontrol		

COMMERCIAL

tradeSELECT SWITCHABLE LUMEN & CCT WGH2	tradeSELECT SWITCHABLE LUMEN & CCT WGH3	tradeSELECT SLING WALL	tradeSELECT SWITCHABLE WATTAGE PRELUDE
Yes	Yes	Yes	Yes
Junction box, conduit	Junction Box, conduit	Junction Box, conduit	Junction Box, conduit
+++	+++	+++	+++
Low	Low	Low	Low
4800-10,700	11,400-17,000	2200–8100	2500-8600
30-70W	80–120W	21–80W	18-60W
146-162	140-154	110–115	139-–144
Type IV	Type IV	Type IV	Type III (Cut Off), Type IV (Refractor)
Lumen and CCT	Lumen and CCT	–	Wattage
3000K, 4000K, 5000K	3000K, 4000K, 5000K	3000K, 4000K, 5000K	3000K, 4000K, 5000K
80	80	70	70

Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65	UL1598	IP65	IP65	Listed for Wet Locations	UL1598	IP65
Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
>60,000hrs.			>60,000hrs.			>60,000hrs.			>60,000hrs.		
Up to 250W			up to 400W			100–250W			70–250W		
75–80%			75–80%			70–80%			75–80%		
120-347V			120-347V			120–277V			120–277V		
Yes			Yes			Yes			–		
Photocontrol			Photocontrol			Optional			–		

Area and Site

Poles and Accessories

Square Straight Steel Poles and Accessories

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
93085300 Template (only): anchor bolt details for square steel poles (DO NOT USE ON OTHER POLE DESIGNS)		0.01		-
20102389702 Pole cap (only): for 4" square pole, top cap	785988004485	0.3		-
SSSH20-40A-4-HV-DBT-WPO Square steel pole, 20', 4" square cross-section, 1/8" wall thickness, dark bronze matte textured	78598838961	142		-
SSSH25-40A-4-HV-DBT-WPO Square steel pole, 25', 4" square cross-section, 1/8" wall thickness, dark bronze matte textured	78598838978	175		-
SSSHSTK4KIT SSSH-STK-4-KIT, includes anchor bolts, template, base cover and plastic pole cap	785988045983	20		-
TAB30M38 Anchor bolts (only): 3/4" x 30" x 3" anchor bolt set (four bolts with hardware)	785988496983	16		-
TAB36M38 Anchor bolts, 1 in x 36 in x 4 in	785988496938	16		-
VM14DBT Vibration Dampener, mounts to top of pole for reduced vibration	785988046249	20		-

SGC-F Sling Canopy

SWITCHABLE WATTAGE & CCT

Commercial grade LED canopy luminaire for use in outdoor applications such as commercial building, retail, government and educational facilities. Low profile housing with a lightly diffused lens for reduced pixelation and glare. Heat dissipating fins provide superior thermal performance extending the life of the electronic components.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
SGC-F-60-LSCS SGC Sling Canopy, Switchable Lumen 3500-7800lm, 25/40/60W, Switchable CCT 3000/4000/5000K, 250W equivalency, dark bronze matte textured	840141432137	5.1	1	S-B7MJBN

SGD Sling Dusk-to-Dawn

Multi-purpose Dusk-to-Dawn LED luminaire provides general purpose area, security, roadway and landscape lighting. Rugged die-cast aluminum housing with textured grey or dark bronze powder paint provides corrosion resistance and clean finish.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
SGD-60-LSCS Sling Dusk-to-Dawn, Switchable Wattage 40W-60W, 154-156LPW, Switchable CCT 4000K/4500K/5000K, 120-277V, dark bronze	840141413419	7.4	2	S-Z05VPC
SGD-60-LSCS-GR Sling Dusk-to-Dawn, Switchable Wattage 40W-60W, 145-156LPW, Switchable CCT 4000K/4500K/5000K, 120-277V, light gray	840141413402	7.4	2	S0GW3EI

Sling Bollard

Commercial grade LED Bollard for use in outdoor applications such a commercial building, retail, government and educational facilities. Features field switchable wattage and color temperature.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
SGB-R-LSCS Round bollard, Switchable Wattage 12/16/22W, Switchable CCT 3000K/4000K/5000K, Type 5 distribution, 120-277V, dark bronze matte textured	84014141283	15.6	1	-
SGB-S-LSCS Square bollard, Switchable Wattage 12/16/22W, Switchable CCT 3000K/4000K/5000K, Type 5 distribution, 120-277V, dark bronze matte textured	840141412825	15.6	1	-

VBGL2 & VWGL2 Vaportites

LED vaportite luminaires for wall or ceiling mount, compact yet rugged design with standard frosted globe and wire guard.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
VBGL-2 LED, die-cast aluminum, ceiling mount, 2722 lumens, 20W, 4000K, 120-277V, 100W HID equivalent, platinum silver, IP66	840141407319	3.8	1	-
VGL-BU Globe, blue	78598841275	1	1	-
VGL-FG Globe, frosted glass	78598841282	1	1	-
VGL-GN Globe, green	78598841299	1	1	-
VGL-GUARD Wire guard, grey	840141408316	0.5	1	-
VGL-RD Globe, red	78598841305	1	1	-
VGL-YW Globe, yellow	78598841312	1	1	-
VWGL-2 LED, die-cast aluminum, wall mount, 2673 lumens, 20W, 4000K, 120-277V, 100W HID equivalent, platinum silver, IP66	840141407326	4.4	1	-

Floodlights

LBUL Colt

SWITCHABLE WATTAGE & CCT

Ultra compact LED flood with NEMA 5x5 distributions for lighting applications such as safety/security, accent, flag pole, columns, or signs. The LBUL Colt flood was designed for traditional landscape form with improved performance and efficacy.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
LBUL-25-LSCS Small LED Flood, Up to 3234 lumens, switchable wattage (13W,20W,25W), switchable CCT (3K,4K,5K), 80 CRI, 5x5 distribution, 1/2" threaded knuckle mount, die-cast aluminum, 120-277V, dark bronze matte textured, 8" mounting stake	840141416939	1	12	S-TDR3HY
LBUL-25-RGBW Small LED Flood, Up to 2550 lumens, 20W, switchable RGBW (4K, Red, Blue, Green), 80 CRI, 5x5 distribution, 1/2" threaded knuckle mount, die-cast aluminum, 120-277V, dark bronze matte textured, 8" mounting stake	840141430560	1	12	-

Lightscaper®

A versatile LED floodlight perfect for illuminating signs, trees and entrances or small area illumination. It features Switchable Wattage and CCT technology as well as adjustable knuckle pivot from 0–75º, with wide 6X7 flood distribution and tempered glass lens.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
LSP-LSCS LED, die-cast aluminum, Switchable Wattage, 8-20W, 984-2009lm, and Switchable CCT 3000K/4000K/5000K, 70 CRI. 6x7 distribution, knuckle mount, glass lens, 120-277V, 0-10V dimming, dark bronze matte textured	840141403939	3.4	6	PGM3XQL6

Lightscaper® RGBW

A versatile LED floodlight perfect for illuminating signs, trees and entrances or small area illumination. It features switchable colors; Red, Blue, Green and White which provides ten different custom color illumination choices, as well as adjustable knuckle pivot from 0–75º, with wide 6X7 flood distribution and tempered glass lens.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
LSP-RGBW LED, die-cast aluminum, Switchable Red Blue Green White, 1950 lumens, 17W, 6x7 distribution, knuckle mount, glass lens, 120-277V, 0-10V dimming, dark bronze matte textured	840141408309	3.3	6	-

Marshal LED Twin Head Motion Sensor Kit

Attractive security floodlight improves safety and replaces bulky outdated fixtures. Powerful LED system saves energy and maintenance over traditional lighting sources. Includes adjustable settings for time, sensitivity, and distance. Aimable PIR occupancy sensor has 180° coverage, perfect for outdoor applications.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
ML-2L-50-LSCS Marshal LED Twin Head Motion Sensor Kit, up to 6468 lumens, switchable wattage (13W,20W,25W per head), switchable CCT(3K,4K,5K), 80 CRI, ceiling or wall mounted, dark bronze, 120-277V VAC	840141432946	2.3	1	-
ML-2L-50-LSCS-WH Marshal LED Twin Head Motion Sensor Kit, up to 6468 lumens, switchable wattage (13W,20W,25W per head), switchable CCT(3K,4K,5K), 80 CRI, ceiling or wall mounted, white, 120-277V VAC	840141432953	2.3	1	-

Options and Accessories

Steel and Cast Iron Brackets.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
4040 Steel Wall/Pole mounting bracket, steel, dark bronze matte textured	785988310555	2.5	1	-
4041 Steel Wall/Pole mounting bracket, steel, dark bronze matte textured	785988310579	7	1	-
4024C Steel slipfitter, 2" pipe, steel, dark bronze matte textured	785988310326	3.7	1	-
BHH-2180-PT20-DBT Pole top bracket, two luminaires, dark bronze matte textured	785988041244	14.4	1	-
S-302-M51 Slipfitter, 1/2" hub, 2 3/8" slip fit, die-cast aluminum, dark bronze matte textured	785988473861	0.6	1	-
TRN-DB Trunnion, die-cast aluminum, dark bronze matte textured	785988030446	0.5	1	-
TWK-11 Wall bracket, aluminum	785988502202	3.3	1	-

Photocontrol

Button Photocontrol for dusk to dawn lighting.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
PHOTOCELL-BTN U Button photocontrol, 120-277V	840141435343	0.01	1	-

SGF Sling Flood Family Floodlights

SWITCHABLE WATTAGE & CCT

Commercial grade LED flood luminaire, available in three sizes, for use in outdoor applications such as commercial building, retail, government and educational facilities. Includes a durable glass lens and reflector to create a wide 7x7 uniform distribution.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
SGF1-60-LSCS-UNVC-PC Sling Flood, Switchable Wattage 20-60W, 3049-8214lm, 125LPW, Switchable CCT 3000K/4000K/5000K, 120-347V, Photocell, 1/2 inch threaded knuckle mount	840141433967	3.9	1	S-1E2H6P
SGF2-120-LSCS-UNVC-PC Sling Flood, Switchable Wattage 80-120W, 10,000-15,000lm, 125LPW, Switchable CCT 3000K/4000K/5000K, 120-347V, Photocell. Ships with trunnion & knuckle mount.	840141433974	13.6	1	S-PXH9GR
SGF3-200-LSCS-UNVC-PC Sling Flood, Switchable Wattage 130-200W, 16,000-25,000lm, 125LPW, Switchable CCT 3000K/4000K/5000K, 120-347V, Photocell. Ships with trunnion & knuckle mount.	840141433981	23.8	1	S-6EO87I
SGF3-320-LSCS-UNVC-PC Sling Flood, Switchable Wattage 200-320W, 25,000-40,000lm, 125LPW, Switchable CCT 3000K/4000K/5000K, 120-347V, Photocell. Ships with trunnion & knuckle mount.	840141433998	24.6	1	S-O1KN8G

Wallpack

LNC2 Wallpack

The LitePak LNC2 LED is designed for perimeter illumination for safety, security and identity. Featuring Micro Strike optics for improved uniformity and reduce glare.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
LNC2-35-4K7-3-PC LNC2 Micro Strike Wallpack, 4500 lumens, 4000K, Type 3, 120-277V, die-cast aluminum, dark bronze matte textured, photocontrol	840141432663	9.6	1	-

Prelude Wallpack

The Prelude Wallpack luminaires offers an architectural contemporary form with maximum flexibility. These luminaires feature field Switchable Wattages from 18 to 60 Watts. The cut-off configuration is perfect for applications requiring no up-light.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
PRL-C-LS-4K LED, 2500-8400lm, 18-60W, 4000K, Type 3, cut-off, 120-277V, 0-10V dimming, wall mount, die-cast aluminum, dark bronze matte textured	840141404271	5.3	4	P1OVAZ9O

PRS Perimashield Wallpack

Compact stylish wallpack constructed of die-cast aluminum. Features impact resistant UV stabilized polycarbonate refractor. Mounts to standard 3–3–1/2" junction boxes with 1/2" conduit entry for surface mount applications. Optional photocontrol available for dusk to dawn operations.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
PRS–20–4K–PC PRS Perimashield, 2899 lumens, 20W, 4000K, Type 4, polycarbonate lens, 120-277V, 0-10V dimming, wall mount, die-cast aluminum, dark bronze matte textured, photocontrol	840141419848	2.8	4	PLNW1XXG7LNV
PRS–20–5K–PC PRS Perimashield, 2899 lumens, 20W, 5000K, Type 4, polycarbonate lens, 120-277V, 0-10V dimming, wall mount, die-cast aluminum, dark bronze matte textured, photocontrol	840141419855	2.8	4	PLR2TUO8Y8TN

WGH Switchable Glass Refractor Wallpack

SWITCHABLE WATTAGE & CCT

Available in three sizes. Borosilicate glass refractor softens LED and provides uniform distribution. Field switchable wattage and color temperature (3000K, 4000K, 5000K), with ideal wall mounting heights from 15-25ft.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
WGH1-50-LSCS-UNVC Glass Refractor Wallpacks, Switchable Wattage 20-50W, 2800-6900lm, 143-159LPW, Switchable CCT 3000K/4000K/5000K , Type 4 , bronze, button photocontrol with optional cover, 120-347V	840141432076	8.4	1	S-F57SGY
WGH2-70-LSCS-UNVC Glass Refractor Wallpacks, Switchable Wattage 30-70W, 4600-10,000lm, 146-162 LPW, Switchable CCT 3000K/4000K/5000K , Type 4 , bronze, button photocontrol with optional cover, 120-347V	840141431192	10.8	1	S-5NRXRT
WGH3-120-LSCS-UNVC Glass Refractor Wallpacks, Switchable Wattage 80-120W, 9800-17,000lm, 140-154 LPW, Switchable CCT 3000K/4000K/5000K , Type 4 , bronze, button photocontrol with optional cover, 120-347V	840141431208	13.9	1	S-G1NR91

SG Sling Wallpack

Slender wallpack/floodlight available in two sizes for a variety of applications including building perimeter/security lighting, entrances, stairways, loading docks or facades for schools, apartments or commercial buildings.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
SG1-20-4K-PCU LED, Small, 2310 lumens, 21W, 4000K, forward throw distribution, 120-277V, 0-10 dimming, wall mount, die-cast aluminum, dark bronze matte textured, photocontrol	785988033195	4.3	6	-
SG1-20-PCU LED, Small, 2263 lumens, 21W, 5000K, forward throw distribution, 120-277V, 0-10 dimming, wall mount, die-cast aluminum, dark bronze matte textured, photocontrol	785988033140	4.3	6	-
SG1-30-4K-PCU LED, Small, 3060 lumens, 29W, 4000K, forward throw distribution, 120-277V, 0-10 dimming, wall mount, die-cast aluminum, dark bronze matte textured, photocontrol	785988033201	4.3	6	-
SG1-30-PCU LED, Small, 3270 lumens, 29W, 5000K, forward throw distribution, 120-277V, 0-10 dimming, wall mount, die-cast aluminum, dark bronze matte textured, photocontrol	785988033157	4.3	6	-
SG1-40-4K-PCU LED, Small, 4070 lumens, 11W, 4000K, forward throw distribution, 120-277V, 0-10 dimming, wall mount, die-cast aluminum, dark bronze matte textured, photocontrol	785988044740	4.3	6	-
SG1-40-PCU LED, Small, 4008 lumens, 11W, 5000K, forward throw distribution, 120-277V, 0-10 dimming, wall mount, die-cast aluminum, dark bronze matte textured, photocontrol	785988044733	4.3	6	-
SG2-50-4K-PCU LED, Large, 5526 lumens, 51W, 4000K, forward throw distribution, 120-277V, 0-10 dimming, wall mount, die-cast aluminum, dark bronze matte textured, photocontrol	785988033225	11	6	-
SG2-50-PCU LED, Large, 5548 lumens, 51W, 110 LPW, 5000K, forward throw distribution, 120-277V, 0-10V dimming, wall mount, die-cast aluminum, dark bronze matte textured	785988033171	11	6	-
SG2-80-4K-PCU LED, Large, 8079 lumens, 80W, 4000K, forward throw distribution, 120-277V, 0-10 dimming, wall mount, die-cast aluminum, dark bronze matte textured, photocontrol	785988033232	11	6	-
SG2-80-PCU LED, Large, 8061 lumens, 80W, 5000K, forward throw distribution, 120-277V, 0-10 dimming, wall mount, die-cast aluminum, dark bronze matte textured, photocontrol	785988033188	11	6	-

SGS Sling Site

Compact sleek design area/site lighter featuring an arm for round or square pole and mast arm fitter. Switchable wattage and CCT, ships with Type 3, Type 4, and Type 5 optics, which can easily be changed in the field.

	Catalog Number	Material Description	Description	UPC Code	Lbs. each	DLC Listing	Carton Qty
Fixture	SGS-150-LSCS-UNVC-HEAD	95063703	Compact sleek design, field switchable wattage (85W, 120W, 150W) with a lumen range of 13,000 - 23,000 lumens and switchable CCT (3000K, 4000K, 5000K). Ships with interchangeable Type 3, Type 4, and Type 5 optics, 120-347V.	84014147684	5.5	S-HBQ9CB	1
	SGS-150-LSCS-UNVC-7PC-HEAD	93320292	Compact sleek design, field switchable wattage (85W, 120W, 150W) with a lumen range of 13,000 - 23,000 lumens and switchable CCT (3000K, 4000K, 5000K). Ships with interchangeable Type 3, Type 4, and Type 5 optics, 120-347V. Includes 7-pin receptacle with shorting cap and photocell. Fixture head only.	840141430430	5.5	S-HBQ9CB	1
Mounting	SGS-ARM	95063704	Area/site light arm mount with RPA for 4"-5"OD Pole and knuckle	840141417691	3.4	-	6
	SGS-MAF	95063705	Area/site light mast arm fitter mount (2-3/8"OD) with knuckle	840141417707	1.6	-	10
Optional Accessories	HB03DPR	93161798	Field Installed Occupancy and Daylight Sensor	840141406213	.08	-	1
	HB03DPR-REMOTE	93161799	Programming Remote for HB03DPR Sensor (Typically one required per site to program the sensors)	840141406220	.16	-	1
	SGS-HSS	93315247	Field Installed House Side Shield	840141417714	1.2	-	6
	241-C-DBT	241CDB	Flat surface bracket (Wall Mount Accessory. Compatible with MAF mounting only.)	785988019540	16	-	1

SGS Sling Site Pole Combo

Square Straight Steel Poles with SGS Area Light

Catalog Number	Material Description	Description	UPC Code	Lbs. each	DLC Listing	Carton Qty
SGS-150-LSCS-S20	93315634	20' Pole with single, SGS-150-LSCS-UNVC-HEAD-7PR and SGS-ARM. Field switchable wattage (85W/120W/150W) with a lumen range of 13,000 - 23,000 lumens and switchable CCT (3000K/4000K/5000K). Ships with interchangeable Type 3, Type 4, and Type 5 optics, 120-347V. Includes 7-pin receptacle with shorting cap and photocell.	-	-	-	-
SGS-150-LSCS-S20-2X	93315635	20' Pole with two, SGS-150-LSCS-UNVC-HEAD-7PR and SGS-ARM. Field switchable wattage (85W/120W/150W) with a lumen range of 13,000 - 23,000 lumens and switchable CCT (3000K/4000K 5000K). Ships with interchangeable Type 3, Type 4, and Type 5 optics, 120-347V. Includes 7-pin receptacle with shorting cap and photocell.	-	-	-	-
SGS-150-LSCS-S25	93315636	25' Pole with single, SGS-150-LSCS-UNVC-HEAD-7PR and SGS-ARM. Field switchable wattage (85W/120W/150W) with a lumen range of 13,000 - 23,000 lumens and switchable CCT (3000K/4000K/5000K). Ships with interchangeable Type 3, Type 4, and Type 5 optics, 120-347V. Includes 7-pin receptacle with shorting cap and photocell.	-	-	-	-
SGS-150-LSCS-S25-2X	93315637	25' Pole with two, SGS-150-LSCS-UNVC-HEAD-7PR and SGS-ARM. Field switchable wattage (85W/120W/150W) with a lumen range of 13,000 - 23,000 lumens and switchable CCT (3000K/4000K/5000K). Ships with interchangeable Type 3, Type 4, and Type 5 optics, 120-347V. Includes 7-pin receptacle with shorting cap and photocell.	-	-	-	-



CANOPY

PRODUCT SELECTION GUIDE

		VALUE			COMMERCIAL		
		tradeSELECT					
		SLING CANOPY			LUMASQUARE		
FEATURES	Easy to Install	Yes			Yes		
	Mounting Options	Standard J–Box–¾" Pendant, 3 sided 1/2" 14 NPS threaded conduit entry			Standard J–Box or ¾" Pendant, 4 sided 1/2" threaded conduit entry		
	Features	++			++		
	Maintenance	Low			Low		
PERFORMANCE	Lumens (lm)	3560-8312			3000–9000		
	Watts	25–60W			25–75W		
	Efficacy (maximum LPW)	122-164			120–127		
	Distribution	Type V			Type V		
	CCT	3000K, 4000K, 5000K			3000K, 4000K, 5000K		
	CRI	70			70		
	Certifications	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
		Yes	Yes	Yes	Yes	Yes	Yes
	Product Life	>60,000hrs.			>60,000hrs.		
	HID Equivalence	100-250W			175–250W		
	Energy Savings	75%			75%		
	Voltage	120–277V			120–277V		
CONTROLS	Basic occupancy	–			Yes		
	Occupancy and Daylight Harvesting	–			Yes		

DUSK TO DAWN

PRODUCT SELECTION GUIDE

		COMMERCIAL			SPECIFICATION		
		 SLING SGD			SGS Sling Site		
FEATURES	Easy to Install	Yes			Yes		
	Mounting Options	2 ⅜"–1 ⅝", Pipe & Wall Mount			Arm Mount for Round or Square Pole and Knuckle Slipfitter, , Wall Mount with Optional Accessory		
	Features	++			+++		
	Maintenance	Low			Low		
PERFORMANCE	Lumens (lm)	6230-8175			13,000-23,000		
	Watts	40-60W			85-150W		
	Efficacy (maximum LPW)	145–156			153-157		
	Distribution	Type V			Type III, Type IV, Type V		
	CCT	4000K, 4500K, 5000K			3000K, 4000K, 5000K		
	CRI	70			70		
	Certifications	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
		Yes	Yes	Yes	Yes	Yes	Yes
	Product Life	>60,000hrs.			>60,000hrs.		
	HID Equivalence	100–250W			250–400W		
	Energy Savings (Based on HID Equivalence)	78%			78%		
	Voltage	120–277V			120–347V		



VAPORTITE
PRODUCT SELECTION GUIDE

VALUE

		tradeSELECT VBGL			tradeSELECT VWGL		
FEATURES	Easy to Install	Yes			Yes		
	Mounting Options	Standard J–Box–Ceiling–4 sided ½" 14 NPS threaded conduit entry			Standard J–Box–4 sided ½" 14 NPS threaded conduit entry		
	Features	++			++		
	Maintenance	Low			Low		
PERFORMANCE	Lumens (lm)	2722			2673		
	Wattage	20W			20W		
	Efficacy (maximum LPW)	136			134		
	CCT	4000K			4000K		
	CRI	80			80		
	Certifications	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
		Yes	Yes	Yes	Yes	Yes	Yes
	Product Life	60,000hrs.			60,000hrs.		
	HID Equivalence	100W			100W		
	Energy Savings (Based on HID Equivalence)	82%			82%		
	Voltage	120-277V			120-277V		

LIGHTING CONTROLS™

Lighting control technologies provide intuitive and flexible deployment options to meet code, enhance comfort, increase energy savings and improve operating efficiency for enterprises of any size.

LIGHTHAWK®
PRODUCT SELECTION GUIDE

		VALUE	COMMERCIAL	SPECIFICATION
		tradeSELECT LightHAWK LHL PIR	 LightHAWK PIR	 LightHAWK Dual Tech
FEATURES	**Easy to Install**	Yes	Yes	Yes
	Features	+	++	+++
	Sensing Technology	PIR	PIR	PIR/US
	Self-adjusting Settings	No	Yes – IntelliDAPT®	Yes – IntelliDAPT®
	Mounting	Standard Switch Box	Standard Switch Box	Standard Switch Box
	Coverage	1,000 Sq. Ft., 180° coverage area	1,000 Sq. Ft., 180° coverage area	1,000 Sq. Ft., 180° coverage area
	Voltage	120/277VAC;50/60Hz	120/277VAC;50/60Hz, 347VAC; 50/60Hz 24VDC (requires UVPP)	120/277VAC;50/60Hz 347VAC; 50/60Hz 24VDC (requires UVPP)
	Electrical Ratings	120VAC: 800W Incandescent/ Electronic Ballast/ LED Driver: 1,000W Magnetic Ballast; 1/6 HP Motor 277VAC: 1,800W Magnetic Ballast/ Electronic Ballast/ LED Driver: 1/6 HP Motor	120VAC: 800W Incandescent/Electronic Ballast/ LED Driver: 1,000W Magnetic Ballast; 1/6 HP Motor 277VAC: 1,800W Magnetic Ballast/ Electronic Ballast/ LED Driver: 1/6 HP Motor 347VAC: 1,500W Magnetic Ballast/ Electronic Ballast/ LED Driver: 1/6 HP Motor	120VAC: 800W Incandescent/Electronic Ballast/ LED Driver: 1,000W Magnetic Ballast; 1/6 HP Motor 277VAC: 1,800W Magnetic Ballast/ Electronic Ballast/ LED Driver: 1/6 HP Motor 347VAC: 1,500W Magnetic Ballast/ Electronic Ballast/ LED Driver: 1/6 HP Motor
	Minimum Load	None	None	None
	Operating Modes	Occupancy (Auto–ON) / Vacancy (Manual–ON)	Occupancy (Auto–ON) / Vacancy (Manual–ON)	Occupancy (Auto–ON) / Vacancy (Manual–ON)
	Time Delay	4, 8, 16, 20 mins	4, 8, 15, 30 mins	4, 8, 15, 30 mins
	Photocell	10–500 foot–candles	10–500 foot–candles	10–500 foot–candles
	Relay	Single	Single and Dual versions	Single and Dual versions
	Operating Environment	Indoor	Indoor	Indoor
	Occupancy and Daylight Harvesting	Yes	Yes	Yes
	Construction	RhinoTuff™ vandal resistant lens	RhinoTuff vandal resistant lens	RhinoTuff vandal resistant lens
	Color	White; Ivory; Light Almond; Gray; Black	White; Ivory; Light Almond; Gray; Black	White; Ivory; Light Almond; Gray; Black
	Certifications	Title 24, cULus	Title 24, cULus	Title 24, cULus
USES	**Applications**	Storerooms, Copier Rooms, Closets, Breakrooms, Small Single Person Bathrooms (No Stalls)	Storerooms, Copier Rooms, Closets, Breakrooms, Small Single Person Bathrooms (No Stalls)	Private Offices, Small Conference Rooms, Small Classrooms

Cables

Network System Cables are plenum rated, Cat5 cables that can be used with the NX Lighting Controls system and CX Panels.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
CAT5-25F-OR-PLENUM Cat5 cable, 25ft, orange, plenum rated	640181727329	0.5		-
CAT5-50F-OR-PLENUM Cat5 cable, 50ft, orange, plenum rated	640181727343	0.01		-

CX Lighting Control Panels

The CX Commercial Lighting Control Panel is a self-contained lighting control system that replaces conventional time clock and contractor combinations with a labor saving, simple and flexible module solution. CX provides a reliable standalone relay control solution to reduce energy consumption for small and intermediate size projects that are cost sensitive.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
CX042S042NN CX Lighting Control Panel, 4 relay 120/277V input, with 4-20A/1P elect. held normally open relays NEMA 1 surface enclosure standalone	640181200563	23.15		-
CX082S082NM CX Lighting Control Panel, 8 relay 120/277V input, with 8-20A/1P elect. held normally open relays NEMA 1 surface enclosure master	640181200624	22.4		-
CX082S083LM CX Lighting Control Panel, 8 relay 120/277V input, with 8-30A/1P latching relays NEMA 1 surface enclosure master	640181200631	24.2		-
CX162S162NM CX Lighting Control Panel, 16 relay 120/277V input, with 16-20A/1P elect. held normally open relays NEMA 1 surface enclosure master	640181200921	38.75		-

Emergency Lighting Units

Emergency Relays include UL924 applications for shunt or bypass and UL1008 applications for local transfer for 0-10V dimming applications.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
ALCR1277 UL924 Automatic Load Control Relay	640181727237	1.5		-

LightHAWK® Wall Switch Sensors

LightHAWK sensors combine state-of-the-art technology to provide precise control of lighting loads within small to medium sized areas. With the choice of either Manual-ON (Vacancy Sensor) or Automatic-ON (Occupancy Sensor), these energy-saving sensors are designed to control a broad range of lighting fixtures and ensure that lights will turn OFF automatically when motion is no longer detected. All LightHAWK sensors are designed to fit in standard decorator style wall plates.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
LHL-IRS1-G-WH LightHAWK LHL Series Passive Infrared Wall Switch Sensor, single circuit, 1 button, ground, 120/277VAC, 1000 Sq Ft, photocell, white	640181708861	0.35		-
LHRDCMTD2-G-WH LightHAWK Dual Technology, Dual Circuit, 2 buttons, ground 120/277V, white, switchable vacancy or occupancy mode	840141410302	0.35		-
LHRDCMTD2-N-WH LightHAWK Dual Circuit Neutral Multi-Technology Wall Switch Sensor with IntelliDAPT, dual circuit (two inputs/two outputs), 2 buttons, 120/277VAC, 1000 Sq Ft, photocell, white	840141410319	0.31		-
LHRDMIRS3-N-WH LightHAWK Dimmer Passive Infrared Wall Switch Sensor with IntelliDAPT, single circuit, 3 buttons, 120/277VAC, 1000 Sq Ft, photocell, white	840141410500	0.34		-
LHRDMMTS2-N-WH LightHAWK dimming Dual Technology, single relay, 2 button, 120/277V, white, switchable vacancy or occupancy mode	840141408996	0.36		-
LHRIRS1-G-WH LightHAWK Passive Infrared, single relay, 1 button, ground 120/277V, white, switchable vacancy or occupancy mode	840141410081	0.32		-
LHRIRS1-N-WH LightHAWK Passive Infrared, single relay, 1 button, neutral 120/277V, white, switchable vacancy or occupancy mode	840141408002	0.33		-
LHRMTS1-G-WH LightHAWK Dual Technology, single relay, 1 button, ground 120/277V, white, switchable vacancy or occupancy mode	840141407982	1.32		-
LHRMTS1-N-WH LightHAWK Dual Technology, single relay, 1 button, neutral 120/277V, white, switchable vacancy or occupancy mode	840141408989	0.31		-

Wallbox Devices

Wallbox Devices include low voltage dimmer switches, momentary and latching switches and digital timers making them the perfect solution for low voltage occupancy sensors, daylighting controls and networked lighting control panels.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
LVSD-M-3-WH Low voltage switch, momentary, 3 button, with pilot LED, raise-On/Off-lower, 0-10V control, 100mA, white	640181723055	0.2		-
LVSM1NPWH Low voltage switch, 1 button, momentary, no pilot, white	640181100269	2.5		-
PSD0108-UNV-WH Preset slide dimmer for 0–10V LED drivers and fluorescent and HID ballasts, single pole or 3-way, 10A@120VAC, 5A@277VAC, white	840141413129	0.18		-
RSD0108-UNV-WH Rocker-slide dimmer for 0-10V LED drivers and fluorescent and HID ballasts, 10A@120VAC, 5A@277VAC, 60Hz, single pole or 3-way, white	840141413150	0.18		-

NX Lighting Controls

The NX Lighting Controls platform delivers a seamless lighting control solution for both indoor and outdoor spaces. NX is capable of scaling from standalone fixture and room control applications to networked building deployments. NX operates using wired, wireless and hybrid connectivity with native BACnet™ support.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
NXDS NX Daylight Sensor	640181713384	2.5		N02WNCR6KTE
NXOFM2-1R1D-UNV NX On-Fixture module, 1 Relay 1 Dimmer, Universal Voltage (120V-480V)	840141433561	6.6 oz		N02WNCR6KTE
NXP2-PNL-16-16-9US NX Lighting Control Panel V2, UL924, 16 relay capacity,16 dimming channels, 16-20A/single pole latching relays, Bluetooth radio bridge with real time clock included, 120/277VAC, surface mount		9.13		N02WNCR6KTE
NXP2-PNL-16-16-U-S NX Lighting Control Panel V2, 16 relay capacity,16 dimming channels, 16-20A/single pole latching relays, Bluetooth radio bridge with real time clock included, 120/277VAC, surface mount	640181728739	9.13		N02WNCR6KTE
NXP2-PNL-24-24-9US NX Lighting Control Panel V2, UL924, 24 relay capacity,24 dimming channels, 24-20A/single pole latching relays, Bluetooth radio bridge with real time clock included, 120/277VAC, surface mount		21		N02WNCR6KTE
NXP2-PNL-24-24-U-S NX Lighting Control Panel V2, 24 relay capacity,24 dimming channels, 24-20A/single pole latching relays, Bluetooth radio bridge with real time clock included, 120/277VAC, surface mount	640181728753	21		N02WNCR6KTE
NXP2-PNL-8-8-9US NX Lighting Control Panel V2, UL924, 8 relay capacity, 8 dimming channels, 8-20A/single pole latching relays, Bluetooth radio bridge with real time clock included, 120/277VAC, surface mount		5.75		N02WNCR6KTE
NXP2-PNL-8-8-U-S NX Lighting Control Panel V2, 8 relay capacity, 8 dimming channels, 8-20A/single pole latching relays, Bluetooth radio bridge with real time clock included, 120/277VAC, surface mount	640181728715	5.75		N02WNCR6KTE
NXRCFX2-1RD-UNV NX Room Controller, FX Bus compatible, 1 relay, 0-10V dimming, universal voltage	640181727916	0.77		N02WNCR6KTE
NXRCFX2-2RD-UNV NX Room Controller, FX Bus compatible, 2 relay, 0-10V dimming, universal voltage	640181727909	0.77		N02WNCR6KTE
NXRCFX-UL924-UNV NX Emergency Lighting Room Controller, 1 relay, 0-10V dimming, one color channel, universal voltage	640181727923	0.77		N02WNCR6KTE
NXSMDT-OMNI NX Digital Smart Occupancy Sensor, ceiling mount, PIR/US	840141411491	0.42		N02WNCR6KTE
NXSW2-3-WH NX Digital Smart Switch, 3 button, momentary, pilot, white	840141413679	0.15		N02WNCR6KTE
NXSW2-5-WH NX Digital Smart Switch, 5 button, momentary, pilot, white	840141413693	0.15		N02WNCR6KTE

NX Lighting Controls (continued)

The NX Lighting Controls platform delivers a seamless lighting control solution for both indoor and outdoor spaces. NX is capable of scaling from standalone fixture and room control applications to networked building deployments. NX operates using wired, wireless and hybrid connectivity with native BACnet™ support.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
NXSW2-6-WH NX Digital Smart Switch, 6 button, momentary, pilot, white	840141413709	0.15		N02WNCR6KTE
NXSW2-OO-WH NX Digital Specialty Switch, On/Raise/Lower/Off, white	840141413747	0.15		N02WNCR6KTE
NXSW2-ORLO-WH NX Digital Specialty Switch, On/Raise/Lower/Off, white	840141413723	0.15		N02WNCR6KTE
NXSW2-SS-WH NX Digital Specialty Switch, scene switch, white	840141413761	0.15		N02WNCR6KTE
NXSW2–W1–WH NX Digital Smart Switch, Wireless, 1 button, white	840141439907	0.15		N02WNCR6KTE
NXSW2–W2–WH NX Digital Smart Switch, Wireless, 2 button, white	840141439921	0.15		N02WNCR6KTE
NXSW2–W3–WH NX Digital Smart Switch, Wireless, 3 button, white	840141439945	0.15		N02WNCR6KTE
NXSW2–W4–WH NX Digital Smart Switch, Wireless, 4 button, white	840141439969	0.15		N02WNCR6KTE
NXSW2–W5–WH NX Digital Smart Switch, Wireless, 5 button, white	840141439983	0.15		N02WNCR6KTE
NXSW2–W6–WH NX Digital Smart Switch, Wireless, 6 button, white	840141440002	0.15		N02WNCR6KTE
NXSW2–W8–WH NX Digital Smart Switch, Wireless, 8 button, white	840141440026	0.15		N02WNCR6KTE
NXSW2-WCCT-WH NX Digital Specialty Switch, Wireless, Color Control Switch, white	840141440101	0.15		N02WNCR6KTE
NXSW2-WOO-WH NX Digital Specialty Switch, Wireless, On/Off, white	840141440040	0.15		N02WNCR6KTE
NXSW2-WORLO-WH NX Digital Specialty Switch, Wireless, On/Raise/Lower/Off, white	840141440064	0.15		N02WNCR6KTE
NXSW2-WSS-WH NX Digital Specialty Switch, Wireless, Scene Switch, white	840141440088	0.15		N02WNCR6KTE

OMNI® Ceiling Sensors

The OMNI Ceiling Mount Occupancy/Vacancy Sensor is designed for medium to large spaces with ceilings up to 12' in height. The sensor is available with Ultrasonic and Passive Infrared technology for unequaled motion detection. Embedded smart IntelliDAPT® technology eliminates false triggers. The sensor has 500-2,000 square foot coverage area, depending on the model.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
OMNIDT2000 OMNI Passive Infrared & Ultrasonic Ceiling Sensor with IntelliDAPT, 360 degrees, 2000 Sq Ft, white	640181402868	0.45		-
OMNIDT2000RP OMNI Passive Infrared & Ultrasonic Ceiling Sensor with IntelliDAPT, 360 degrees, 2000 Sq Ft, relay & photocell, white	640181402912	0.45		-
OMNIDT500 OMNI Passive Infrared & Ultrasonic Ceiling Sensor with IntelliDAPT, 180 degrees, 500 Sq Ft, white	640181402660	2.38		-
OMNIIRLRP OMNI Passive Infrared Ceiling Sensor with IntelliDAPT, 360 degrees, 1500 Sq Ft, relay & photocell, white	640181403414	2.5		-
OMNIUS2000 OMNI Ultrasonic Ceiling Sensor with IntelliDAPT, 360 degrees, 2000 Sq Ft, white	640181403162	0.45		-

Power Packs and Controlled Relays

Power Packs, Relays and Controlled Receptacles are self-contained devices that provide ON/OFF circuit control and are designed to work with low-voltage occupancy sensors.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
UVPPHD+ Heavy Duty Universal Voltage Power Pack with automatic or manual ON operation	840141417547	1	20	-

WASP Fixture Sensors

The WASP Fixture Sensor is specifically designed for ON/OFF and 0-10V dimming control of high mount/low mount fixtures in warehouses, distribution centers and similar facilities. The sensor is available in end mount and surface mount versions. Also available in an IP65 version.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
WSP-EM-UNV WASP Sensor, end mount, 120/277/347 VAC	640181200839	0.55	10	-
WSP-L360-WH WASP Sensor Lens, high mount, 360-degree coverage area, white	640181708298	2.5	50	-
WSP-SM-24V WASP Sensor, surface mount, 24VDC	640181200457	0.55	10	-

SRT

prescolite

Delivers downlighting solutions that are used in applications ranging from residential spaces to demanding architectural environments - always with an emphasis on performance, flexibility, quality and ease of installation.

ENERGY STAR® certified models available (For list and additional information, visit http://www.energystar.gov)

LiteBox® Edge-Lit

LiteBox® Edge-Lit is a low-profile surface-mount downlighting family that affordably combines Edge-Lit technology and contemporary appearance with ease of installation and functional versatility.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
LBSE-4RD-30K8-WH 4" Surface Downlight, Round, 750 lumens, 3000K, 80+ CRI, 0-10V/Triac/ELV dimming driver, 120-277V, white	840141400662	2	12	-
LBSE-4RD-35K8-WH 4" Surface Downlight, Round, 750 lumens, 3500K, 80+ CRI, 0-10V/Triac/ELV dimming driver, 120-277V, white	840141400679	2	12	-
LBSE-6RD-30K8-WH 6" Surface Downlight, round, direct J-box mount, 1100 lumens, 3000K, 80+ CRI, 0-10V/Triac/ELV dimming driver, 120-277V, white	840141400686	2	12	-
LBSE-6RD-35K8-WH 6" Surface Downlight, round, direct J-box mount, 1100 lumens, 3500K, 80+ CRI, 0-10V/Triac/ELV dimming driver, 120-277V, white	840141400693	2	12	-
LBSES-4RD-CS9-WH 4" Surface Downlight, round, direct J-box mount, 750 lumens, Switchable CCT (2700/3000/3500/400K), 90 CRI, 0-10V/Triac/ELV dimming driver, 120-277V, white	840141400723	2	12	-
LBSES-6RD-CS9-WH 6" Surface Downlight, round, direct J-box mount, 1100 lumens, Switchable CCT (2700/3000/3500/400K), 90 CRI, 0-10V/Triac/ELV dimming driver, 120-277V, white	840141400730	2	12	-

LiteBox® Standard

LiteBox® Standard is an install-from-below downlight family for retrofit, remodel or new construction applications. Standard features include switchable lumen output and color temperature for maximum application flexibility.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
LBRST-4RD-M-LSSL-CS9-WH-34 4" Downlight, round, Switchable Lumen (750/1100/1500lm), Switchable CCT (2700/3000/3500/4000/5000K), 90 CRI, tri-dimming (0-10V/TRIAC/ELV), 120-347V, white	840141413341	1.1	8	-
LBRST-4RD-M-LSSL-CS9-WH-EMR 4" Downlight, round, Switchable Lumen (750/1100/1500lm), Switchable CCT (2700/3000/3500/4000/5000K), 90 CRI, tri-dimming (0-10V/TRIAC/ELV), 120-277V, white, EMR Emergency Battery Ready	840141413280	1.1	8	-
LBRST-6RD-M-LSML-CS9-WH-34 6" Downlight, round, Switchable Lumen (1100/1500/2500lm), Switchable CCT (2700/3000/3500/4000/5000K), 90 CRI, 0-10V/TRIAC/ELV dimming to 5%, 120-347V, white	840141413358	2	12	-
LBRST-6RD-M-LSML-CS9-WH-EMR 6" Downlight, round, Switchable Lumen (1100/1500/2500lm), Switchable CCT (2700/3000/3500/4000/5000K), 90 CRI, tri-dimming (0-10V/TRIAC/ELV), 120-277V, white, EMR Emergency Battery Ready	840141413297	1.2	12	-
LBRST-8RD-M-LSHL-CS9-WH 8" Downlight, round, Switchable Lumen (3000/4000/4600lm), Switchable CCT (2700/3000/3500/4000/5000K), 90 CRI, tri-dimming (0-10V/TRIAC/ELV), 120-277V, white	840141413303	1.3	8	-
LBRST-8RD-M-LSHL-CS9-WH-34 8" Downlight, round, Switchable Lumen (3000/4000/4600lm), Switchable CCT (2700/3000/3500/4000/5000K), 90 CRI, tri-dimming (0-10V/TRIAC/ELV), 120-347V, white	840141413365	1.3	8	-

LiteBox® Pro

LiteBox® Pro is an install-from-below downlight family for new construction or remodel applications. Standard features include switchable lumen output, color temperature, and dial-in beam angle for maximum application flexibility.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
FRAME4R-HB Accessory, pan w/bar hangers for T-grid/joist, 4" round	840141432564	2.5	12	-
FRAME6R-HB Accessory, pan w/bar hangers for T-grid/joist, 6" round	840141432571	2.5	12	-
FRAME8-HB Accessory, pan w/bar hangers for T-grid/joist, 8" round or square	840141432601	1.7	12	-
LBRP-4RD-T-DWT 4" Downlight Trim, Round, clear anodized diffuse cone, white flange	840141410456	0.6	8	-
LBRP-4RD-T-WC 4" Downlight Trim, Round, white cone, white flange	840141407647	0.6	8	-
LBRP-6RD-T-DWT 6" Downlight Trim, round, clear anodized diffuse cone, white flange reflector	840141410463	0.9	8	-
LBRP-6RD-T-WC 6" Downlight Trim, Round, white cone, white flange	840141407661	0.9	8	-
LBRP-8RD-T-DWT 8" Downlight Trim, Round, clear anodized diffuse cone, white flange	840141410470	1.4	8	-
LBRP-8RD-T-WC 8" Downlight Trim, Round, white cone, white flange	840141407685	1.4	8	-
LBRP-M-LSHL35K9-WD High Lumen LED Module, Switchable Lumen (4000/4500/5500lm), 3500K, 90 CRI, 0-10V dimming, 120-277V	840141413006	3.6	8	-
LBRP-M-LSHL40K9-WD High Lumen LED Module, Switchable Lumen (4000/4500/5500lm), 4000K, 90 CRI, 0-10V dimming, 120-277V	840141413013	3.6	8	-
LBRP-M-LSMLCS9-WD Medium Lumen LED Module, Switchable Lumen (1900/2300/2700lm), Switchable CCT (2700/3000/3500/4000/5000K), 90 CRI, 0-10V dimming, 120-277V	840141412979	2.9	8	-
LBRP-M-LSSLCS9-WD Standard Lumen LED Module, Switchable Lumen (700/1050/1400m), Switchable CCT (2700/3000/3500/4000/5000K), 90 CRI, 0-10V dimming, 120-277V	840141435374	2.9	8	-

Accessories

Optional bar hanger accessories provide a means of tightly securing the fixture to standard T-bar grid supports, saving the contractor installation time.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
B24 Accessory, bar hangers 24" for T-bar ceilings, set of 2	785235103633	0.5	20	-

LiteFrame 2.0

LiteFrame® 2.0 is a high performance commercial downlight family featuring a broad breadth of round and square fixtures, beam options, and installation flexibility.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
LFR-4RD-H Accessory, 4" Chicago Plenum Housing, New Construction, round	840141405896	2.6	12	-
LFR-4RD-H-CP 4" Housing, New Construction, Round, Chicago Plenum	840141412269	11.9	6	-
LFR-4RD-M-10L35K8-XW-DM1 4" Downlight Module, Round, 1000 lumens, 80+ CRI, 3500K, 60 degree beam, 0-10V 1% dimming, 120-277V	840141406831	3.2	1	-
LFR-4RD-M-15L35K8-WD-DM1-CP 4" Downlight Module, Round, 1500 lumens, 80+ CRI, 3500K, 48 degree beam, 0-10V 1% dimming, 120-277V, Chicago Plenum	840141412290	3.4	1	-
LFR-4RD-M-15L35K8-XW-DM1 4" Downlight Module, Round, 1500 lumens, 80+ CRI, 3500K, 60 degree beam, 0-10V 1% dimming, 120-277V	840141406848	3.3	1	-
LFR-4RD-T-S 4" Downlight Trim, round, NR/MD/WD/XW, specular clear reflector	840141406558	0.3	72	-
LFR-4RD-T-SS 4" Downlight Trim, round, NR/MD/WD/XW, semi-specular clear reflector	840141406565	0.3	72	-
LFR-4SQD-H Accessory, 4" Housing Frame, New Construction, square	840141408507	2.6	12	-
LFR-6RD-H Accessory, 6" Housing Frame, New Construction, round	840141405902	2.5	12	-
LFR-6RD-H-CP 6" Housing, New Construction, Round, Chicago Plenum	840141412351	11.9	6	-
LFR-6RD-M-10L35K8-XW-DM1 6" Downlight Module, Round, 1000 lumens, 80+ CRI, 3500K, 60 degree beam, 0-10V 1% dimming, 120-277V	840141407012	3.2	1	-
LFR-6RD-M-15L35K8-WD-DM1-CP 6" Downlight Module, Round, 1500 lumens, 80+ CRI, 3500K, 48 degree beam, 0-10V 1% dimming, 120-277V, Chicago Plenum	840141412399	3.8	1	-
LFR-6RD-M-15L35K8-XW-DM1 6" Downlight Module, Round, 1500 lumens, 80+ CRI, 3500K, 60 degree beam, 0-10V 1% dimming, 120-277V	840141407029	3.8	1	-
LFR-6RD-T-S 6" Downlight Trim, round, NR/MD/WD/XW, specular clear reflector	840141406633	0.5	54	-
LFR-6RD-T-SS 6" Downlight Trim, round, NR/MD/WD/XW semi-specular clear reflector	840141406640	0.5	54	-
LFR-6SQD-H 6" Housing, New Construction, Square	840141408514	2.6	12	-

LITEISTRY™

LITEISTRY provides a broad palette of architectural downlighting solutions with consistent aperture appearance, quiet ceiling design and exceptional optical performance.

Catalog # Description	UPC Code	Lbs. Each	Carton QTY	DLC
LTR-4RD-H-ML20L-DM1 4" Downlight Housing, New Construction, round, medium lumen, 2000 lumens, 0-10V 1% dimming driver, 120-277V	785235433013	4.9	2	-
LTR-4RD-H-SL10L-DM1 4" Downlight Housing, New Construction, round, standard lumen, 1000 lumens, 0-10V 1% dimming driver, 120-277V	785235433037	4.9	2	-
LTR-4RD-H-SL15L-DM1 4" Downlight Housing, New Construction, round, standard lumen, 1500 lumens, 0-10V 1% dimming driver, 120-277V	785235433044	4.9	2	-
LTR-4RD-H-SL15L-DM1CP 4" Downlight Housing, New Construction, round, standard lumen, 1500 lumens, 0-10V 1% dimming driver, 120-277V, Chicago Plenum	785235433600	13.8	1	-
LTR-4SQD-H-ML20L-DM1 4" Downlight Housing, New Construction, square, medium Lumen, 2000 lumens, 0-10V 1% dimming driver, 120-277V	785235433334	4.9	2	-
LTR-4SQD-H-SL10L-DM1 4" Downlight Housing, New Construction, square, standard lumen, 1000 lumens, 0-10V 1% dimming driver, 120-277V	785235433365	4.9	1	-
LTR-4SQD-H-SL15L-DM1 4" Downlight Housing, New Construction, square, standard lumen, 1500 lumens, 0-10V 1% dimming driver, 120-277V	785235433372	4.9	2	-
LTR-6RD-H-ML20L-DM1 6" Downlight Housing, New Construction, round, medium Lumen, 2000 lumens, 0-10V 1% dimming driver, 120-277V	785235433174	4.8	2	-
LTR-6RD-H-ML30L-DM1 6" Downlight Housing, New Construction, round, medium Lumen, 3000 lumens, 0-10V 1% dimming driver, 120-277V	785235433136	4.8	2	-
LTR-6RD-H-SL10L-DM1 6" Downlight Housing, New Construction, round, standard lumen, 1000 lumens, 0-10V 1% dimming driver, 120-277V	785235433150	4.8	2	-
LTR-6RD-H-SL15L-DM1 6" Downlight Housing, New Construction, round, standard lumen, 1500 lumens, 0-10V 1% dimming driver, 120-277V	785235433167	4.8	2	-
LTR-6RD-H-SL15L-DM1CP 6" Downlight Housing, New Construction, round, standard lumen, 1500 lumens, 0-10V 1% dimming driver, 120-277V, Chicago Plenum	840141402321	13.8	1	-
LTR-6SQD-H-SL15L-DM1 6" Downlight Housing, New Construction, square, standard lumen, 1500 lumens, 0-10V 1% dimming driver, 120-277V	785235433488	4.8	2	-

DOWNLIGHTS
PRODUCT SELECTION GUIDE

VALUE

		LiteBox® Edge-Lit LBSE/LBSES	LiteBox® Standard LBRST	LiteBox® Pro LBRP
FEATURES	**Mounting**	Surface	Recessed	Recessed
	Aperture	4/6/8	4/6/8	4/6/8
	Style	Round/Square	Round	Round/Square
	New Construction/ Retrofit	Both	Both	Both
	IC/Non-IC	Both	Both	Both
	Lumen Range	750/1100/1750 lumens	750-4600 lumens	700-5500 lumens
	Efficacy (lp/w)	75-99	76-106	82-103
	Watts	10.4-20	9-49	9-57
LISTINGS AND CERTIFICATIONS	**CRI**	80	90	90
	CCT	3000K 3500K	2700K 3000K 3500K 4000K 5000K	2700K 3000K 3500K 4000K 5000K
	Dimming	0-10V/TRIAC/ELV	0-10V/TRIAC/ELV	0-10V/TRIAC/ELV
	Switchable Technology	n/a	CCT	Lumens/CCT
	Colors	White	White	Diffuse/White

COMMERCIAL SPECIFICATION

LiteFrame® 2.0 **LFR**	**LITEISTRY™** **LTR**
Recessed	Recessed
4/6	3/4/6
Round/Square	Round/Square
Both	Both
Both	Both
1000-8000 lumens	600-9000 lumens
118-139	87-99
8-71	8-99
80/90	80/90
2700K 3000K 3500K 4000K 5000K	2700K 3000K 3500K 4000K 5000K
0-10V/TRIAC/ELV	0-10V/TRIAC/ELV/DALI/DMX
N/A	N/A
Specular/Semi-Specular/White	Anodized & Painted

ENERGY STAR® certified models available (For list and additional information, visit http://www.energystar.gov)

Current

Current - HLI Brands

701 Millennium Blvd.
Greenville, SC 29607

currentlighting.com

© 2025 HLI Solutions, Inc. All rights reserved. Information and specifications subject to change without notice.
All values are design or typical values when measured under laboratory conditions.

Rev 05/16/25

HLI-tradeSELECT