

BMP®21-PLUS LABEL PRINTER

BMP®21-LAB / BMP®21

LABEL SELECTION GUIDE

Wire/Cable Markers

Shelves

Tools

Bins/Containers

Faceplates

Electrical Panels

Patch Panels

Terminal Blocks

Instruments

Racks

Tubes/Vials

Bottles/Flasks/Dishes

www.BradyID.com/bmp21plus



BMP®21-PLUS LABEL PRINTER

BMP®21-LAB / BMP®21

MATERIAL SELECTION GUIDE

BMP®21-PLUS / BMP®21-LAB / BMP®21 Label Printer features multiple materials for a variety of applications.

GENERAL POLYESTER



IDEAL FOR:

- Components and other flat surfaces
- Instruments
- Racks & bins
- General labeling

Color	0.250" x 21' *	0.375" x 21'	0.500" x 21'	0.750" x 21'
Black on White	M21-250-423	M21-375-423	M21-500-423	M21-750-423
Black on Clear	M21-250-430	M21-375-430	M21-500-430	M21-750-430
White on Clear	M21-250-430-WT-CL	M21-375-430-WT-CL	M21-500-430-WT-CL	M21-750-430-WT-CL

* Only works in BMP®21-PLUS and BMP®21-LAB Label Printers.

SELF-LAMINATING VINYL




IDEAL FOR:

- Marking terminated or un-terminated wires
- Wire markers needing abrasion/chemical resistance

Color	0.750" x 14'	1.000" x 14'	1.250" x 14'	1.500" x 14'
Black on White	M21-750-427	M21-1000-427	M21-1250-427	M21-1500-427

PERMASLEEVE® HEAT SHRINK WIRE MARKERS



IDEAL FOR:

- Un-terminated wires
- Professional looking wire identification
- Meeting SAE-AS-81531, MIL-STD-202G, RoHS 2005/618/EC standards

Color	0.125" x 7'	0.187" x 7'	0.250" x 7'	0.375" x 7'
Black on White	M21-125-C-342	M21-187-C-342	M21-250-C-342	M21-375-C-342
Black on Yellow	M21-125-C-342-YL	M21-187-C-342-YL	M21-250-C-342-YL	M21-375-C-342-YL

INDOOR AND OUTDOOR GRADE VINYL



IDEAL FOR:

- Shelves
- Round surfaces
- Tools
- Containers
- Bins
- Rough or uneven surfaces
- Instruments
- Panels

Color	0.250" x 21' 	0.375" x 21'	0.500" x 21'	0.750" x 21'
Black on White	M21-250-595-WT	M21-375-595-WT	M21-500-595-WT	M21-750-595-WT
Black on Yellow	M21-250-595-YL	M21-375-595-YL	M21-500-595-YL	M21-750-595-YL
Black on Orange	—	M21-375-595-OR	M21-500-595-OR	M21-750-595-OR
White on Red	—	M21-375-595-RD	M21-500-595-RD	M21-750-595-RD
White on Blue	—	M21-375-595-BL	M21-500-595-BL	M21-750-595-BL
White on Green	—	M21-375-595-GN	M21-500-595-GN	M21-750-595-GN
White on Purple	—	M21-375-595-PL	M21-500-595-PL	M21-750-595-PL
White on Brown	—	M21-375-595-BR	M21-500-595-BR	M21-750-595-BR
Black on Gray	—	M21-375-595-GY	M21-500-595-GY	M21-750-595-GY
White on Black	—	M21-375-595-BK	M21-500-595-BK	M21-750-595-BK

** Only works in BMP®21-PLUS and BMP®21-LAB Label Printers.*

NYLON CLOTH



IDEAL FOR:

- Wrap around wire and cable identification
- Patch panels
- Terminal blocks
- Vials and tubes

Color	0.375" x 16'	0.500" x 16'	0.750" x 16'
Black on White	M21-375-499	M21-500-499	M21-750-499
Terminal Block	M21-375-499-TB	M21-500-499-TB	

LAB POLYESTER / POLYPROPYLENE



IDEAL FOR:

- Tubes and vials
- Bottles and flasks
- Lab supplies

Color	0.375" x 21'	0.500" x 21'	0.750" x 21'
Black on White	M21-375-461	M21-500-461	M21-750-461
Black on White	M21-375-488	M21-500-488	M21-750-488
Black on White	M21-375-7425	M21-500-7425	M21-750-7425

6555 W. Good Hope Rd.
Milwaukee WI, 53223
1-888-272-3946

 **BRADY**
WHEN PERFORMANCE MATTERS MOST™