

The AIPHONE logo is located in the top left corner. It consists of a circular icon with a stylized 'A' inside, followed by the word 'AIPHONE' in a bold, sans-serif font.

AIPHONE

The main title is centered in the lower half of the image. It features the text 'IX | IXG SERIES' in a large, white, serif font, with 'IP VIDEO INTERCOM' in a smaller, white, sans-serif font directly below it. The background is a modern building entrance with wood paneling and glass doors.

IX | IXG SERIES

IP VIDEO INTERCOM

The tagline 'UNCOMPROMISED SECURITY' is located in the bottom right corner, enclosed within an orange rectangular box. The text is white and in a sans-serif font.

UNCOMPROMISED SECURITY

IX | IXG SERIES
QR CODE
VISITOR ACCESS PASS





IX | IXG SERIES

IP VIDEO INTERCOM

Transform communication and security with the **IX | IXG Series**, the most powerful and customizable IP video intercom solution on the market. Designed to cover commercial, multi-tenant, and mixed-use environments, the solution offers a wide range of door stations, answering stations, and emergency options to meet the needs of any property. The IX | IXG app provides a frictionless experience for users and visitors to see, speak, and unlock doors.


Elevate your access control to an enterprise level by integrating the IX | IXG with the **AC Series**. The AC Series allows for centralized management of entries, streamlined credentialing, and access control to every door.



IX | IXG SERIES

CREATING A COMPREHENSIVE SECURITY ECOSYSTEM

Engineered with purpose, leveraging industry standards like SIP and ONVIF allows the IX | IXG seamlessly integrate with all layers of security infrastructure, including IP cameras and VMS solutions.





VIDEO TENANT STATION
Tenants inside the building can communicate with visitors outside the building.

EMERGENCY WALL BOX
Provides critical communication in emergencies, ensuring tenant safety

VIDEO DOOR STATION
Welcomes visitors with a secure, modern video entry experience, built to withstand harsh weather

PC ANSWERING STATION SOFTWARE
Centralizes visitor management and monitoring on computer desktops

VIDEO ANSWERING STATION
Convenient two-way communication

IX-DVM VIDEO DOOR STATION
Streamlines visitor access with video identification and touchless calling

MOBILE APP
Empower tenants with remote access and communication on their mobile devices

DOOR STATIONS

Secure your premises with the IX | IXG Series, built to the highest standards for integration and reliability.

DURABLE DESIGN, WEATHERPROOF PERFORMANCE

Built to withstand the harshest conditions, the IX | IXG series features IP65 and IK08 certified durability, providing robust protection against weather and vandalism. This ensures reliable performance in any environment. With a variety of mounting options, these devices seamlessly blend into your building's aesthetic.

SEAMLESS INTEGRATION FOR THE ULTIMATE PROTECTION

Our intercoms are SIP and ONVIF compliant, allowing seamless integration with leading providers of IP cameras, video management systems, and access controls. This open architecture empowers you to build a customized security ecosystem that evolves alongside your needs.



IXG-DM7-HID/A
IP Video Door Station
with HID® Card Reader

- Customizable 7-inch touchscreen
- Flexible Tenant Directory
- QR Code Access
- Built-in HID Reader
- Tamper sensor
- IK08 / IP65
- 13-11/16" H x 7-3/16" W



IX-DV
IP Video Door Station

- HD Camera
- PoE Passthrough
- 6 contact outputs, 2 inputs
- IK08 / IP65
- 8-1/16" H x 4-1/2" W



IX-DVF-L



IX-DVF-HW



IXW-HWCBP



IX-DVF-PR



IX-EA
1-Gang Surface Mount
IP Video Door Station

- HD Camera
- Compact and lightweight design
- Manually Adjustable Camera
- 1 contact output, 1 input
- IK06 / IP54
- 6-5/16" H x 3-15/16" W



IX-DVM
Mullion-mount
IP Video Door Station

- WDR HD Camera
- Mullion mountable
- Optional Touchless Calling
- 1 contact output, 1 input
- IK07 / IP54
- 1-7/8" W x 1-5/16" L x 6-7/8" H



IX-DVF
IP Video Door Station

- HD Camera
- PoE Passthrough
- Flush mountable
- 6 contact outputs, 2 inputs
- IK08 / IP65
- 10-7/16" H x 5-7/8" W



IX-SS-2G
Audio Door Station

- Audio-only
- 2-Gang, flush mountable
- Audio output for paging
- 1 contact output, 1 input
- IK08 / IP65
- 4-3/4" H x 4-3/4" W



IX-DVF-10KP



IX-DVF-4A



IX-DVF-6



IX-NVP



IX-NVP2

ANSWERING STATIONS

With the IX | IXG Series, you have the flexibility to communicate and unlock doors using answering stations, VoIP phones, mobile apps, and PCs.

INTUITIVE EXPERIENCE

The home screen offers quick access to essential functions like monitoring, call history, favorites, status, settings, and paging.

CALL TRANSFERS

Its versatile call transfer options include transferring active calls, automatic forwarding when absent, transferring unanswered calls after a set time, and convenient scheduling options.

MONITORING AND RECORDING

The answering station monitors and records video from connected door stations and network cameras.

DOOR RELEASE

Tie directly to electric locks or integration with access control solutions to enable remote unlocking of doors from the answering station.

IXGW-TGW CLOUD GATEWAY

Our Cloud Gateway allows you to answer video intercom calls and remotely unlock doors using your mobile device, either through the IXG mobile app or a regular phone call. It provides a reliable LTE connection via a SIM card for seamless communication, even if your primary network is down.



IX-MV7-HB
IX-MV7-HW

Touchscreen answering stations with handset

- 7" touchscreen
- T-Coil hearing aid supported handset
- 8 customizable speed dial buttons
- 2 contact outputs, 4 trigger inputs
- Audio and video recording
- Wall or desk mounted



IXG MOBILE APP

- Video calling and answering
- Remote door release
- Intuitive user interface
- Generate temporary QR code access



IX-RS-B
IX-RS-W



IXG-2C7



IX-MV7-HW-JP

ACCESSORIES



**IX-MV7-B
IX-MV7-W**

Touchscreen answering stations

- 7" touchscreen
- 8 customizable speed dial buttons
- 2 contact outputs, 4 trigger inputs
- Audio and video recording
- Wall or desk mounted



IX-SOFT

PC Answering Station Software

- Complete answering station features
- 50 highly customizable speed dials
- Record custom message pages
- Interactive map
- Line Supervision and Device Check



IXGW-TGW

Cloud Gateway

- PoE
- DIN rail mountable
- Eight simultaneous calls per adaptor
- Supports up to 9,999 mobile apps
- Available 4G LTE data connection
- Allows telephone calls from door and entrance stations



IXW-MAA

Multi-Purpose Relay Adaptor

- 802.3af PoE
- Ten Form C relay outputs
- Four contact inputs
- 24V AC/DC 500mA relay contact rating
- Mountable to a 170mm DIN rail or directly to a wall



IPW-1VC

- 2-wire to Ethernet Adaptor
- Provides PoE w/ included power supply
- Up to 1,000' on 22AWG wire
- Call up to 5 master stations up to 500'
- Call up to 3 master stations up to 1000'



IXW-PBXA

IP PBX

- Simple IP PBX
- Register up to 500 Devices
- Supports Analog and SIP Trunk Connections to PSTN



IX-MB



SBX-IXDV30



SBX-IDVF



DBX-IDVFRA



SBX-IXGDM7



SBX-2G/A

EMERGENCY PRODUCTS

We provide a single security communication platform, offering ADA compliant emergency towers, wall boxes and stations.



IX-SSA-2RA

- ADA compliant raised lettering and Braille signage
- Buttons for standard & emergency calls
- PoE pass through
- 2 contact outputs; 6 trigger inputs
- IK08 / IP65
- 11-11/16" H x 7" W



IX-DVF-2RA

- HD Camera
- ADA compliant raised lettering and Braille signage
- Buttons for standard & emergency calls
- PoE pass through
- 2 contact outputs; 6 trigger inputs
- IK08 / IP65
- 11-11/16" H x 7" W



IX-DVF-RA



IX-SSA-RA



WB-HE WB-HA

- 12-Gauge stainless steel
- ADA Compliant 4" depth
- Each box includes a UL Listed electrical box for installing an AC outlet, and a bracket to install a power supply internally
- 27" H x 10-13/16" W x 4" D



TW-SA TW-SE

- UL-514-A listed electrical box included at the base
- ADA compliant intercom mounting height
- Beacon/Strobe is always lit; flashes during emergency call-in
- LED for station illumination in station over-hang
- 73" H x 8" W x 8" D

TW-TA TW-TE



TW-TA-ARM TW-TE-ARM

- Camera arm with universal pipe threading
- UL-514-A listed electrical box included at the base
- ADA compliant intercom mounting height
- Strobe is always lit; flashes during emergency call-in
- LED for station illumination in station over-hang
- 174" H x 8" W x 15-3/4" D



WB-CA



WB-CE



WB-HA



TWS-Z4
Sets also available
for Zones 1 and 2

French versions available:
IX-DVF-2RA-FR,
IX-DVF-RA-FR,
IX-SSA-2RA-FR,
IX-SSA-RA-FR

TECHNOLOGY PARTNERS



CHOSEN BY THOUSANDS OF ORGANIZATIONS



 **AIPHONE**.com

info@aiphone.com for sales inquiries