



IN-WALL BOX SOLUTIONS



PEERLESS-AV IN-WALL BOX SOLUTIONS



IBA4-W



IBA5-W



IBA3-W
(13.1 x 4.4")



IB14X9-W
IB14X9-AC-W



IB14X14-W
IB14X14-AC-W

PRODUCT SPECIFICATIONS - FEATURES & BENEFITS

IB14X9-W and IB14X14-W

REMOVABLE TRIM RING


Allows pre-construction or retrofit installations on 3/8"-3/4" drywall

DRYWALL CLAMPS

Allows the in-wall box to be installed in drywall, unsupported by studs

MODULAR MOUNTING PLATES

Removable top and bottom plates ease installation by allowing wiring terminations to take place outside the box



IBMP ACCESSORY

Optional component panel secures media players or other AV components

MULTIPLE RECEPTACLES


Mount up to 4 duplex receptacles

ACCEPTS MULTIPLE CONDUIT SIZES


3/4", 1", 1 1/4" and 1 1/2"
Conduit knock-outs

FLEXIBLE INSTALLATIONS

IB14X9-W and IB14X14-W



Retrofit




New Construction



IB14X9-W




IB14X14-W




Removable
Trim Ring

MULTIPLE STUD SPACING


IB14X9-W and IB14X14-W



Between 16" Studs
(25 lbs. load)





Attached to a Single Stud
(25 lbs. load)



Drywall Only
(25 lbs. load)

SPEED OF INSTALLATION



IB14X9-W and IB14X14-W



- Modular Mounting Plates prevent damaging the in-wall box when knocking-out sections for conduit or junction boxes
- Allows electricians to work away from the wall, speeding up installation.

IBMP COMPONENT ACCESSORY

Compatible with IB14X9-W, IB14X14-W, IM747PU and IM771PU



- Double stack multiple components on the inside and outside of the IBMP to make the most use out of your in-wall box
- Easily install or remove the IBMP with a single screw

IN-WALL BOX COVERS

Compatible with IB14X9(AC)-W and IB14X14(AC)-W

REMOVABLE KNOCK-OUTS FOR CABLE ENTRY + VENTILATION

Easily remove the (4) knock-outs by bending them back and forth

FULLY BONDED COVER

All hardware is bonded for safety


REMOVABLE PLUGS FOR EXTERNAL WIFI ANTENNA

Easily connect a RP-SMA external WIFI antenna with up to a .33" (8mm) diameter opening

SLEEK DESIGN

Color matches Peerless-AV® In-Wall Box models for a complete installation


IB14X9C-W: 14"x9" In-Wall Box Cover for IB14X9(-AC)-W In-Wall Boxes
IB14X14C-W: 14"x14" In-Wall Box Cover for IB14X14(-AC)-W In-Wall Boxes




PEERLESS-AV IN-WALL BOX FAMILY

IBA4-W


- Low Voltage Cable Plate
- Mounting Wings secure the box to drywall
- Installs vertically or horizontally



SIDE VIEW



Ideal for running HDMI from a receiver through the wall to a TV above it.





PEERLESS-AV IN-WALL BOX FAMILY


Ideal for running HDMI from a receiver through the wall to a TV above it.
Power is located behind the TV for a completely clean look.

IBA5-W


- Low Voltage Cable Plate
- Duplex Surge Protector
- Mounting Wings secure the box to drywall
- Installs vertically or horizontally




PEERLESS-AV IN-WALL BOX SOLUTIONS



IM747PU



IM771PU



IM746P



IM760PU

PRODUCT SPECIFICATIONS - FEATURES & BENEFITS

In-Wall Box Family – IM747PU

FLEXIBLE MOUNTING

Includes both 400x400 and 600x400 adaptor brackets

Perfect solution for ADA compliant installations

FULL EXTENSION

Articulating mount extends up to 25.0", providing room for servicing equipment



OPEN ACCESS


Articulating mount provides completely open access to AV equipment – no obstructions!

IB14X14-W

Includes UL2416 in-wall box

HEAVY DUTY TRIM RING

Included trim ring mounts independently than the in-wall box and provides solid support out to 16" stud centers



IBMP ACCESSORY

Optional component panel secures media players or other AV components

PRODUCT SPECIFICATIONS - FEATURES & BENEFITS

In-Wall Box Family – IM771PU

FLEXIBLE MOUNTING

Includes VESA adaptor for up to 800x400 mounting patterns

Perfect solution for ADA compliant installations


FULL EXTENSION

Articulating mount extends up to 25.0", providing room for servicing equipment



OPEN ACCESS

Articulating mount provides completely open access to AV equipment – no obstructions!



IBMP ACCESSORY

Optional component panel secures media players or other AV components

IB14X14-W

Includes UL2416 in-wall box

HEAVY DUTY TRIM RING

Included trim ring mounts independently than the in-wall box and provides solid support out to 16" stud centers

FULL SERVICE MOUNTS AND IN-WALL BOX

For larger interactive displays



DS-VW795-QR



IB14X14-AC-W

peerless-AV[®]

THANK YOU

We're social – Interact with us on your favorite social media site!



630.375.5100



info@peerless-av.com



peerless-av.com



twitter.com/peerlessav (@peerlessav)



YouTube

youtube.com/c/peerlessav



facebook.com/peerlessav



blog.peerless-av.com



linkedin.com/company/peerless-av



instagram.com/peerlessav