


V-FIT® Full-Body Harness




Superior Comfort



Using a patent-pending RaceFLEX™ connection, webbing is routed across the chest for a secure and comfortable fit—eliminating the need for bulky chest straps or cumbersome buckles.



Shoulder padding responds to your movement to conform to your body, eliminating pressure points and chafing. Shoulder padding can be removed for cleaning, extending the life of the harness.




Patented leg strap design keeps leg straps in place as webbing lays horizontally across the thighs, creating a more natural fit.

Flexibility



The RaceFLEX Buckle creates an athletic cut contouring the harness to the body and improving upper torso movement on the job.


Adjustability



Pull-down adjustment allows you to quickly and easily get the right fit that lasts throughout the work day.



Dedicated attachment point for Personal Fall Limiters allows for quick and easy attachment, and keeps your back D-ring free for other use.



WE KNOW WHAT'S AT STAKE.

MSA V-FIT Full-Body Harness



V-FIT Standard Full-Body Harness



V-FIT Construction Full-Body Harness



V-FIT Standard Full-Body Harness w/Front D-Ring



V-FIT Tower Full-Body Harness w/Front D-Ring

The V-FIT Harness' adjustable waist pad allows you to position the waist pad specifically for you and your work day. With it's patent pending design, the V-FIT waist pad can be adjusted higher on your torso for lumbar support or lower for work positioning applications. Designed around pressure points and by choosing breathable materials, the V-FIT waist pad delivers ultimate on-the-job comfort.

In addition to features found on other V-FIT Harnesses, the V-FIT Tower Harness adds an adjustable and removable padded saddle that can be stored when not in use for increased maneuverability. The saddle also includes two large gear rings, and two color differentiated D-rings for work positioning. Combined with the V-FIT construction waist pad, the V-FIT Tower Harness ensures ultimate comfort for long shifts at height.



ft.	(m)														
6'-6"	(2.0)														
6'-4"	(1.9)														
6'-2"	(1.9)														
6'-0"	(1.8)														
5'-10"	(1.8)														
5'-8"	(1.7)														
5'-6"	(1.7)														
5'-4"	(1.6)														
5'-2"	(1.6)														
5'-0"	(1.5)														
		110	130	150	170	190	210	230	250	270	290	310	330	400	
		(50)	(59)	(68)	(77)	(86)	(95)	(105)	(114)	(123)	(132)	(141)	(150)	(181)	

V-FIT Standard Full-Body Harness

Part Number	Size				D-Ring Configuration				Leg Straps		Padding			Standards		
	XSM	STD	XLG	SXL	Back	Back & Hips	Back, Shoulder	Back, Hip, & Shoulder	Tongue Buckle	Quick-Connect	None	Shoulder	Shoulder & Leg	ANSI Z359.11	CSA Z259.10	OSHA
10194536	■				■					■		■		■	■	■
10194630		■			■					■		■		■	■	■
10194671			■		■					■		■		■	■	■
10194672				■	■					■		■		■	■	■
10194872	■					■				■		■		■	■	■
10194873		■				■				■		■		■	■	■
10194874			■			■				■		■		■	■	■
10194875				■		■				■		■		■	■	■
10194888	■				■				■			■		■	■	■
10194889		■			■				■			■		■	■	■
10194890			■		■				■			■		■	■	■
10194891				■	■				■			■		■	■	■
10194908	■					■			■			■		■	■	■
10194909		■				■			■			■		■	■	■
10194910			■			■			■			■		■	■	■
10194931				■		■			■			■		■	■	■
10194936	■						■		■			■		■	■	■
10194937		■					■		■			■		■	■	■
10194938			■				■		■			■		■	■	■
10194939				■			■		■			■		■	■	■
10194940	■							■	■			■		■	■	■
10194941		■						■	■			■		■	■	■
10194942			■					■	■			■		■	■	■
10194943				■				■	■			■		■	■	■
10194961		■				■				■			■	■	■	■
10194962			■			■				■			■	■	■	■
10195038		■			■					■	■			■	■	■
10195039			■		■					■	■			■	■	■
10195092		■			■				■		■			■	■	■
10195093			■		■				■		■			■	■	■
10195110		■				■			■		■			■	■	■
10195111			■			■			■		■			■	■	■

MSA V-FIT Full-Body Harness

V-FIT Standard Full-Body Harness with Front D-Ring

Part Number	Size				D-Ring Configuration			Leg Straps		Padding	Standards		
	XSM	STD	XLG	SXL	Back & Chest	Back, Chest, & Hip	Shoulder	Tongue Buckle	Quick-Connect	Shoulder	ANSI Z359.11	CSA Z259.10	OSHA
10194673	■				■				■	■	■	■	■
10194656		■			■				■	■	■	■	■
10194657			■		■				■	■	■	■	■
10194862				■	■				■	■	■	■	■
10194863	■					■			■	■	■	■	■
10194864		■				■			■	■	■	■	■
10194865			■			■			■	■	■	■	■
10194866				■		■			■	■	■	■	■
10194892	■				■			■		■	■	■	■
10194893		■			■			■		■	■	■	■
10194894			■		■			■		■	■	■	■
10194895				■	■			■		■	■	■	■
10194896	■					■		■		■	■	■	■
10194897		■				■		■		■	■	■	■
10194898			■			■		■		■	■	■	■
10194899				■		■		■		■	■	■	■
10194900	■					■	■	■		■	■	■	■
10194905		■				■	■	■		■	■	■	■
10194906			■			■	■	■		■	■	■	■
10194907				■		■	■	■		■	■	■	■

V-FIT Construction Full-Body Harness

Part Number	Size				D-Ring Configuration		Leg Straps		Padding		Standards		
	XSM	STD	XLG	SXL	Back, Chest, & Hip	Back & Hips	Tongue Buckle	Quick-Connect	Shoulder & Lumbar	Shoulder, Leg, & Lumbar	ANSI Z359.11	CSA Z259.10	OSHA
10195133	■					■		■	■		■	■	■
10195134		■				■		■	■		■	■	■
10195135			■			■		■	■		■	■	■
10195136				■		■		■	■		■	■	■
10195140	■				■		■		■		■	■	■
10195141		■			■		■		■		■	■	■
10195142			■		■		■		■		■	■	■
10195143				■	■		■		■		■	■	■
10195149		■				■	■		■		■	■	■
10195150			■			■	■		■		■	■	■
10195151				■		■	■		■		■	■	■
10195181		■				■	■			■	■	■	■
10195182			■			■	■			■	■	■	■
DERRICK HARNESS													
10195204	■				■		■		■		■	■	■
10195205		■			■		■		■		■	■	■
10195206			■		■		■		■		■	■	■
10195207				■	■		■		■		■	■	■

V-FIT Tower Full-Body Harness with Front D-Ring

Part Number	Size				D-Ring Configuration	Leg Straps		Tool Belt		Padding	Standards		
	XSM	STD	XLG	SXL	Back, Hip, & Shoulder	Tongue Buckle	Quick-Connect	Tongue Buckle	Quick-Connect	Shoulder, Leg, & Lumbar	ANSI Z359.11	CSA Z259.10	OSHA
10218041	■				■	■		■		■	■	■	■
10218042		■			■	■		■		■	■	■	■
10218043			■		■	■		■		■	■	■	■
10218045				■	■	■		■		■	■	■	■
10218046	■				■		■		■	■	■	■	■
10218048		■			■		■		■	■	■	■	■
10218049			■		■		■		■	■	■	■	■
10218050				■	■		■		■	■	■	■	■

Our Mission

MSA's mission is to see to it that men and women may work in safety and that they, their families and their communities may live in health throughout the world.

MSA: WE KNOW WHAT'S AT STAKE.

Note: This Bulletin contains only a general description of the products shown. While product uses and performance capabilities are generally described, the products shall not, under any circumstances, be used by untrained or unqualified individuals. The products shall not be used until the product instructions/user manual, which contains detailed information concerning the proper use and care of the products, including any warnings or cautions, have been thoroughly read and understood. Specifications are subject to change without prior notice. MSA is a registered trademark of MSA Technology, LLC in the US, Europe, and other Countries. For all other trademarks visit <https://us.msasafety.com/Trademarks>.

MSA operates in over 40 countries worldwide. To find an MSA office near you, please visit [MSAsafety.com/offices](https://us.msasafety.com/offices).