




V-FLEX[®] Full-Body Harness

Superior Comfort



Using a patent-pending RaceFLEX connection, webbing is routed across the chest for a secure and comfortable fit—eliminating the need for bulky chest straps or cumbersome buckles.



Reduce fatigue with flexible foam shoulder pad that responds to your movement to conform to your body, eliminating pressure points and chafing.



Keep cool and reduce heat stress with interior padding designed with channels for continuous air flow and ventilation.

Flexibility



Using an exclusive racing style design, webbing contours to the torso, reducing the need for adjustments throughout the day and allowing for better mobility on the job.



Featuring a patent-pending hip connection, the harness “flexes” with the worker, reducing fatigue throughout the day.

Adjustability



Pull down adjustment allows you to quickly and easily get the right fit that last throughout the work day.




WE KNOW WHAT'S AT STAKE.


V-FLEX Full-Body Harness



**V-FLEX Standard
Full-Body Harness**



**V-FLEX Construction
Full-Body Harness**



**V-FLEX Standard Full-Body
Harness w/Front D-Ring**



V-FLEX Harness Padding

Contoured padding fits the body's normal curves to reduce pinch points and chaffing.

Closed cell foam reduces moisture build-up—keeping your pad from getting soggy and extending the life of your harness.

Keep cool and reduce heat stress with interior padding designed with channels for continuous air flow. Vented “V” feature allows for fresh air to flow from outside the pad, to inside.

Check out our [Harness Heat Study](#) here!

V-FLEX Construction Harness Adjustable Waist Pad

The V-FLEX Harness' adjustable waist pad allows you to position the waist pad specifically for you and your work day. With its patent-pending design, the V-FLEX waist pad can be adjusted higher on your torso for lumbar support or lower for work positioning applications. Designed around pressure points and by choosing breathable materials, the V-FLEX waist pad delivers ultimate on-the-job comfort.

Harness Size Chart

	ft.	(m)												
	6'-6"	(2.0)												
	6'-4"	(1.9)												
	6'-2"	(1.9)												
	6'-0"	(1.8)												
	5'-10"	(1.8)												
	5'-8"	(1.7)												
	5'-6"	(1.7)												
	5'-4"	(1.6)												
	5'-2"	(1.6)												
	5'-0"	(1.5)												



V-FLEX Construction Full-Body Harness Ordering Information

Part Number	Size				D-Ring Configuration			Leg Straps		Standards		
	XSM	STD	XLG	SXL	Back	Chest	Hip	Tongue Buckle	Quick-Connect	ANSI Z359.11	CSA Z259.5	OSHA
10211324	■				■		■		■	■	■	■
10211325		■			■		■		■	■	■	■
10211326			■		■		■		■	■	■	■
10211327				■	■		■		■	■	■	■
10211328	■				■		■	■		■	■	■
10211329		■			■		■	■		■	■	■
10211330			■		■		■	■		■	■	■
10211331				■	■		■	■		■	■	■
10211342	■				■	■	■		■	■	■	■
10211343		■			■	■	■		■	■	■	■
10211344			■		■	■	■		■	■	■	■
10211345				■	■	■	■		■	■	■	■
10211346	■				■	■	■	■		■	■	■
10211347		■			■	■	■	■		■	■	■
10211348			■		■	■	■	■		■	■	■
10211349				■	■	■	■	■		■	■	■

Note: This Bulletin contains only a general description of the products shown. While product uses and performance capabilities are generally described, the products shall not, under any circumstances, be used by untrained or unqualified individuals. The products shall not be used until the product instructions/user manual, which contains detailed information concerning the proper use and care of the products, including any warnings or cautions, have been thoroughly read and understood. Specifications are subject to change without prior notice. MSA is a registered trademark of MSA Technology, LLC in the US, Europe, and other Countries. For all other trademarks visit <https://us.msasafety.com/Trademarks>.

MSA operates in over 40 countries worldwide. To find an MSA office near you, please visit [MSAsafety.com/offices](https://us.msasafety.com/offices).