

V-FORM[®]+ Full-Body Harness



Superior Comfort



The patent-pending racing-style buckle allows for a close, comfortable harness fit — eliminating the need for bulky chest straps or cumbersome buckles.



Shoulder padding responds to your movement to conform to your body, eliminating pressure points and chafing.

Increased Flexibility



The racing-style buckle creates an athletic cut, contouring the harness to the body and improving upper torso movement on the job.

Adjustability



Pull-down adjustment allows you to quickly and easily get the right fit that lasts throughout the work day.



Dedicated attachment point for Personal Fall Limiters allows for quick and easy attachment, and keeps your back D-ring free for other use.

WE KNOW WHAT'S AT STAKE.

V-FORM+ Harness Ordering Information

Part Number	D-Ring Configuration				Size (See chart on following page.)				Leg Buckle Type		Padding	Standards
	Back	Back, Hips	Back, Chest	Back, Chest, Hips	XSM	STD	XLG	SXL	Tongue Buckle	Quick-Connect	Shoulder	ANSI Z359.11/ CSA Z259.10/ OSHA
10206085	■				■				■		■	■
10205845	■					■			■		■	■
10206086	■						■		■		■	■
10206087	■							■	■		■	■
10206088		■			■				■		■	■
10206089		■				■			■		■	■
10206090		■					■		■		■	■
10206091		■						■	■		■	■
10206092			■		■				■		■	■
10206093			■			■			■		■	■
10206094			■				■		■		■	■
10206095			■					■	■		■	■
10206136				■	■				■		■	■
10206137				■		■			■		■	■
10206138				■			■		■		■	■
10206139				■				■	■		■	■
10206100	■				■					■	■	■
10206101	■					■				■	■	■
10206102	■						■			■	■	■
10206103	■							■		■	■	■
10206104		■			■					■	■	■
10206105		■				■				■	■	■
10206106		■					■			■	■	■
10206107		■						■		■	■	■
10206108			■		■					■	■	■
10206109			■			■				■	■	■
10206110			■				■			■	■	■
10206111			■					■		■	■	■
10206144				■	■					■	■	■
10206145				■		■				■	■	■
10206146				■			■			■	■	■
10206147				■				■		■	■	■



V-FORM+ Construction Harness Ordering Information

Part Number	D-Ring Configuration		Size (See chart below.)				Leg Buckle Type		Standards
	Back, Hips	Back, Chest, Hips	XSM	STD	XLG	SXL	Tongue Buckle	Quick-Connect	
10206160	■		■				■		■
10206161	■			■			■		■
10206162	■				■		■		■
10206163	■					■	■		■
10206164		■	■				■		■
10206165		■		■			■		■
10206166		■			■		■		■
10206167		■				■	■		■
10206172	■		■					■	■
10206173	■			■				■	■
10206174	■				■			■	■
10206175	■					■		■	■
10206176		■	■					■	■
10206177		■		■				■	■
10206178		■			■			■	■
10206179		■				■		■	■



Harness Size Chart

ft.	(m)	
6'-6"	(2.0)	
6'-4"	(1.9)	
6'-2"	(1.9)	
6'-0"	(1.8)	
5'-10"	(1.8)	
5'-8"	(1.7)	
5'-6"	(1.7)	
5'-4"	(1.6)	
5'-2"	(1.6)	
5'-0"	(1.5)	
lb.	(kg)	
110	(50)	
130	(59)	
150	(68)	
170	(77)	
190	(86)	
210	(95)	
230	(105)	
250	(114)	
270	(123)	
290	(132)	
310	(141)	
330	(150)	
400	(181)	

Note: This Bulletin contains only a general description of the products shown. While product uses and performance capabilities are generally described, the products shall not, under any circumstances, be used by untrained or unqualified individuals. The products shall not be used until the product instructions/user manual, which contains detailed information concerning the proper use and care of the products, including any warnings or cautions, have been thoroughly read and understood. Specifications are subject to change without prior notice. MSA is a registered trademark of MSA Technology, LLC in the US, Europe, and other Countries. For all other trademarks visit <https://us.msasafety.com/Trademarks>.

MSA operates in over 40 countries worldwide. To find an MSA office near you, please visit [MSAsafety.com/offices](https://us.msasafety.com/offices).